



# OAKTON®

## WATERPROOF ECOTESTR™ PH 2 POCKET METER

EASY-TO-READ DISPLAY WITH  
AN EASY-TO-AFFORD PRICE!

**New**



- Economical and easy to use
- Simply dip and read—the orientation of the display means there is no need to turn your head or tilt the tester.
- Nonreplaceable sensor keeps the costs down—great for applications where losing a more expensive meter is a concern
- The single-junction electrode is recessed to protect against breakage
- The unit offers up to three-point calibration with auto-buffer recognition for quick calibrations
- Automatic temperature compensation ensures accurate reading under changing conditions
- Waterproof and dustproof housing designed for use in dirty or wet field conditions

 **Cole-Parmer®**  
scientific experts



**In the U.S.**

625 E. Bunker Court  
Vernon Hills, IL 60061  
Call toll-free 800-323-4340  
Phone: 847-549-7600  
Fax: 847-247-2929  
[www.coleparmer.com](http://www.coleparmer.com)

**In Canada**

Call toll-free 800-363-5900  
Phone: 514-355-6100  
Fax: 514-355-7119  
[www.coleparmer.ca](http://www.coleparmer.ca)

**In the United Kingdom**

Free phone: 0500-345-300  
Phone: 020-8574-7556  
Fax: 020-8574-7543  
[www.coleparmer.co.uk](http://www.coleparmer.co.uk)

**In India**

Phone: 91-22-6716-2222  
Fax: 91-22-6716-2211  
[www.coleparmer.in](http://www.coleparmer.in)

**International customers**

Call 847-549-7600 to reach our International Sales Department or contact your local dealer.

**FREE TECHNICAL APPLICATIONS ASSISTANCE!**

## APPLICATIONS

Drinking water, hydroponics, classroom, environmental studies, field work, basic lab use, and anywhere where you frequently have to replace lost or broken pH meters!

## PERFORMANCE SPECIFICATIONS

- Hold function allows you to lock a measured value
- Auto-off feature prolongs battery life
- Clear cover serves as a solution holder
- Built-in belt clip allows you to keep meter accessible when not in use



**Range:**

0.0 to 14.0 pH

**Buffer recognition:**

4.0, 7.0, or 10.0

**Dimensions:**

6¼"L x 1⅝"W x 1⅛"H

**Resolution:**

0.1 pH

**Operating temperature:**

32 to 122°F (0 to 50°C)

**Accuracy:**

±0.1 pH

**Display**

three-digit vertical LCD

**Temperature compensation:**

automatic

**Power:**

four 1.5 V button cell batteries (included)

**Calibration:**

up to three point

**Battery life:**

>300 hours

Catalog number	Description
<a href="#">ML-35423-10</a>	Waterproof EcoTestr™ pH 2 Pocket Meter

[ML-09377-16](#) Replacement batteries, 1.5 V. Pack of 6

**What's included:**

Four 1.5 V button cell batteries

