

## WHIRL-PAK® Sterile Sampling Bags, LDPE

Keep samples safe—easy-seal bags hold solids and liquids

- Quick and easy sealing—flip bag around wire/tape and bend to seal
- No more poking—puncture-proof tabs keep wire intact even after extensive use

Sampling Bags are available with or without a white labeling area.

“Speci-Sponge” Bags are designed to sample surfaces and equipment for *Listeria*, *Salmonella*, and other food-borne pathogens; contain a 1½" x 3" (3.8 x 7.6 cm) sponge that is free of bactericides and noninhibitory; with white labeling area.

Sodium Thiosulfate Bags are EPA-compliant for potable water collection; contain a nontoxic, nonnutritive 10-mg active ingredient tablet of sodium thiosulfate to neutralize the chlorine at the point of collection; with white labeling area.

High-Temperature Bag is for hot fill samples with a temperature up to 215°F (102°C). The FDA-compliant film is a blend of low-density polyethylene and nylon that will hold liquids, solids, sauces, gravies, and other samples having a high temperature. Bag is self standing and does not need a rack or special holder to keep it upright, making sample collection safe and easy. With white labeling area. **Caution:** Do not put bag in boiling water.



**Buy More...Save More!**  
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

STERILE

Capacity oz (mL)	Size (W x L)	Thickness (mil)	Catalog number	Qty/pk	Price/pk
<b>Sampling bags without white labeling area</b>					
4 (118)	3" x 7¼" (7.6 x 18.4 cm)	2.25	<a href="#">GH-06499-10</a>	500	
18 (532)	4½" x 9" (11.4 x 22.9 cm)	2.5	<a href="#">GH-06499-20</a>	500	
24 (710)	6" x 9" (15.2 x 22.9 cm)	3.0	<a href="#">GH-06499-30</a>	500	
36 (1065)	5" x 15" (12.7 x 38.1 cm)	3.0	<a href="#">GH-06499-40</a>	500	
42 (1242)	6" x 15" (15.2 x 38.1 cm)	3.0	<a href="#">GH-06499-50</a>	500	
69 (2041)	7½" x 15" (19.1 x 38.1 cm)	3.0	<a href="#">GH-06499-54</a>	500	
<b>Standup sampling bags with white labeling area</b>					
4 (118)	3" x 7¼" (7.6 x 18.4 cm)	2.5	<a href="#">GH-06499-16</a>	500	
18 (532)	4½" x 9" (11.4 x 22.9 cm)	3.0	<a href="#">GH-06499-21</a>	500	
24 (710)	6" x 9" (15.2 x 22.9 cm)	3.0	<a href="#">GH-06499-31</a>	500	
27 (798)	5" x 12" (12.7 x 30.5 cm)	3.0	<a href="#">GH-06499-32</a>	250	
36 (1065)	5" x 15" (12.7 x 38.1 cm)	4.0	<a href="#">GH-06499-33</a>	250	
42 (1242)	6" x 15" (15.2 x 38.1 cm)	4.0	<a href="#">GH-06499-34</a>	250	
69 (2041)	7½" x 15" (19.1 x 38.1 cm)	4.0	<a href="#">GH-06499-35</a>	250	
<b>Sampling bags with white labeling area</b>					
2 (58)	3" x 5" (7.6 x 12.7 cm)	2.5	<a href="#">GH-06499-60</a>	500	
4 (118)	3" x 7¼" (7.6 x 18.4 cm)	2.25	<a href="#">GH-06499-70</a>	500	
7 (207)	3¾" x 7" (9.5 x 17.8 cm)	2.5	<a href="#">GH-06499-72</a>	500	
13 (384)	5½" x 7½" (13.3 x 19.1 cm)	2.5	<a href="#">GH-06499-74</a>	500	
18 (532)	4½" x 9" (11.4 x 22.9 cm)	2.5	<a href="#">GH-06499-80</a>	500	
24 (710)	6" x 9" (15.2 x 22.9 cm)	3.0	<a href="#">GH-06499-85</a>	500	
27 (798)	5" x 12" (12.7 x 30.5 cm)	3.0	<a href="#">GH-06499-87</a>	500	
69 (2041)	7½" x 15" (19.1 x 38.1 cm)	3.0	<a href="#">GH-06499-89</a>	500	
92 (2721)	10" x 15" (25.4 x 38.1 cm)	4.0	<a href="#">GH-06499-94</a>	250	
123 (3637)	10" x 20" (25.4 x 50.8 cm)	4.0	<a href="#">GH-06499-98</a>	250	
184 (5441)	15" x 20" (38.1 x 50.8 cm)	4.0	<a href="#">GH-06499-99</a>	100	
<b>"Speci-Sponge" bags for surface sampling with sponge</b>					
18 (532)	4½" x 9" (11.4 x 22.9 cm)	2.5	<a href="#">GH-06499-13</a>	100	
55 (1627)	7½" x 11¼" (19.1 x 29.8 cm)	4.0	<a href="#">GH-06499-14</a>	100	
18 (532)	4" x 9" (10.2 x 22.9 cm)	2.5	<a href="#">GH-06499-52</a>	100	
<b>Sodium thiosulfate bags for water sampling with tablet</b>					
3% (100)	3" x 7¼" (7.6 x 18.4 cm)	2.5	<a href="#">GH-06499-90</a>	100	
10% (300)	4½" x 9" (11.4 x 22.9 cm)	2.5	<a href="#">GH-06499-95</a>	100	
<b>High-temperature bag</b>					
18 (532)	4½" x 9" (11.4 x 22.9 cm)	3.0	<a href="#">GH-06498-16</a>	500	

\*Model 06499-52 has a sterile glove.

### Accessories

[GH-66203-10](#) Carrying rack for 2- and 4-oz bags. Double-grid design keeps bags upright and has 15 compartments. Vinyl coated, autoclavable

[GH-66203-00](#) Carrying rack for 18-oz bags. Double-grid design keeps bags upright. Rack has 20 compartments. Vinyl coated, autoclavable

[GH-06498-12](#) Water scoop, 18" (45.7 cm) L coated handle. Two alligator clips hold a variety of bag sizes

[GH-06498-14](#) Mailing tube for 3%-oz (100 mL) sodium thiosulfate bag. Polyethylene, 5"L x 2" dia (12.7 x 5.1 cm)



Standup bags stay upright



Water scoop holds bag open for easy filling



Mailing tube



Rack