

OHAUS® Defender™ 3000 Washdown Industrial Scales

Rugged design for industrial weighing and counting

- 304 stainless steel platform with painted carbon steel frame and IP67-rated load cell
- Parts counting mode with selectable sample sizes, last sample size, and average piece weight data
- Built-in RS-232 for printing and data connection
- Display indicator offers flexible mounting capabilities for unlimited placement options
- Built-in rechargeable battery operation allows portability

What's included: indicator, display column, AC power adapter and internal rechargeable lead acid battery.



Specifications

Calibration: external, with calibration mass

Weighing units: g, kg, oz, lb:oz



| Capacity | Readability | Repeatability | Linearity | Platform size (L x W) | Display column (H) | 115 VAC | | 230 VAC | |
|----------|-------------|---------------|-----------|-------------------------------|--------------------|-----------------------------|-------|-----------------------------|-------|
| | | | | | | Catalog number | Price | Catalog number | Price |
| 30 kg | 5 g | ±5 g | ±5 g | 14" x 12" (35.6 x 30.5 cm) | 23" (58.4 cm) | GH-01006-71 | | GH-01006-72 | |
| 60 kg | 10 g | ±10 g | ±10 g | | | GH-01006-73 | | GH-01006-74 | |
| 60 kg | 10 g | ±10 g | ±10 g | 21 5/8" x 16 1/2" | 36" (91.4 cm) | GH-01006-75 | | GH-01006-76 | |
| 150 kg | 20 g | ±20 g | ±20 g | (54.9 x 41.9 cm) | | GH-01006-77 | | GH-01006-78 | |
| 150 kg | 20 g | ±20 g | ±20 g | 19 3/4" x 25 1/2" | | GH-01006-48 | | GH-01006-49 | |
| 300 kg | 20 g | ±20 g | ±20 g | (65 x 50 cm) | | GH-01006-58 | | GH-01006-59 | |

[GH-11610-68](#) Compact thermal printer

[GH-11901-57](#) Printer cable kit, required for use with printer

[GH-11901-53](#) Thermal printer paper

[GH-17101-52](#) NIST-traceable calibration w/data for balance/scale

A&D GP Washdown Industrial Scales

Adjustable swing arm display makes weighing bulky items easy

- Protection against moisture and dust to IP65/NEMA 4 standards
- Automatic internal calibration when scale detects changes in ambient temperature
- Clear, large vacuum fluorescent display is easy to see under any lighting conditions

What's included: AC power adapter.



Specifications

Calibration: internal

Weighing units: g, kg, lb, oz, ct, dwt, momme

Platform size: 15 1/4" x 12 1/2" (38.4 x 34.3 cm)

Output: built-in bidirectional RS-232C with Windows® Communication Tools (WinCT)

Power: 115 VAC

| Capacity | Readability | Repeatability | Linearity | Display column (H) | Catalog number | Price |
|----------------|-------------|---------------|-----------|--|---|-------|
| 6/31 kg | 0.1/1 g | ±0.1/0.5 g | ±0.2/1 g | Remote indicator, no column 25 1/2" (65.2 cm) | GH-11115-92 GH-11115-91 | |
| 12 kg 21 kg | 0.1 g | ±0.1 g | ±0.2 g | 25 1/2" (65.2 cm) | GH-11126-00 GH-11126-02 | |
| 31 kg | 0.1 g | ±0.1 g | ±0.2 g | 25 1/2" (65.2 cm) | GH-11126-06 | |
| 41 kg | 0.5 g | ±0.5 g | ±1 g | Remote indicator, no column 25 1/2" (65.2 cm) | GH-11111-09 GH-11126-08 | |
| 61 kg | 0.1 g | ±0.2 g | ±0.5 g | 25 1/2" (65.2 cm) | GH-11115-94 | |
| 61 kg | 1 g | ±0.7 g | ±1 g | Remote indicator, no column 25 1/2" (65.2 cm) | GH-11115-95 GH-11115-93 GH-11126-10 | |
| 61/101 kg | 10/1 g | ±5/1 g | ±10/2 g | 25 1/2" (65.2 cm) | GH-11126-14 | |
| 100 kg | 1 g | ±1 g | ±2 g | 25 1/2" (65.2 cm) | GH-11126-12 | |
| | | | | Remote indicator, no column | GH-11111-10 | |

*Scale comes with remote indicator

[GH-11126-92](#) Printer, compact

[GH-17101-52](#) NIST-traceable calibration for balances/scales

