

### Scienceware® High-Capacity Beakers, PP

#### Easy pouring of large samples

- Easy dispensing with flared rim and pouring spout
- Withstand temperatures to 250°F (121°C).
- Autoclavable



Capacity mL (oz)	Graduations (mL)	Catalog number	Qty/pk	Price/pk
5000 (160)	100	<a href="#">GH-06147-00</a>	1	
10,000 (320)	200	<a href="#">GH-06147-10</a>		

### Graduated Beakers with Easy-Grip Handles

#### Sturdy handle

- Always know your volume—molded-in graduations never rub off
- Choose the right material for your application—available in PMP, HDPE, PP, PC, and PFA



**Buy More... Save More!**  
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Graduations (mL)	Qty/pk	Catalog number	Price/pk
<b>Thermo Scientific™ Nalgene™ polymethylpentene (PMP) beakers</b>				
1000 (32)	5	1	<a href="#">GH-06004-97</a>	
3000 (96)	10		<a href="#">GH-06004-99</a>	
<b>Thermo Scientific Nalgene high-density polyethylene (HDPE) beakers</b>				
1000 (32)	100	1	<a href="#">GH-06005-10</a>	
3000 (96)	200		<a href="#">GH-06005-20</a>	
<b>Polypropylene (PP) beakers</b>				
50 (1.5)	10	1	<a href="#">GH-06100-97</a>	
100 (3.5)	20		<a href="#">GH-06100-99</a>	
250 (8)	5		<a href="#">GH-06008-35</a>	
500 (16)	10		<a href="#">GH-06008-40</a>	
1000 (32)	10	1	<a href="#">GH-06008-50</a>	
2000 (64)	20		<a href="#">GH-06008-60</a>	
3000 (96)	50		<a href="#">GH-06008-70</a>	
5000 (160)	100		<a href="#">GH-06008-80</a>	
<b>Polycarbonate (PC) beakers</b>				
470 (16)	25	1	<a href="#">GH-06004-80</a>	
950 (32)	50		<a href="#">GH-06004-85</a>	
1900 (64)	250		<a href="#">GH-06004-90</a>	
3800 (128)	500		<a href="#">GH-06004-95</a>	
<b>Thermo Scientific Nalgene PFA beakers</b>				
1000 (32)	50	1	<a href="#">GH-06006-00</a>	
3000 (96)	125		<a href="#">GH-06006-05</a>	

### Cole-Parmer® Class A Griffin Low-Form Graduated Glass Beakers

#### Easy readings and exceptional durability

- Double-scale graduations for easy measuring while pouring in or out
- Meet ASTM E960 specifications for Class A borosilicate glass beakers
- Stand up to temperatures of 445°F (230°C) for long-term, or 752°F (400°C) for short-term
- Autoclavable

**NEW**



**Buy More... Save More!**

20% off on 120+  
15% off on 30 to 119  
10% off on 6 to 29 packs or cases

Capacity mL (oz)	Graduation interval (mL)	Catalog number	Qty/pk	Price/pk
10 (1/8)	—	<a href="#">GH-34503-42</a>	12	
25 (7/8)	5	<a href="#">GH-34503-44</a>	12	
50 (1 3/4)	10	<a href="#">GH-34503-46</a>	12	
100 (3)	10	<a href="#">GH-34503-48</a>	12	
150 (5)	20	<a href="#">GH-34503-50</a>	12	
250 (8)	25	<a href="#">GH-34503-52</a>	12	
400 (13)	25	<a href="#">GH-34503-54</a>	12	
600 (20)	50	<a href="#">GH-34503-56</a>	6	
1000 (32)	50	<a href="#">GH-34503-58</a>	6	
2000 (64)	100	<a href="#">GH-34503-60</a>	4	
3000 (96)	125	<a href="#">GH-34503-62</a>	1	
5000 (160)	250	<a href="#">GH-34503-64</a>	1	

†The 10-mL beaker does not have graduations

### Cole-Parmer® Broad-Spout Beakers, PTFE

#### Stand up to the harshest chemicals

- Pour easily with broad spout
- Heatable beakers can be used on hot plates to 518°F (270°C)
- Autoclavable

Heatable beaker 06300-02 has a PTFE carbon base.



**Buy More... Save More!**  
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Beaker			Optional cover		
	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/pk	Price/pk
<b>Heatable beakers with PTFE-carbon base, for use on hot plates</b>						
100 (3)	<a href="#">GH-06300-02</a>	1		<a href="#">GH-06300-87</a>	1	
250 (8)	<a href="#">GH-06300-04</a>	1		<a href="#">GH-06300-91</a>	1	
400 (13)	<a href="#">GH-06300-06</a>	1		<a href="#">GH-06300-93</a>	1	
<b>Beakers</b>						
1 (0.03)	<a href="#">GH-06300-62</a>	2		<a href="#">GH-06300-79</a>	2	
5 (1.17)	<a href="#">GH-06300-64</a>	2		<a href="#">GH-06300-81</a>	2	
10 (0.3)	<a href="#">GH-06300-66</a>	2		<a href="#">GH-06300-81</a>	2	
25 (0.8)	<a href="#">GH-06300-68</a>	2		<a href="#">GH-06300-83</a>	2	
50 (1.6)	<a href="#">GH-06300-74</a>	1		<a href="#">GH-06300-85</a>	1	
100 (3)	<a href="#">GH-06300-76</a>	1		<a href="#">GH-06300-87</a>	1	
150 (5)	<a href="#">GH-06300-78</a>	1		<a href="#">GH-06300-89</a>	1	
250 (8)	<a href="#">GH-06300-82</a>	1		<a href="#">GH-06300-91</a>	1	
400 (13)	<a href="#">GH-06300-84</a>	1		<a href="#">GH-06300-93</a>	1	
500 (16)	<a href="#">GH-06300-86</a>	1		<a href="#">GH-06300-93</a>	1	
600 (20)	<a href="#">GH-06300-88</a>	1		<a href="#">GH-06300-95</a>	1	
1000 (32)	<a href="#">GH-06300-92</a>	1		<a href="#">GH-06300-95</a>	1	
2000 (64)	<a href="#">GH-06300-94</a>	1		<a href="#">GH-06300-97</a>	1	
5000 (170)	<a href="#">GH-06300-96</a>	1		<a href="#">GH-06300-99</a>	1	