

**Thermo Scientific™ Nalgene™
Narrow-Mouth PassPort™
IP2 Bottles, HDPE**

Ship hazardous
samples reliably

- Safe for small quantities of corrosives or cleaning supplies
- Leakproof, PP screw cap
- Volume, registration notch, material, and IP2 markings molded into bottom



Buy More...Save More!

- 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Cap size	Catalog number	Qty/pk	Price/pk
60 (2)	20 mm	GH-06253-10	12	
125 (4)	24 mm	GH-06253-20	12	
250 (8)	24 mm	GH-06253-30	12	
500 (16)	28 mm	GH-06253-40	12	
1000 (32)	38-430	GH-06253-50	6	
4000 (128)	38-430	GH-06253-60	1	

**Thermo Scientific™ Nalgene™ Large
Narrow-Mouth
Bottles, PP**

Store large samples
of chemicals safely

- Leakproof, polypropylene caps
- Built-in shoulder loop for easier handling on 4- and 8-liter sizes
- Autoclavable



Buy More...Save More!

- 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity L (gal.)	Cap size	Catalog number	Qty/pk	Price/pk
Clear bottles, PP				
2 (½)	38-430	GH-06028-10		
4 (1)	38-430	GH-06028-20	1	
8 (2)	53B	GH-06028-30		
Amber bottles, PP				
2 (½)	38-430	GH-06027-10		
4 (1)	38-430	GH-06027-20	1	
8 (2)	53B	GH-06027-30		

**Thermo Scientific™ Nalgene™ Jugs with
Handle, LDPE and PP**

Easy pour design

- Carry samples easily with molded-in handle
- PP versions are autoclavable
- Leakproof



Buy More...Save More!

- 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity L (gal.)	Cap size	Catalog number	Qty/pk	Price/pk
Jugs, LDPE				
4 (1)	38-430	GH-06062-10		
8 (2)	53B	GH-06062-20	1	
Jugs, PP, Autoclavable				
4 (1)	38-430	GH-06064-10		
8 (2)	53B	GH-06064-20	1	
Replacement caps, PP				
—	38-430	GH-63000-18	12	
—	53B	GH-63000-20		

**Sanitary
Bottles, 316L SS
(Light Gauge)**

Keep air and
liquids out

- Constructed of 316L stainless steel with #9, 24 Ra finish
- Included sanitary Tri-Clamp® flange opening, end cap platinum-cured silicone gasket, and heavy-duty clamp



Capacity L (gal.)	Tri-Clamp opening	Neck ID	Bottom OD	Catalog number	Qty/pk	Price/pk
1 (¼)	2" 3"	1⅞" 3"	4" (10.2 cm)	GH-07506-01 GH-07506-31	1	
2 (½)	2" 4"	1⅞" 3⅞"	4¾" (12.1 cm)	GH-07506-02 GH-07506-32	1	
5 (1½)	2" 4"	1⅞" 3⅞"	7⅞" (18.1 cm) 6⅞" (16.2 cm)	GH-07506-05 GH-07506-35	1	
10 (2½)	2" 4"	1⅞" 3⅞"	8¾" (22.2 cm) 8⅞" (21.3 cm)	GH-07506-10 GH-07506-80	1	
20 (5¼)	2" 4"	1⅞" 3⅞"	10⅝" (27.0 cm)	GH-07506-20 GH-07506-90	1	

Wait!

There's More at
ColeParmer.com

Browse 100,000+ products plus find
Technical Resources to help you choose