

### Cole-Parmer® Wide-Mouth Bottles, LDPE, HDPE, PP

Wide-mouth opening provides easier filling and sampling

- Offered in pack quantities or bulk pack quantities to meet your specific requirements
- Reliable and sturdy
- Choose from three materials; all include a leakproof PP closure

**HDPE Bottles** are manufactured with FDA-compliant resin for noncontaminating storage of chemicals and food-grade products.

**LDPE Bottles** are translucent and ideal for food and general-use laboratory applications.

**PP Bottles** are rigid and offer superior chemical resistance; perfect for storage and sampling of liquids and solids. **Autoclavable.**



**Buy More...Save More!**

- \$ 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases



Capacity mL (oz)	Cap size	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/cs	Price/cs
<b>HDPE</b>							
60 (2)	22 mm	<a href="#">GH-06045-18</a>	12		<a href="#">GH-06045-23</a>	72	
125 (4)	28 mm	<a href="#">GH-06045-24</a>	12		<a href="#">GH-06045-25</a>	72	
250 (8)	28 mm	<a href="#">GH-06045-26</a>	12		<a href="#">GH-06045-27</a>	72	
500 (16)	28 mm	<a href="#">GH-06045-28</a>	12		<a href="#">GH-06045-29</a>	48	
1000 (32)	28 mm	<a href="#">GH-06045-44</a>	6		<a href="#">GH-06045-31</a>	24	
2000 (64)	45 mm	<a href="#">GH-06045-46</a>	1		<a href="#">GH-06045-33</a>	6	
<b>LDPE</b>							
60 (2)	22 mm	<a href="#">GH-06045-02</a>	12		<a href="#">GH-06045-03</a>	72	
125 (4)	28 mm	<a href="#">GH-06045-04</a>	12		<a href="#">GH-06045-05</a>	72	
250 (8)	28 mm	<a href="#">GH-06045-06</a>	12		<a href="#">GH-06045-07</a>	72	
500 (16)	28 mm	<a href="#">GH-06045-08</a>	12		<a href="#">GH-06045-09</a>	48	
1000 (32)	28 mm	<a href="#">GH-06045-14</a>	6		<a href="#">GH-06045-11</a>	6	
<b>PP</b>							
30 (1)	22 mm	<a href="#">GH-06045-48</a>	12		<a href="#">GH-06045-41</a>	72	
60 (2)	22 mm	<a href="#">GH-06045-58</a>	12		<a href="#">GH-06045-43</a>	72	
125 (4)	28 mm	<a href="#">GH-06045-56</a>	12		<a href="#">GH-06045-45</a>	72	
250 (8)	28 mm	<a href="#">GH-06045-62</a>	12		<a href="#">GH-06045-47</a>	72	
500 (16)	28 mm	<a href="#">GH-06045-66</a>	12		<a href="#">GH-06045-49</a>	48	
1000 (32)	28 mm	<a href="#">GH-06045-68</a>	6		<a href="#">GH-06045-51</a>	24	
2000 (64)	45 mm	<a href="#">GH-06045-74</a>	1		<a href="#">GH-06045-53</a>	6	

### Sample Bottles, HDPE

Store samples without breaking your budget

- Provide good chemical resistance for a wide range of uses
- Bottles are made of HDPE; included cap is made of polypropylene and lined with polyethylene foam
- Easy mailing with optional mailing tube (sold separately)



**Buy More...Save More!**

- \$ 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Qty/pk	Catalog number	Price/pk
180 (6)	300	<a href="#">GH-06043-01</a>	
250 (8)	329	<a href="#">GH-06049-01</a>	
500 (16)	198	<a href="#">GH-06050-05</a>	

[GH-06049-30](#) Mailing tubes for bottle 06049-01. Carton of 240

### Thermo Scientific™ Nalgene™ Amber Wide-Mouth Bottles, HDPE

Keep light-sensitive samples safe

- Reduce UV light transmission
- Meet USP requirements
- Leakproof, PP closures



**Buy More...Save More!**

- \$ 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Cap size	Catalog number	Qty/pk	Price/pk
30 (1)	28 mm	<a href="#">GH-06027-50</a>		
60 (2)	28 mm	<a href="#">GH-06027-52</a>		
125 (4)	38 mm	<a href="#">GH-06027-54</a>	12	
250 (8)	43 mm	<a href="#">GH-06027-56</a>		
500 (16)	53 mm	<a href="#">GH-06027-58</a>		
1000 (32)	63 mm	<a href="#">GH-06027-60</a>	6	

### Thermo Scientific™ Nalgene™ Economy Wide-Mouth Bottles, HDPE

Rugged design fits all your needs

- Leakproof, PP enclosure

**Buy More...Save More!**

- \$ 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity mL (oz)	Cap size	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/cs	Price/cs
30 (1)	28 mm	<a href="#">GH-06035-31</a>			<a href="#">GH-06035-33</a>		
60 (2)	28 mm	<a href="#">GH-06035-35</a>	12		<a href="#">GH-06035-37</a>	72	
125 (4)	38 mm	<a href="#">GH-06035-39</a>			<a href="#">GH-06035-41</a>		
250 (8)	43 mm	<a href="#">GH-06035-43</a>	12		<a href="#">GH-06035-45</a>	72	
500 (16)	53 mm	<a href="#">GH-06035-47</a>	6		<a href="#">GH-06035-49</a>	48	
1000 (32)	63 mm	<a href="#">GH-06035-51</a>	6		<a href="#">GH-06035-53</a>	24	

