

Bio-Simplex™ Carboys, PP

Don't compromise sterility—
completely autoclavable

- Eliminate contaminations—select C-Flex® or Sani-Tech® high-purity closures
- No more difficult transporting—handles on top and bottom make carrying easy
- No more leaks—EZ Top® closure provides leakproof top connections
- Chemical resistant polypropylene (PP) is BPA-free and can be heated to 275°F (135°C)

NEW



Buy More...Save More!

20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Liters (gallons)	Cap size	Spigot	Catalog number	Price/pk
10 (2.6)	83 mm	No	GH-62500-01	
		Yes	GH-62500-03	
20 (5.3)	120 mm	No	GH-62500-05	
		Yes	GH-62500-07	
40 (10.5)	120 mm	No	GH-62500-09	
		Yes	GH-62500-11	

High-Purity EZ Top® Container Closures

Fits carboy size	Material	No. of ports	Catalog number	Price
10 L (2.6 gal.)	C-Flex	2	GH-62500-47	
	Sani-Tech	3	GH-62500-53	
20 L (5.3 gal.)	C-Flex	2	GH-62500-49	
	Sani-Tech	3	GH-62500-55	
40 L (10.5 gal.)	C-Flex	2	GH-62500-51	
	Sani-Tech	3	GH-62500-57	

[GH-62500-41](#) Replacement EZ Top closed top cap, 83 mm. 2/pk

[GH-62500-43](#) Replacement EZ Top closed top cap, 120 mm. 2/pk

[GH-62500-45](#) Replacement spigot, fits all sizes. 2/pk

Bel-Art® HDPE Dispensing Jug with Handle, HDPE

Save space

- Maximize storage space with unique cube design
- Keep aqueous solutions close at hand with easy dispensing
- Know sample levels with molded-in graduations
- Threaded LDPE spigot features a 35-mm stem for easy dispensing

NEW



Buy More...Save More!

20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Liters (gallons)	Cap size	Catalog number	Price/pk
20 (5)	70 mm	GH-06034-00	

Thermo Scientific™ Nalgene™ FDA-Compliant Carboys, PP

Get a better grip with
two-handle construction

- Dispense solutions more quickly with optional spigot models—accept ¼", ½", or ⅝" ID tubing
- Leakproof polypropylene (PP) cap
- Autoclavable



Buy More...Save More!

20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Liters (gallons)	Cap size	Catalog number	Qty/pk	Price/pk
FDA-compliant carboys, USP Class VI				
10 (2½)	83B	GH-06063-12	1	
20 (5)	83B	GH-06063-22		
50 (13)	83B	GH-06063-32		
FDA-compliant carboys with spigot, USP Class VI				
10 (2½)	83B	GH-06064-50	1	
20 (5)	83B	GH-06064-60		
50 (13)	83B	GH-06064-70		

Cole-Parmer® Heavy-Walled Carboys, HDPE

Don't worry about
shipping!

- Resistant to most chemicals
- Effortless transport via heavy-duty swing handle

Narrow-Mouth Carboys come with rubber O-ring and HDPE closure with tag holes for identification. Available with or without leakproof spigot.

Wide-Mouth Carboys feature LDPE neck insert plug for maximum security.



Buy More...Save More!

20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Capacity L (gal.)	Cap size mm	Catalog number	Qty/pk	Price/pk
Narrow-mouth carboy				
5 (1¼)	46	GH-06035-93	1	
10 (2½)	55	GH-06035-95	1	
25 (6½)	55	GH-06035-97	1	
50 (13)	55	GH-06035-99	1	
Narrow-mouth carboys with spigot				
5 (1¼)	46	GH-06035-81	1	
10 (2½)	55	GH-06035-83	1	
25 (6½)	55	GH-06035-85	1	
50 (13)	55	GH-06035-87	1	
Wide-mouth carboys with neck insert				
5 (¼)	90	GH-06035-89	1	
10 (2½)	120	GH-06035-91	1	

[GH-06035-76](#) Replacement spigot