

## Thermo Scientific™ Nalgene™ Vacuum Desiccator, PC

### Won't shatter

- Easily view samples through transparent material
- No need to grease silicone O-ring
- Holds maximum vacuum of 28" Hg for 24 hours
- Order desiccator plate separately



#### Buy More...Save More!

**\$** 20% off on 120+  
15% off on 30 to 119  
10% off on 6 to 29 packs or cases

Plate dia (mm)	Total height (mm)	Clearance above plate (mm)	Qty/pk	Catalog number	Price/pk
230	330	195	1	<a href="#">GH-06520-05</a>	

[GH-06521-00](#) Desiccator plate; ceramic metal, 230 mm dia  
[GH-06520-06](#) Replacement stopcock

## Scienceware® Vacuum Desiccators, PP/PC

### No need for grease

- Maximize interior space with high crowned lid
- Control vacuum draw via stopcock, holds 29" Hg for 24 hours
- Includes perforated plate
- Room temperature use only—do not autoclave



#### Buy More...Save More!

**\$** 20% off on 120+  
15% off on 30 to 119  
10% off on 6 to 29 packs or cases

Plate dia (mm)	Total height (mm)	Clearance above plate (mm)	Qty/pk	Catalog number	Price/pk
140	206	122	1	<a href="#">GH-06514-10</a>	
190	260	157		<a href="#">GH-06514-20</a>	
230	311	198		<a href="#">GH-06514-30</a>	

## Secador® Techni-Dome® 360 Vacuum Desiccator, PC

### Store four times more than other desiccators

- Remains airtight even if not under pressure for extended period
- Holds maximum vacuum of 29" Hg at room temperature for 24 hours
- Maximize storage with two polypropylene sleeves, or remove for awkward items
- Halves nest inside each other for easy storage



Holding capacity	Inside dia	Total height	Catalog number	Price
65 L (4000 cu. in.)	20" (50.8 cm)	18" (45.7 cm)	<a href="#">GH-06514-50</a>	

[GH-06514-51](#) Vacuum pressure indicator. Plastic bellows type; no tools needed to install  
[GH-06514-52](#) Replacement stopcock

## PYREX® Vacuum Desiccators, Glass

### Pull more vacuum

- Holds maximum vacuum of 29.9" Hg
- No need for grease to create tight seal
- Order desiccator plate separately

**Warning:** Do not heat or subject to pressure.



Plate dia (mm)	Bowl capacity	Total height (mm)	Clearance above plate (mm)	Catalog number	Price
140	2400 mL	239	81	<a href="#">GH-34548-27</a>	
190	5800 mL	296	115	<a href="#">GH-34548-28</a>	
230	10,500 mL	344	120	<a href="#">GH-34548-29</a>	

[GH-06518-30](#) Desiccator plate; porcelain, 140 mm dia  
[GH-06518-40](#) Desiccator plate; porcelain, 190 mm dia  
[GH-06518-50](#) Desiccator plate; porcelain, 230 mm dia



## Can't choose?

Trust our **expert** Application Specialists to help you find the right product.

Jeevan, 25+ years of experience

Call: 800-323-4340 E-mail: [sales@coleparmer.com](mailto:sales@coleparmer.com) Chat live: [ColeParmer.com](http://ColeParmer.com)

Find even more online! Go to [ColeParmer.com](http://ColeParmer.com) to search more than 100,000 products.