

Scienceware® Lab Companion™ Round Vacuum Desiccators

Know your vacuum level via analog gauge

NEW

- Get vacuum results with Viton® three-way valve
- Maintain 29" Hg vacuum for over 72 hours at room temperature
- Maintain leakproof vacuum with silicone O-ring
- Keep lid secure with included locking ring



What's included: perforated plate or shelves, desiccant tray, analog vacuum gauge, and three-way valve.

| Chamber volume cu ft (L) | Interior height | Clearance above plate (mm) | Clear | | Amber | |
|--------------------------|-----------------|----------------------------|-----------------------------|-------|-----------------------------|-------|
| | | | Cat. no. | Price | Cat. no. | Price |
| 0.2 (6) | 8¾" | 165 | GH-08909-05 | | GH-08909-07 | |
| 0.4 (10) | 10¾" | 213 | GH-08909-09 | | GH-08909-11 | |
| 0.7 (20) | 13¾" | 254 | GH-08909-13 | | GH-08909-15 | |

Cole-Parmer® Desi-Vac™ Containers, PC

Easily remove air with built-in pump

- Get tight seal, maintains vacuum >200" H₂O
- Easily release vacuum via quick release button
- Ideal for airtight sample storage



Self-contained polycarbonate containers are ideal for drying, preserving, storing, and shipping samples. Built-in vacuum pump removes air via manual strokes. Rubber O-ring ensures a tight seal and maintains a vacuum of >200" H₂O (14.7" Hg) for over 24 hours. Quick-release button allows air back into unit to remove the lid.

| Volume | Dimensions (L x W x H) | Catalog number | Price |
|---------|----------------------------------------|-----------------------------|-------|
| 700 mL | 4¾" x 4½" dia (12.1 cm x 10.4 dia cm) | GH-06525-02 | |
| 1500 mL | 7½" x 4½" dia (18.1 cm x 10.4 dia cm) | GH-06525-06 | |
| 3000 mL | 8½" x 6½" x 7" (21.6 x 16.5 x 17.8 cm) | GH-06525-08 | |

Cole-Parmer® Desiccators, PP/PC
Secure, tight seal

- Neoprene O-ring provides tight seal—add grease for complete air tight storage
- Perforated plate holds samples above desiccant
- Chemical resistant body (PP), and polycarbonate cover



Desiccator has a chemical-resistant polypropylene (PP) body and polycarbonate (PC) cover. A neoprene O-ring offers a secure seal. Use grease on the flanges to make the unit completely airtight. Includes PP plate.



| Plate dia (mm) | Total height (mm) | Clearance above plate (mm) | Catalog number | Price |
|----------------|-------------------|----------------------------|-----------------------------|-------|
| 138 | 204 | 123 | GH-06525-22 | |
| 190 | 257 | 166 | GH-06525-24 | |
| 248 | 315 | 207 | GH-06525-26 | |

Static-Free Desiccators
Don't let static ruin equipment

- Withstands static build-up with stainless steel, neoprene, and glass construction with static dissipative film
- Prevent static discharge with grounding plug when humidity falls below 40%
- Maximize storage space with adjustable shelves



What's included: two shelves, pressure relief valve, and a grounding plug.

| Chamber volume | Dimensions (W x H x D) | | Catalog number | Price |
|----------------|-----------------------------------------------|---------------------------------------------|-----------------------------|-------|
| | Interior | Overall | | |
| 3.2 cu ft | 19½" x 9½" x 18⅞" (48.5 x 24.1 x 47.9 cm) | 21¾" x 12" x 21" (55.2 x 30.5 x 53.3 cm) | GH-24000-00 | |
| 6.4 cu ft | 19½" x 21½" x 18⅞" (48.5 x 54.6 x 47.9 cm) | 21¾" x 24" x 21" (55.2 x 61.0 x 53.3 cm) | GH-24000-10 | |

GH-24000-50 Replacement shelf. Fits both models; measures 19½"W x 18⅞"D (48.5 x 47.9 cm)

GH-07193-02 Mini-dehumidifier designed for static absorption of moisture in closed containers; measures 6½" x ½" dia (16.5 x 1.3 cm)

Wait!

There's More at [ColeParmer.com](#)

Browse 100,000+ products plus find **Technical Resources** to help you choose