

Stackable Acrylic Desiccators with Sliding Trays

No messy spills

- Deep trays keep samples secure
- No lubrication needed with airtight doors
- Use in refrigerators or freezers for temperature-sensitive samples

Models 08933-00 and -10 feature transparent acrylic walls for easy viewing of contents. Desiccators provide dry, dust-free storage to 100°F (38°C).

What's included: two extra-deep sample trays and a desiccant tray.


Models 08933-20 and -30 have all the features of the desiccators above plus a built-in thermohygrometer. Thermohygrometer has a temperature range of -58 to 158°F (-50 to 70°C) with a ±1.8°F accuracy up to 104°F (40°C) and a humidity range of 20 to 95% with a ±5% accuracy.

What's included: a thermohygrometer with LCD, two AAA alkaline batteries, two extra-deep sample trays, and a desiccant tray.

Dimensions (W x H x D)		Catalog number	Price	Replacement shelves	
Interior	Overall			Cat. no.	Price
Desiccators without thermohygrometer					
7" x 8½" x 10"	7½" x 9½" x 10½"	GH-08933-00		GH-08933-50	
9" x 10½" x 16"	9½" x 11½" x 17½"	GH-08933-10		GH-08933-60	
Desiccators with built-in thermohygrometer					
7" x 8½" x 10"	7½" x 9½" x 11½"	GH-08933-20		GH-08933-50	
9" x 10½" x 16"	9½" x 11" x 18½"	GH-08933-30		GH-08933-60	

[GH-09376-00](#) Replacement batteries, AAA. For thermohygrometer in models 08933-20 and -30. Pack of 12

[GH-17030-20](#) NIST-traceable calibration for thermohygrometers



Desiccator 08933-20 features a built-in digital thermohygrometer.

MicroLog RH/TempLog Data Logger

Keep track of temperature and humidity data for months with this RH/TempLog data logger! Logger holds up to 16,000 readings on selectable intervals. Built-in clock and calendar track your data in real time.



Description	Cat. no.	Price
RH/TempLog data logger	GH-35710-92	

Stackable Acrylic Desiccator Cabinets with Gas Ports

Create oxygen-free or inert gas atmosphere

- Keep humidity levels in check with built-in hygrometer
- Get full access to interior with fully removable door
- Protect light sensitive samples with amber-colored units
- Customize interior with adjustable shelves

These heavy-duty desiccators are made of ¼"-thick acrylic for durability. Resilient, closed-cell PVC gaskets prevent system leaks. Temperature range is 40 to 120°F (4 to 49°C). All models feature two gas ports—¼" hose barb inlet; ¼" hose barb outlet. Models 08900-54 thru -64 have a nonremovable divider separating the chamber into two separate cubicles.

Note: Not designed for vacuum use.

What's included: a hygrometer and shelves (models 08900-50 and -52 include two shelves; will hold five shelves. Other models include four shelves; will hold 10).

Cabinet color	Dimensions (W x H x D)		Catalog number	Price	Additional shelves	
	Interior	Overall			Cat. no.	Price
Clear	11½" x 11½" x 11½"	12" x 12" x 12"	GH-08900-50		GH-08900-80	
Amber	(29.2 x 29.2 x 29.2 cm)	(30.5 x 30.5 x 30.5 cm)	GH-08900-52		GH-08900-81	
Clear	11½" x 23½" x 11½"	12" x 24" x 12"	GH-08900-54		GH-08900-80	
Amber	(29.2 x 59.7 x 29.2 cm)	(30.5 x 61.0 x 30.5 cm)	GH-08900-56		GH-08900-81	
Clear	17½" x 17½" x 17½"	18" x 18" x 18"	GH-08900-58†		GH-08900-82	
Amber	(44.5 x 44.5 x 44.5 cm)	(45.7 x 45.7 x 45.7 cm)	GH-08900-60†		GH-08900-83	
Clear	23½" x 23½" x 17½"	24" x 24" x 18"	GH-08900-62†		GH-08900-84	
Amber	(59.7 x 59.7 x 44.5 cm)	(61.0 x 61.0 x 45.7 cm)	GH-08900-64†		GH-08900-85	

†Must be shipped motor freight.

[GH-06406-64](#) FEP tubing, ¼" ID. Pack of 25 feet

[GH-31501-40](#) Nylon pipe adapter connects tubing to inlet port.

⅛" NPT(F) x ⅛" tubing ID. Pack of 2

[GH-31501-41](#) Nylon pipe adapter connects tubing to outlet port and inlet tubing to regulator; ¼" NPT(F) x ⅛" tubing ID. Pack of 25



08900-52 Amber colored desiccators protect light-sensitive compounds from ultraviolet light.