

Cole-Parmer® Bottletop Dispensers

Get precise dispensing of even harsh chemicals

- Easy volume adjustments
- Have confidence in dispensed volumes—easy calibration and cleaning

Unique PTFE piston with integral O-ring provides smooth motion and high accuracy. All models feature a built-in 30-mm threaded screw top and include adapters for 28-, 32-, 36-, 40- and 45-mm bottles.

What's included: individual report of calibration and a calibration tool.



Specifications

Wetted materials: borosilicate glass, FEP and PTFE
Autoclavable: yes

Volume range	Scale divisions	Accuracy	Reproducibility	Bottle size (included)	Catalog number	Price
Bottletop dispensers only						
0.25 to 2.5 mL	0.05 mL	±0.6%	±0.2%	—	GH-25208-02	
0.5 to 5 mL	0.1 mL	±0.5%	±0.1%	—	GH-25208-04	
1 to 10 mL	0.2 mL	±0.5%	±0.1%	—	GH-25208-06	
2.5 to 30 mL	0.5 mL	±0.5%	±0.1%	—	GH-25208-08	
5 to 60 mL	1.0 mL	±0.5%	±0.1%	—	GH-25208-10	
Bottletop dispensers with plastic bottle						
1 to 10 mL	0.2 mL	±0.5%	±0.1%	250 mL	GH-25208-28	
2.5 to 30 mL	0.5 mL	±0.5%	±0.1%	500 mL	GH-25208-28	
5 to 60 mL	1.0 mL	±0.5%	±0.1%	1000 mL	GH-25208-32	
Bottletop dispensers with glass bottle						
0.25 to 2.5 mL	0.05 mL	±0.6%	±0.2%	100 mL	GH-25208-12	
0.5 to 5 mL	0.1 mL	±0.5%	±0.1%	100 mL	GH-25208-14	
1 to 10 mL	0.2 mL	±0.5%	±0.1%	250 mL	GH-25208-16	
2.5 to 30 mL	0.5 mL	±0.5%	±0.1%	500 mL	GH-25208-18	
5 to 60 mL	1.0 mL	±0.5%	±0.1%	1000 mL	GH-25208-22	
5 to 60 mL	1.0 mL	±0.5%	±0.1%	2000 mL	GH-25208-24	

KIMAX® Tilting Dispensers

Tilted head allows accurate measurements

Dispensers feature a fixed-volume dispensing head secured with a ⚙ joint. Flask tilts back to fill to desired volume, forward to dispense. Clamp is included.



Volume	Reservoir capacity	Joint size	Catalog number	Price
5 mL	250 mL	24/40	GH-07899-15	
10 mL	500 mL	24/40	GH-07899-20	
15 mL	500 mL	24/40	GH-07899-25	
20 mL	1000 mL	29/42	GH-07899-30	
25 mL	1000 mL	29/42	GH-07899-35	
30 mL	1000 mL	29/42	GH-07899-40	
40 mL	2000 mL	29/42	GH-07899-45	
50 mL	2000 mL	29/42	GH-07899-50	
60 mL	2000 mL	29/42	GH-07899-55	
100 mL	2000 mL	29/42	GH-07899-60	

Cole-Parmer® Chempette® Low-Profile Dispensers

Easily fill racks of vials with extension tube

- Set volume, pump, fill—it's that easy
- Precise dispensing each time—accurate to ±1.0%
- No waste—access port in cap for recycling reagent when priming

All models feature a durable, chemical-resistant bottle and PP funnel for easy reservoir filling without dispenser removal.



Specifications

Wetted materials: Pyrex® borosilicate glass, PTFE, and Tefzel® ETFE
Autoclavable: yes

Volume range	Scale divisions	Reproducibility	Bottle size (included)	Catalog number	Price
0.2 to 1 mL	0.05 mL	±1.0%	250 mL	GH-07916-10	
0.4 to 2 mL	0.1 mL	±1.0%	250 mL	GH-07916-20	
1 to 5 mL	0.1 mL	±1.0%	500 mL	GH-07916-30	
2 to 10 mL	0.25 mL	±1.0%	1000 mL	GH-07916-40	

Brinkmann® ChemSaver™ Dispensers

No more freezing of piston

- No residue left behind—PTFE seal displaces reagent in cylinder, eliminating swelling and crystallization
- No wasted reagent—safety valve channels reagent back during priming

Models 07932-00, -01, and -02 fit bottles with 33-mm screw tops and include adapters for 28-, 38-, and 45-mm bottles. Models 07932-03, -04, and -05 fit bottles with 45-mm screw tops and include adapters for 33- and 38-mm bottles.



Dispenser rotates 360°; positive-lock volume adjustment maintains setting.

Specifications

Wetted materials: borosilicate glass, PP, PTFE platinum-iridium, and ETFE
Autoclavable: yes

Volume range	Scale division	Accuracy	Reproducibility	Catalog number	Price
0.1 to 2.5 mL	0.05 mL	±0.6%		GH-07932-00	
1 to 5 mL	0.10 mL	±0.5%	≤0.1%	GH-07932-01	
2 to 10 mL	0.20 mL	±0.5%		GH-07932-02	
5 to 25 mL	0.50 mL	±0.5%		GH-07932-03	
10 to 50 mL	1.00 mL	±0.5%	≤0.1%	GH-07932-04	
20 to 100 mL	1.00 mL	±0.5%		GH-07932-05	