

PYREXPLUS® Brand 65340 Filtering Flasks

Put safety first—no more shattered glass

- Get longer life with protective PVC coating
- Resists thermal shock
- Easy tubing connection—10 mm OD on sizes to 1000 mL, 12.5 mm on 2000- and 4000-mL sizes
- Autoclavable



Protective PVC coating protects you and the glassware.

Buy More...Save More!

- 15%** off on 10+ packs or cases
- 10%** off on 5 to 9 packs or cases

Capacity (mL)	Stopper no.	Graduation range (mL)	Graduations (mL)	Catalog number	Qty/ cs	Price/ cs
250	6	75 to 250	25	GH-34577-21	6	
500	7	150 to 500	50	GH-34577-22	6	
1000	8	300 to 1000	50	GH-34577-23	6	
2000	9	600 to 2000	200	GH-34577-24	4	
4000	12	1500 to 4000	500	GH-34577-25	2	

[GH-06414-30](#) Tygon® vacuum tubing, 3/8" ID (for 10-mm tubing). 10 ft (3 m)

[GH-06414-40](#) Tygon vacuum tubing, 1/2" ID (for 12.5-mm tubing). 10 ft (3 m)

PYREX® Brand 5340 Filtering Flasks

Get maximum performance and durability

- Heavy-wall flasks have maximum mechanical strength
- Graduated for approximate measurements
- Use 10 mm OD tubing for flasks to 1000 mL; 12.5 mm OD for 2000- and 4000-mL sizes
- Case quantities also available



Buy More...Save More!

- 15%** off on 10+ packs or cases
- 10%** off on 5 to 9 packs or cases

Capacity	Stopper no.	Graduation range (mL)	Grad. (mL)	Catalog number	Qty/ pk	Price/ pk
250	6	75 to 250	25	GH-34557-01	6	
500	7	150 to 500	50	GH-34557-02	6	
1000	8	300 to 1000	50	GH-34557-03	6	
2000	9	600 to 2000	200	GH-34557-04	1	
4000	12	1500 to 4000	500	GH-34557-05	1	

[GH-06414-20](#) Tygon® vacuum tubing, 3/8" ID (for 10-mm tubing). 10 ft (3 m)

[GH-06414-30](#) Tygon vacuum tubing, 1/2" ID (for 12.5-mm tubing). 10 ft (3 m)

KimCote™ Safety-Coated Filtering Flasks

No more cleaning up broken glass

- Plastic coating keeps broken glass from going all over
- Side arm provides 1/4" connection for vacuum filtration
- Autoclavable to 120°C (250°F)



Capacity		Accepts stopper size	Hose connection	Catalog number	Qty/cs	Price/cs
mL	oz					
125	4	5	#2	GH-34524-49	1	
1000	32	8		GH-34524-51		
2000	64	8		GH-34524-53		
4000	128	8		GH-34524-55		

KIMAX® Filtering Flasks

Heavy wall for vacuum to 29" Hg

- Use in temperatures up to 840°F (450°C)
- Attach tubing with OD of 5/16" to 25- to 500-mL flasks; 3/8" OD on flasks 1000- to 4000-mL



Buy More...Save More!

- 15%** off on 10+ packs or cases
- 10%** off on 5 to 9 packs or cases

Capacity (mL)	Graduation range (mL)	Graduation (mL)	Stopper number	Catalog number	Qty/ cs	Price/ cs
25	5 to 25	5	3	GH-34524-30	18	
50	20 to 50	10	4	GH-34524-32	18	
125	50 to 125	25	5	GH-34524-34	18	
500	150 to 500	50	7	GH-34524-38	18	
1000	300 to 1000	50	8	GH-34524-40	12	
2000	600 to 2000	100	9	GH-34524-42	12	
4000	1500 to 4000	250	12	GH-34524-44	6	

[GH-06414-20](#) Tygon® vacuum tubing, 1/4" ID (6.5-mm tubing). 10 ft (3 m)

[GH-06414-30](#) Tygon vacuum tubing, 3/8" ID (10-mm tubing). 10 ft (3 m)