

KIMAX® Baffled Shaker Flasks

Don't struggle with clamps

- Baffles sides fit securely into shaker clamps
- Get better oxygen transfer and aeration of samples
- No graduations
- Compliance: ASTM E, Type I, Class I; Type II, Class I



Buy More...Save More!

- 15% off on 10+ packs or cases
- 10% off on 5 to 9 packs or cases

Capacity		Approximate neck OD	Base diameter	Catalog number	Qty/ cs	Price/ cs
mL	oz					
125	4	25 mm	66 mm	GH-34524-00	6	
250	8	38 mm	82 mm	GH-34524-02	6	
500	16	38 mm	102 mm	GH-34524-04	6	
1000	32	38 mm	128 mm	GH-34524-06	6	
2000	64	38 mm	161 mm	GH-34524-08	6	

Thermo Scientific™ Nalgene™ Volumetric Flasks, PP

Won't leak upon inverting

- Get better accuracy in dilutions—calibrated individually TC/TD at 20°C
- Feature no meniscus design
- 200-mL version has extra graduation at 203-mL for BOD and DO determinations
- Autoclavable



Buy More...Save More!

- 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

Capacity		Error limit	Qty/ pk	Catalog number	Price/ 1 pk
mL	oz				
50	1¾	±0.10 mL	1	GH-06108-10	
100	3	±0.16 mL		GH-06108-20	
200	7	±0.20 mL		GH-06108-30	
250	8	±0.24 mL	1	GH-06108-40	
500	16	±0.40 mL		GH-06108-50	
1000	32	±0.60 mL		GH-06108-60	

PYREX® Brand 5580 Volumetric Flasks

Easy and accurate dilutions—sharp line for precise volume

- Durable construction for repeated use
- Class A glassware
- Snap caps included on 10- to 2000-mL sizes



Buy More...Save More!

- 15% off on 10+ packs or cases
- 10% off on 5 to 9 packs or cases

Capacity (mL)	Tolerance (±mL)	Catalog number	Qty/ pk	Price/ pk	Catalog number	Qty/ cs	Price/ cs
1	0.01	GH-34560-01	6		GH-34560-21	12	
2	0.015	GH-34560-02	6		GH-34560-22	12	
10	0.02	—	—	—	GH-34560-27	12	
25	0.03	GH-34560-05	6		GH-34560-25	12	
50	0.05	GH-34560-06	6		GH-34560-26	12	
100	0.08	GH-34560-07	6		GH-34560-27	12	
200	0.10	GH-34560-08	6		GH-34560-28	12	
250	0.12	GH-34560-09	6		GH-34560-29	12	
500	0.20	GH-34560-10	6		GH-34560-30	12	
1000	0.30	GH-34560-11	1		GH-34560-31	6	
2000	0.50	GH-34560-12	1		GH-34560-32	4	

PYREX® Brand 5640 Volumetric Flasks

Get accurate dilutions

- Sharp, permanent graduation makes for easier diluting
- Durable, Class A design for longer life
- Easy-to-read white inscriptions
- More sizes and case quantities available



Buy More...Save More!

- 15% off on 10+ packs or cases
- 10% off on 5 to 9 packs or cases

Capacity mL	Tolerance (±mL)	Stopper no.	Catalog number	Qty/ pk	Price/ pk
25	0.03	9	GH-34505-05	6	
50	0.05	9	GH-34505-06	6	
100	0.08	13	GH-34505-07	6	
200	0.10	13	GH-34505-08	6	
250	0.12	16	GH-34505-09	6	
500	0.20	19	GH-34505-10	6	
1000	0.30	22	GH-34505-11	1	
2000	0.50	27	GH-34505-12	1	

DON'T RISK IT!

Our chemical compatibility database provides important information on chemical resistance—check it out at ColeParmer.com/ChemChart

