

Cryo-Glove® Cryogenic Gloves

Keep hands from freezing

- Protect as low as –256°F (–160°C)
- Maximum protection while remaining flexible

Water-Resistant Gloves provide protection in closed systems. A stay-dry lining keeps you warm and comfortable. **Waterproof Gloves** have a nylon exterior and a seamless waterproof lining. Gloves keep you dry and wick moisture away from your hands. **Cryo-Industrial® Gloves** feature a rugged, abrasion-resistant outer shell that protects the glove and provides an excellent grip for heavy-duty applications. Waterproof liner protects against cryogenic splashes while the inner lining wicks moisture from your hands for enhanced comfort.

Note: Do not immerse gloves in liquid nitrogen.



Description	Size	Length	Catalog number	Price per pair
Water-resistant Cryo-Glove gloves				
Wrist	Medium	12" (30 cm)	GH-09113-02	
	Large		GH-09113-04	
Mid-arm	Medium	15" (38 cm)	GH-09113-12	
	Large		GH-09113-14	
	X-large		GH-09113-16	
Elbow	Medium	19" (48 cm)	GH-09113-22	
	Large		GH-09113-24	
	X-large		GH-09113-26	
Waterproof Cryo-Glove gloves				
Mid-arm	Medium	15" (38 cm)	GH-09113-30	
	Large		GH-09113-32	
	X-large		GH-09113-34	
Elbow	Medium	19" (48 cm)	GH-09113-35	
	Large		GH-09113-37	
	X-large		GH-09113-39	
Cryo-Industrial heavy-duty gloves				
Mid-arm	Medium	15" (38 cm)	GH-09113-62	
	Large		GH-09113-64	
	X-large		GH-09113-66	

North® Drybox Gloves

Protect your entire arm

- Shoulder-length, seamless protection

Neoprene Gloves feature high tensile strength and flexibility for work that requires high sensitivity and good dexterity.

Hypalon® Gloves offer outstanding abrasion protection and resistance to ozone or oxidizing chemicals. Natural softness improves worker comfort.

Butyl Gloves allow highest impermeability to water, vapors and gases. They maintain flexibility even at low temperatures and are resistant to oxygenated solvents and most oxidizing chemicals.



Material	Size	Length	Thickness	Catalog number	Price per pair
Neoprene	9¾	32" (81 cm)	15 mil	GH-86569-00	
			30 mil	GH-86569-02	
Hypalon	9¾	32" (81 cm)	15 mil	GH-86569-10	
			30 mil	GH-86569-12	
Butyl	9¾	32" (81 cm)	15 mil	GH-86569-20	
			30 mil	GH-86569-22	

Salisbury® Insulating Rubber Glove Kits

Don't compromise safety when working with electrical power

- Includes everything you need—insulating rubber gloves, appropriate leather protector, and storage bag
- Protect gloves from cuts, abrasions, and punctures with included leather protector

Tip: In accordance with NFPA 70E, anything over 50 volts requires insulating rubber gloves.



Kits include leather protector, storage bag and insulating rubber gloves



Class	Length	Max use voltage AC / DC	Size	Red gloves		Black gloves		Yellow gloves	
				Catalog number	Price	Catalog number	Price	Catalog number	Price
00	11" (279 mm)	500 / 750	8	GH-86435-00		GH-86435-05		—	—
00	11" (279 mm)	500 / 750	9	GH-86435-01		GH-86435-06		—	—
00	11" (279 mm)	500 / 750	10	GH-86435-02		GH-86435-07		—	—
00	11" (279 mm)	500 / 750	11	GH-86435-03		GH-86435-08		—	—
00	11" (279 mm)	500 / 750	12	GH-86435-04		GH-86435-09		—	—
0	11" (279 mm)	1000 / 1500	8	GH-86435-10		GH-86435-15		GH-86435-20	
0	11" (279 mm)	1000 / 1500	9	GH-86435-11		GH-86435-16		GH-86435-21	
0	11" (279 mm)	1000 / 1500	10	GH-86435-12		GH-86435-17		GH-86435-22	
0	11" (279 mm)	1000 / 1500	11	GH-86435-13		GH-86435-18		GH-86435-23	
0	11" (279 mm)	1000 / 1500	12	GH-86435-14		GH-86435-19		GH-86435-24	
2	14" (356 mm)	17,000 / 25,500	8	—	—	GH-86435-25		—	—
2	14" (356 mm)	17,000 / 25,500	9	—	—	GH-86435-26		—	—
2	14" (356 mm)	17,000 / 25,500	10	—	—	GH-86435-27		—	—
2	14" (356 mm)	17,000 / 25,500	11	—	—	GH-86435-28		—	—
2	14" (356 mm)	17,000 / 25,500	12	—	—	GH-86435-29		—	—