

## HDPE Tote Boxes

### Stackable to maximize storage space

- Contain leaks and spills
- Lockable with cable ties
- Nest inside each other for easy storing when not in use



Capacity (cu ft)	Dimensions (L x W x H)	Catalog number	Price	Optional lids	
				Cat. no.	Price
0.5	16" x 10" x 5 $\frac{7}{8}$ "	<a href="#">GH-06810-60</a>		<a href="#">GH-06810-65</a>	
1.2	17" x 14 $\frac{1}{2}$ " x 9 $\frac{1}{8}$ "	<a href="#">GH-06810-70</a>		<a href="#">GH-06810-75</a>	
2.6	20 $\frac{7}{8}$ " x 18 $\frac{1}{8}$ " x 12 $\frac{7}{8}$ "	<a href="#">GH-06810-80</a>		<a href="#">GH-06810-85</a>	
3.7	26 $\frac{5}{8}$ " x 18 $\frac{1}{4}$ " x 14 $\frac{7}{8}$ "	<a href="#">GH-06810-90</a>		<a href="#">GH-06810-95</a>	

## Stackable Tip-Out Bins

### Customizable to your needs

- See contents at a glance with clear plastic construction
- Easily access items with 45° angle opening
- Clean by lifting bins out of housing

Units are uniform in width for easy stacking.



Number of bins	Bin interior (W x H x D)	Overall dimensions (W x H x D)	Catalog number	Price
6	3 $\frac{1}{2}$ " x 3 $\frac{3}{4}$ " x 2 $\frac{5}{8}$ "	23 $\frac{5}{8}$ " x 4 $\frac{1}{2}$ " x 3 $\frac{5}{8}$ "	<a href="#">GH-47110-02</a>	
5	4 $\frac{1}{4}$ " x 5 $\frac{3}{4}$ " x 3 $\frac{3}{4}$ "	23 $\frac{5}{8}$ " x 6 $\frac{1}{2}$ " x 5 $\frac{1}{4}$ "	<a href="#">GH-47110-04</a>	
4	5 $\frac{5}{8}$ " x 7 $\frac{1}{2}$ " x 5"	23 $\frac{5}{8}$ " x 8 $\frac{1}{8}$ " x 6 $\frac{5}{8}$ "	<a href="#">GH-47110-06</a>	
3	7 $\frac{7}{8}$ " x 8 $\frac{5}{8}$ " x 5 $\frac{7}{8}$ "	23 $\frac{5}{8}$ " x 9 $\frac{1}{2}$ " x 7 $\frac{3}{4}$ "	<a href="#">GH-47110-08</a>	
2	11 $\frac{3}{16}$ " x 13 $\frac{5}{8}$ " x 8 $\frac{7}{8}$ "	23 $\frac{5}{8}$ " x 13 $\frac{7}{8}$ " x 11 $\frac{3}{4}$ "	<a href="#">GH-47110-10</a>	

## Visual Laboratory Storage Cabinets

### Easily view contents

- Lockable for added security
- Wall-mounted cabinet includes wall brackets



Floor cabinet  
47546-62

Description	Size (W x H x D)	Shpg wt		Catalog number	Price
		lb	kg		
Floor	36" x 78" x 24"	176	80	<a href="#">GH-47546-62</a>	
Wall-mount	30" x 26" x 12"	48	22	<a href="#">GH-47546-64</a>	

## Polypropylene Storage Bins and Racks

### Design your own system

- Easily stack on existing shelves or optional racks

### Polypropylene Storage Bins

- Virtually unbreakable with wide-lip stacking ledges

Outer dimensions (W x H x D)	Catalog number	Qty/ pk	Price/ pk	Catalog number	Qty/ pk	Price/ pk
4 $\frac{1}{8}$ " x 3" x 5 $\frac{3}{8}$ "	<a href="#">GH-06811-14</a>	1		<a href="#">GH-06811-12</a>	24	
4 $\frac{1}{8}$ " x 3" x 7 $\frac{3}{8}$ "	<a href="#">GH-06811-24</a>	1		<a href="#">GH-06811-22</a>	24	
5 $\frac{1}{2}$ " x 5" x 10 $\frac{7}{8}$ "	<a href="#">GH-06811-26</a>	1		<a href="#">GH-06811-32</a>	12	
11" x 5" x 10 $\frac{7}{8}$ "	<a href="#">GH-06811-28</a>	1		<a href="#">GH-06811-34</a>	6	
8 $\frac{1}{4}$ " x 7" x 10 $\frac{3}{4}$ "	<a href="#">GH-06811-38</a>	1		<a href="#">GH-06811-36</a>	6	
8 $\frac{1}{4}$ " x 7" x 14 $\frac{3}{4}$ "	<a href="#">GH-06811-44</a>	1		<a href="#">GH-06811-42</a>	12	
16 $\frac{1}{2}$ " x 7" x 14 $\frac{3}{4}$ "	<a href="#">GH-06811-56</a>	1		<a href="#">GH-06811-50</a>	6	
8 $\frac{1}{4}$ " x 9" x 18"	<a href="#">GH-06811-58</a>	1		<a href="#">GH-06811-52</a>	6	
16 $\frac{1}{2}$ " x 11" x 18"	<a href="#">GH-06811-62</a>	1		<a href="#">GH-06811-54</a>	3	

### Optional Racks

Organize bins for easy access—one bin slides out easily without disturbing adjacent bins. Choose from three types:

**A. Benchtop Rack** (model 06811-02) accepts bins on one side of rack. Wide-base design keeps rack upright without mounting. Rack is made of 16-gauge steel with baked-enamel finish.

**B. Floor-Standing Racks** (models 06811-70 and -80) accept bins on both sides for double-sided access. Racks are made of heavy-duty steel with baked-enamel finish. Order optional casters separately below.

**C. Wall-Mount Rack** (model 06811-06 not shown) has slotted mounting holes ( $\frac{3}{4}$ " L x  $\frac{3}{8}$ " W on 6" centers). Made of 16-gauge steel with baked-enamel finish.



**A.** Benchtop rack 06811-02 (bins sold separately)



**B.** Floor rack 06811-70 holds bins on both sides (bins sold separately).

Key	Rack capacity		Dimensions (W x H x D)	Catalog number	Price
	Qty	Bin model no.			
<b>A.</b>	24	06811-12, -22	27 $\frac{3}{4}$ " x 21" x 8"	<a href="#">GH-06811-02</a>	
	12	06811-32			
<b>B.</b>	192	06811-12, -22	36" x 53" x 20"	<a href="#">GH-06811-70</a>	
	48	06811-36, -42			
<b>B.</b>	24	06811-50	36" x 53" x 20"	<a href="#">GH-06811-80</a>	
	96	06811-32			
<b>C.</b>	48	06811-34	35 $\frac{3}{4}$ " x 19" x 1 $\frac{1}{4}$ "	<a href="#">GH-06811-06</a>	
	32	06811-12, -22			
	18	06811-32			
	8	06811-36, -42			
	4	06811-50			

[GH-06811-90](#) Caster set for "B" floor-standing racks; includes four casters and handle