

IKA® RW 20 Digital Dual-Range Mixer

No separate components to purchase—complete system is ready to go!

- No downtime—maintenance-free motor for continuous duty
- Fulfill all your lab mixing needs—two speed ranges for a variety of applications
- No need to move mixer head to reposition propeller—through-shaft design for easy movement
- No difficult controls—easy-to-use knob and LED display for accurate setting

Use this versatile, affordable mixer for liquid volumes up to 5 gallons (18.9 liters) and viscosities up to 10,000 cps (approximately the viscosity of honey). Select speed from 60 to 2000 rpm in two ranges for a variety of applications.

What's included: chuck (accepts up to 3/8" [10 mm] dia shafts), 6 1/4"L x 1/2" dia (159 mm L x 10 mm dia) mounting rod, four-blade propeller mixer stand, and clamp.



Complete system includes propeller, clamp, and stand



Four-Blade Propeller
Yours free!

Boss Head Clamp
Yours free!

Plate Stand
Yours free!



Speed (rpm)	hp	Max torque (in-oz)	Power (VAC, Hz)	Catalog number	Price
60 to 500/ 240 to 2000	1/25	259	115, 50/60 230, 50/60	GH-50705-00 GH-50705-10	

IKA® EUROSTAR Digital Mixers

Mix viscous samples up to 30,000 cps

- Speed won't change even as viscosity changes
- Won't overheat—thermal overload shut-off for safety
- Maintenance-free design for continuous duty

EUROSTAR 20 Digital Mixer handles volumes up to 4 gallons (15 liters) and viscosities up to 10,000 cps.

EUROSTAR 40 Digital Mixer will mix volumes up to 6.6 gallons (25 liters) and viscosities up to 30,000 cps.

What's included: chuck (accepts up to 3/8" [10 mm] dia shaft) and 6 1/4"L x 1/2" dia (159 mm x 13 mm) mounting rod.



Speed (rpm)	hp	Max torque (in-oz)	Power (VAC, Hz)	Catalog number	Price
Eurostar 20 digital mixer					
30 to 2000	1/16	28.3	115, 50/60 230, 50/60	GH-50702-30 GH-50702-35	
Eurostar 40 digital mixer					
30 to 2000	1/8	56.6	115, 50/60 230, 50/60	GH-50702-40 GH-50702-45	

IKA® EUROSTAR Digital Constant-Speed Mixers

Speed won't change even as viscosity does

- Automatic adjustment to desired speed with unique continuous speed comparison
- No need to move mixer head to remove samples—through-shaft design for impeller adjustments
- Worry-free operation—maintenance-free motor with overload protection
- Handle even large samples—up to 26.4 gallons (100 liters)

EUROSTAR 60 Digital Mixer (50704-20 and -25) handles volumes up to 10.6 gallons (40 liters) and viscosities up to 50,000 cps.

EUROSTAR 100 Digital Mixer (50704-30 and -35) will mix volumes up to 26.4 gallons (100 liters) and viscosities up to 70,000 cps.

What's included: chuck (accepts up to 3/8" [10 mm] dia shaft) and 6 1/4"L x 1/2" dia (159 mm x 13 mm) mounting rod.



Speed (rpm)	hp	Max torque (in-oz)	Power (VAC, Hz)	Catalog number	Price
Eurostar 60 digital mixer					
30 to 2000	3/16	85	115, 50/60 230, 50/60	GH-50704-20 GH-50704-25	
Eurostar 100 digital mixer					
30 to 1300	1/5	142	115, 50/60 230, 50/60	GH-50704-30 GH-50704-35	