

Thermo Scientific™ Nalgene™ Lab Notebooks

Keep accurate records for easy recall

Laboratory notebooks feature numbered pages printed with either a green grid or green horizontal lines; additional pages include issuance page, instructions for keeping research records, and table of contents. Numbered pages have spaces for signatures and dates.

Choose either Polypaper or conventional paper. Uncoated Polypaper is highly resistant to moisture, chemicals, tearing, and aging; works best with ballpoint pen or felt-tip marker.

Buy More...Save More!
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Format	Page size	No. of pages†	Cover color	Catalog number	Qty/pk	Price/pk
Notebook with uncoated Polypaper, case bound in a hard waterproof cover						
1/4-inch grid	9 1/4" x 11 1/4" (235 x 286 mm)	100	Black	GH-06551-00	1	
Notebook with conventional paper, case bound in a hard waterproof cover						
1/4-inch grid	8 1/2" x 11" (216 x 279 mm)	100	Green	GH-06553-00	1	
3 lines/inch	8 1/2" x 11" (216 x 279 mm)	100	Burgundy	GH-06556-00	1	
5-mm grid	A4 (210 x 297 mm)	100	Green	GH-06553-10	1	
Notebook with conventional paper, permanently bound in a lightweight spill-resistant cover						
1/4-inch grid	8 1/2" x 11" (216 x 279 mm)	184	Burgundy	GH-06553-05	1	

†Quantity of numbered pages only.



Rite in the Rain® All-Weather Writing Paper

Write in all weather conditions

- Repels water so you can still take notes

Bound Books

- Durable, polydura covers with 156 numbered, 4 3/4" x 7 1/2" pages
- Meets US EPA guidelines



Description	Catalog number	Price
Environmental	GH-06570-00	
Horizontal line	GH-06570-04	

Maxi-Spiral Notebooks

- Sturdy, polydura cover with spiral binding
- Contain 42 sheets of 8 1/2" x 11" of paper



Description	Catalog number	Price
Field pattern	GH-06570-30	
Horizontal line	GH-06570-32	

Copier Paper

- Create your own charts, maps, or worksheets on all-weather paper
- Not for use with ink jet printers



Description	Catalog number	Qty/pk	Price
White, 8 1/2" x 11" (216 x 279 mm)	GH-06570-24	200	

Cole-Parmer® Lab Markers

Won't bleed

- Write on cold, wet surfaces
- Permanent on plastic; washes off glass, metal, and porcelain



Buy More...Save More!
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Color	Catalog number	Qty/pk	Price/pk
Black	GH-09964-00	10	
Blue	GH-09964-10	10	
Green	GH-09964-15	10	
Red	GH-09964-20	10	

Permanent Paint Markers

Will not dry out

- Unique tip design eliminates drying out
- Writes on any surface



Color	Catalog number	Qty/pk	Price/pk
Blue	GH-09964-60	12	
Black	GH-09964-61		
White	GH-09964-62		
Yellow	GH-09964-63	12	
Orange	GH-09964-64		
Red	GH-09964-65		
Green	GH-09964-66		

Sharpie® Industrial Markers

Resists most chemicals, steam, and heat

- Permanent black ink
- Stands heat up to 500°F (260°C)



Tip	Catalog number	Qty/pk	Price/pk
Fine	GH-09969-00	12	
Extra fine	GH-09969-10		