

## Cole-Parmer® StableTemp™ Economical Gravity Convection Ovens

Save money while getting the features you need

- Durable powder-coated cold-rolled steel exterior
- Double-wall aluminum interior with 1"-thick (2.5 cm) silica-based insulation

These economical gravity convection ovens are designed for the budget-conscious laboratory needing to perform basic drying and baking applications. Temperature is controlled via a bimetallic thermostat from ambient  $\pm 5$  to 210°C. All models feature a pilot light to indicate when the oven is in operation and a preset high temperature limit safety thermostat.

**What's included:** two adjustable chrome-plated wire shelves, one fixed shelf. The 120 VAC model has a three-wire cord and plug; the 230 VAC model has a three-wire cord only.



StableTemp



### Specifications

**Temperature range:** ambient  $\pm 5^\circ\text{C}$  to 210°C  
**Temperature accuracy:**  $\pm 9^\circ\text{C}$  at 100°C

**Temperature display:** glass thermometer (not included)

Capacity, cu ft (L)	Shelf positions	Dimensions (W x H x D), in. (cm)		Shpg wt lb (kg)	120 VAC, 60 Hz		230 VAC, 50/60 Hz	
		Chamber	Overall		Catalog number	Price	Catalog number	Price
1.7 (48.1)	3	16 x 16¼ x 11½ (41 x 41 x 29)	18½ x 22½ x 13½ (47 x 57 x 34)	57 (26)	<a href="#">GH-52120-02</a>		<a href="#">GH-52120-03</a>	

[GH-52100-50](#) Replacement shelf for ovens 52120-02 and -03

[GH-17002-30](#) NIST-traceable calibration with data for ovens

## Thermo Scientific™ Precision™ Gravity Convection Oven

Get gentle drying with low turbulence

- Ideal for general drying applications from ambient  $\pm 5^\circ\text{C}$  to 210°C
- Conserve benchspace with small footprint
- Eliminate overtemperature situations with pre-set high temperature safety

Oven features double-wall aluminum interior chamber with 1" (2.5 cm) silica-based insulation and powder-coated, cold-rolled steel exterior.



Capacity, cu ft (L)	Temperature range	Temperature uniformity	Resolution	Shelf positions	Dimensions (W x H x D), in. (cm)		Power (VAC, Hz)	Shpg wt lb (kg)	Catalog number	Price
					Chamber	Overall				
1.7 (48.1)	Ambient $\pm 5$ to 210°C	$\pm 5^\circ\text{C}$ at 100°C	0.5°C	7	16 x 16¼ x 11½ (41 x 41 x 29)	18½ x 22½ x 13½ (47 x 57 x 34)	120, 60 240, 50/60	57 (26)	<a href="#">GH-05014-03</a> <a href="#">GH-05014-04</a>	

[GH-17002-30](#) NIST-traceable calibration with data for ovens

**Wait!**

There's More at [ColeParmer.com](http://ColeParmer.com)

Browse **100,000+** products plus find **Technical Resources** to help you choose