

YSI® Professional Series DO Meters

Configurable to your needs

- Combine meter, probes, and cable lengths to meet your needs
- Handheld meters offer menu-driven software for added convenience
- Read your measurements easily in any light with backlit graphic display and keypad

The YSI Professional series provides plug-and-play capabilities to give you a meter with as much functionality as needed. Don't buy unnecessary accessories, simply build your own system by ordering the meter, probe(s), and cables(s) you need.

Easy-to-use meters feature graphic display with detailed messages and instructions that translate to less time reading manuals. Display and keypad are backlit, making them ideal for low-light situations. Rugged rubber over-molded case protects meters during use. Meters are IP67 rated and waterproof, even without the battery lid.

These DO meters accept either classic polarographic or "instant-on" galvanic DO sensors with screw-on membrane caps for ease of maintenance. These meters also feature selectable two-point DO calibration and automatic barometric compensation for greater accuracy.

NEW
Model



**REQUIRED
System Components**

- 1) Meter
- 2) Probe(s)
- 3) Cable(s)



Pro2030
meter

ISO9001:2008
CERTIFIED SUPPLIER

IP
67

3
METER ONLY

1. YSI Professional Series Meters

Model	Pro20	Pro1020	Pro2030	
Catalog number	GH-59352-04	GH-59352-10	GH-59352-14	
Range	Dissolved oxygen	0 to 50 mg/L		
	Barometric pressure	Automatic correction, 500 to 800 mm Hg		
	pH	—	0 to 14.00 pH	—
	mV	—	±1999 mV	—
	Conductivity	—	—	0 to 200 mS
	TDS	—	—	0 to 100 g/L
	Salinity	Manual input, automatic correction	—	0 to 70 ppt
	Temperature	–5 to 55°C		
Accuracy	Dissolved oxygen	±2% of reading or ±0.2 mg/L, whichever is greater (6% above 20 mg/L)		
	Barometric pressure	±3 mm Hg within 15°C from calibration point		
	pH	—	±0.2 pH	—
	mV	—	±20 mV	—
	Conductivity	—	—	±0.5% of reading or ±0.001 mS/cm, whichever is greater
	TDS	—	—	±1% of reading
	Salinity	—	—	±1% of reading or ±0.1 ppt, whichever is greater
	Temperature	±0.2		
Temperature compensation	Automatic, –5 to 55°C			
Display	Four-line backlit, graphic LCD			
Power	Two C batteries (included)			
Dimensions (L x W x H)	8½" x 3¼" x 2¼" (21.6 x 8.3 x 5.7 cm)			
Price				

2. DO Probes for Professional Series

Description	Catalog number	Price
Galvanic DO	GH-59352-32	
Polarographic DO	GH-59352-34	
BOD probe	GH-59352-35	
pH probe	GH-59352-20	
ORP probe	GH-59352-22	

Accessories

[GH-99852-80 DO membrane kit](#); polyethylene, 1.25 mil. Pack of 6

[GH-05519-61 DO membrane kit](#); PTFE, 1.0 mil. Pack of 6

3. Cables for YSI Professional Series

All cables include a temperature probe. Cables for Pro2030 meters also include a conductivity probe.

Compatible with meter	Pro20		Pro1020		Pro2030	
	Catalog number	Price	Catalog number	Price	Catalog number	Price
Cable length						
3 ft (1 m)	GH-59352-43		GH-59352-63		GH-59352-79	
13 ft (4 m)	GH-59352-44		GH-59352-64		GH-59352-80	
33 ft (10 m)	GH-59352-46		GH-59352-66		GH-59352-82	

Note: Additional cable lengths available at ColeParmer.com.