

NEW

Oakton® Waterproof pH 150 Meter

Get more for your money!

- Intuitive, user-friendly icons show electrode status as pH slope
- Get quick and easy electrode attachment to a beaker or container with Grip-Clip™ holder
- Recall more data with expanded data logging for up to 150 data sets
- mV offset for calibration of ORP standards, zeroing mV value, and pH diagnostics
- Use as a benchtop meter as well—built-in stand or wall-mount option



View more simultaneously with large, three-line LCD providing pH or mV measurement with temperature and calibration % slope. Get faster calibration with auto buffer recognition which identifies the correct pH buffer. Be more accurate with up to six calibration points from USA, NIST, and DIN pH buffer sets and automatic temperature compensation (ATC) for accuracy even in fluctuating temperatures. Select temperature readout from °C or °F to suit your application.

Additional features include ready (stability) indicator, smart averaging, hold function, calibration alarm (visible), battery-life indicator, and electrode status.

Meter only includes: Grip-Clip holder and two AA batteries.

Meter with probe adds: "All-in-One" pH electrode (35808-71).

Meter kit further adds: pH buffers, storage solution, rinse solution, and hard carrying case.

OAKTON®

ISO9001:2008
CERTIFIED SUPPLIER

TUV GS

CE

IP 67

Meter only

Description		Meter only	Meter with probe	Meter kit
Model		pH 150		
Catalog number		GH-35614-32	GH-35614-30	GH-35614-90
Precalibrated catalog number		GH-35614-34	GH-35614-33	GH-35614-91
Range	pH	-2.00 to 16.00		
	mV	±2000 mV		
	Temperature	-17.0° to 230.0° F (-10.0° to 110.0°C)		
Resolution	pH	0.01		
	mV	0.1 mV ±999.9 mV; 1 mV beyond		
	Temperature	0.1°F/C		
Accuracy	pH	±0.01		
	mV	±0.2 mV ±2 LSD or ±0.5% of reading; whichever is greater		
	Temperature	±0.9°F (±0.5°C)		
Calibration	pH	Up to 6 points: USA, NIST, DIN		
	mV	±200 mV		
	Temperature	Offset 0.1 increments		
Temperature compensation		Automatic or manual from -10 to 110°C		
Data logging		Stores up to 150 data sets		
Power		Two AA batteries (included); universal power adapter (optional)		
Price				
Precalibrated price				



Mount to wall to save valuable bench space

Accessories

[GH-35808-71](#) Replacement "All-in-One" combination pH electrode with built-in ATC; single-junction, epoxy body, BNC connector

[GH-35618-05](#) ATC probe. Use with any standard pH electrode for temperature compensation

[GH-35614-50](#) Replacement Grip-Clip, holder attaches probe to side of container for hands-free measurement

[GH-35614-51](#) Hard carrying case, for 150/450 meters

[GH-35420-72](#) Optional power adapter, 110/220 VAC

[GH-09376-01](#) Replacement batteries, AA. Pack of 4

[GH-17106-20](#) NIST-traceable calibration with data for pH meter

Wait!

There's More at
ColeParmer.com

Browse **100,000+** products plus find
Technical Resources to help you choose