

BrandTech accu-jet® pro Pipette Controllers

Get more control, more comfort, and power

- No more over aspiration—adjustable speed limiter prevents over discharging
- Minimize cell pellet disruption with soft blow-out control
- Ergonomic design fits all hand sizes
- Longer pipette lasts eight hours on a single charge

Pipette controllers feature pressure-sensitive buttons for accurate control with 0.1- to 100-mL pipettes. Long-life NiMH battery provides up to eight hours of full speed operation on a four-hour charge. LED indicator alerts you when two hours of pipetting time remain. Don't worry about downtime—the accu-jet pro is fully functional during recharging.

What's included: rechargeable 9 V NiMH battery, 120 VAC power supply/charger, wall holder, and two sterile 0.2-µm hydrophobic filters.



Accessories

- [GH-25210-08](#) Replacement filters, 0.2-µm sterile. Pack of 10
- [GH-25210-10](#) Replacement filters, 0.2-µm non-sterile. Pack of 10
- [GH-25210-09](#) Replacement silicone adapter with PTFE check valve
- [GH-25210-11](#) Wall holder
- [GH-25210-12](#) Snap tape set for wall holder, 12 x 65 mm
- [GH-25210-15](#) Replacement battery charger; 120 VAC, 60 Hz
- [GH-25210-14](#) Replacement battery charger; 230 VAC, 50 Hz
- [GH-25210-16](#) Replacement NiMH battery

Specifications

Pipetting rate: 5 mL/sec
No. of speeds: adjustable via thumbwheel
Memory: no
Autoclavability: silicone adapter

Color	120 VAC, 60 Hz		230 VAC, 50 Hz	
	Catalog number	Price	Catalog number	Price
Dark blue	GH-25210-04		GH-25210-00	
Magenta	GH-25210-05		GH-25210-01	
Green	GH-25210-06		GH-25210-02	
Royal blue	GH-25210-07		GH-25210-03	

Omega™ Pipette Controllers

Don't be surprised by dead batteries again

- LED display indicates battery charge status
- Contoured buttons ensure comfort during pipetting
- Quick and quiet pump fills a 10-mL pipette in 1.3 seconds
- Accepts glass or plastic serological pipettes, from 1 to 100 mL
- Continue pipetting while connected to the charger or adapter

These compact pipette controllers feature an ergonomic rounded design for comfortable hand fit and light-action button springs for minimal activation pressure. The UV-resistant plastic housing is lightly textured to ensure a slip-resistant grip. Five-bar LED battery charge indicator lights up during use; each bar represents 20% of the rechargeable lithium batteries charge capacity.

What's included: one 0.45 µm sterile filter, pipette wall mount, spare I.D. labels, rechargeable lithium ion battery, AC adapter, and pocket knife.



Battery charge LED indicator



Specifications

Pipetting rate: 7.7 mL/sec
No. of speeds: adjustable via thumb dial
Memory: no
Autoclavability: nosepiece, filter, adapter, wall mount
Power: rechargeable lithium battery with 115 VAC, 60 Hz adapter

Housing color	Catalog number	Price
Blue	GH-25200-91	
Clear	GH-25200-92	
Purple	GH-25200-93	
Gray	GH-25200-94	
Green	GH-25200-95	
Red	GH-25200-96	

Accessories

- [GH-25200-66](#) Replacement filters; sterile, 0.45 µm. Pack of 10
- [GH-25200-67](#) Replacement filters; nonsterile, 0.45 µm. Pack of 10
- [GH-25200-68](#) Silicone pipettor mount for pipette sizes 0.1 to 50 mL
- [GH-25200-69](#) Rubber filter interface
- [GH-25200-97](#) Battery charger
- [GH-25200-98](#) Replacement nose-piece, red
- [GH-25200-99](#) Replacement nose-piece, gray