

MLA™ D-Tipper™ Fixed-Volume Pipettes

Stop manual tip removal

- Built-in tip ejector eliminates manual tip removal
- Glove guard ensures user safety and won't catch or tear during tip removal
- Feature engraved serial numbers for quality control

These pipettes are made specifically for accuracy and precision, with proven reliability—the robust construction comes with a lifetime warranty.

These pipettors come factory calibrated and tested at 21.5°C ±2°C using distilled water. Pipette calibration volume can be changed using the calibration key (included).

Smooth one-stroke action yields reproducible results and requires minimal exertion.



Specifications

Tip ejector: yes Autoclavable: no



Volume	Accuracy	Precision	Color	Cat. no.	Price
5 µL	±5.00 %	±3.74 %	Silver	GH-06198-59	
10 µL	±5.00 %	±2.60 %	Orange	GH-06198-35	
15 µL	±5.00 %	±1.73 %	Silver	GH-06198-61	
20 µL	±3.00 %	±1.35 %	Black	GH-06198-37	
25 µL	±3.00 %	±1.12 %	White	GH-06198-39	
30 µL	±3.00 %	±0.93 %	Silver	GH-06198-63	
40 µL	±3.00 %	±0.70 %	Silver	GH-06198-65	
50 µL	±2.00 %	±0.80 %	Green	GH-06198-41	
60 µL	±2.00 %	±0.67 %	Silver	GH-06198-69	
70 µL	±2.00 %	±0.57 %	Silver	GH-06198-85	
75 µL	±2.00 %	±0.53 %	Silver	GH-06198-87	
80 µL	±2.00 %	±0.50 %	Silver	GH-06198-89	
90 µL	±2.00 %	±0.44 %	Silver	GH-06198-91	
100 µL	±1.00 %	±0.54 %	Blue	GH-06198-43	
120 µL	±1.00 %	±0.45 %	Silver	GH-06198-93	
150 µL	±1.00 %	±0.36 %	Silver	GH-06198-95	
200 µL	±1.00 %	±0.30 %	Red	GH-06198-45	
200 µL†	±1.00 %	±0.30 %	Red	GH-06198-47	
250 µL	±1.00 %	±0.72 %	Purple	GH-06198-49	
300 µL	±1.00 %	±0.60 %	Brown	GH-06198-51	
400 µL	±1.00 %	±0.50 %	Silver	GH-06198-97	
450 µL	±1.00 %	±0.44 %	Silver	GH-06198-99	
500 µL	±1.00 %	±0.40 %	Yellow	GH-06198-53	
600 µL	±1.00 %	±1.00 %	Silver	GH-06199-03	
700 µL	±1.00 %	±0.86 %	Silver	GH-06199-07	
750 µL	±1.00 %	±0.80 %	Silver	GH-06199-01	
800 µL	±1.00 %	±0.75 %	Silver	GH-06199-05	
900 µL	±1.00 %	±0.67 %	Silver	GH-06199-09	
1000 µL	±1.00 %	±0.60 %	Gray	GH-06198-55	

†Large tip

[GH-17104-01](#) NIST-traceable calibration with data for pipettes

Find even more online!
Go to [ColeParmer.com](#) to see full product details.

Ovation M Mechanical Adjustable-Volume-Set Pipettors

Simple conventional volume setting

- Dispense with minimal force with proven ergonomic design
- Easily contours to your hand for ultimate comfort
- Open PCR and microtubes with ease using built-in cap opener at base

These mechanical adjustable-volume pipettors use the same proven ergonomic Ovation design to minimize contact pressure, tension, and exertion.

The low force plunger allows you to manually control speed with a light touch of the thumb. Releasing pipette tips is a breeze with just a quick press of the tip eject button. The one-way nozzle protects your pipettor and samples as it blocks access of liquid into the body of the pipettor.

No pipette stands required, the Ovation pipettor stands by itself on the benchtop.



Specifications

Tip ejector: yes Autoclavable: yes

Volume	Increments	Accuracy	Precision	Color	Cat. no.	Price
0.2 to 2 µL	0.002 µL	±2.7% at 1 µL	1.8% at 1 µL	Red	GH-06199-02	
1 to 10 µL	0.01 µL	±1.5% at 5 µL	0.6% at 5 µL	Orange	GH-06199-04	
2 to 20 µL	0.02 µL	±1.5% at 10 µL	0.5% at 10 µL	Yellow	GH-06199-06	
10 to 100 µL	0.1 µL	±0.8% at 50 µL	0.24% at 50 µL	Green	GH-06199-08	
20 to 200 µL	0.2 µL	±0.8% at 100 µL	0.25% at 100 µL	Blue	GH-06199-10	
100 to 1000 µL	1.0 µL	±0.8% at 500 µL	0.2% at 500 µL	Purple	GH-06199-12	

Polypropylene Tips

Pack description	Volume	Catalog number	Price
VistaRak style (separate racks)			
Racks of 192 each	0.2 to 20 µL	GH-06197-70	
	2 to 250 µL	GH-06197-71	
	25 to 1250 µL	GH-06197-72	
5 racks of 192 each; sterile, pyrogen-free, RNase/DNase certified	0.2 to 20 µL	GH-06197-76	
	2 to 250 µL	GH-06197-77	
	25 to 1250 µL	GH-06197-78	

Note: Filtered tips and other styles are available at [www.coleparmer.com](#)

[GH-06199-20](#) Ovation M Core pipettor kit. Includes four pipettors (06199-02, -06, -10, -12), pipette stand, and three racks of tips (06197-70, -71, -72)

[GH-06199-22](#) Ovation M Starter pipettor kit. Includes three pipettors (06199-04, -08, -12), pipette stand, and three racks of tips (06197-70, -71, -72)