

Uvex® by Honeywell Seismic Safety Eyewear**Won't cause discomfort**

- Range of comfort and adjustability features for all-day wear
- Protect from particulates with cushioning seals
- Minimize fogging with top and bottom venting
- Won't block peripheral vision



Cushioning seals eyes (above) or remove for standard safety glasses

Flexible design allows you to wear these as safety glasses, or attach the flame-resistant headband to wear as goggles. Also, leave the face cushioning inner frame on for extra comfort during extended-wear applications, remove it for a standard safety glasses feel.

Compliance: ANSI Z87.1-2010 (with or without cushioning), CSA Z94.3 (with cushioning only)

Frame color	Lens	Catalog number	Price per pair	
			1 pr	10 pr
Black	Clear, hard coat	GH-86497-60		
	Clear, antifog	GH-86497-61		
	Clear, dual hard coat/antifog	GH-86497-62		

Sellstrom® Odyssey® II Autoclavable Goggles**Autoclavable for cleanroom use**

- Sterilize by autoclave or gamma radiation

Created for aseptic and cleanroom environments, these autoclavable safety goggles feature UV-absorbing polycarbonate lenses and a comfortable soft body that easily fits over prescription eyewear.



Compliance: ANSI Z87.1+ (High impact), CUL certified to meet CAN/CSA-Z94.3

Description	Lens	Catalog number	Price per pair	
			1 pr	10 pr
Non-vented goggles	Clear, antifog	GH-86281-01		
Vented goggles	Clear	GH-86281-02		

MonoGoggle® XTR™ Goggles
Don't risk safety for visibility

- Greater range of visibility with a more comfortable fit

The 0.060"-thick polycarbonate lens features antifog coating and provides 99.9% UV protection. The soft frame is pliable and conforms to worker's face for a comfortable fit. Model 81657-18 features a detachable curved face shield for full-face protection.



Compliance: ANSI Z87.1+ (High impact)

Description	Frame color	Lens	Catalog number	Price/pr
MonoGoggle XTR goggles	Blue	Clear, antifog	GH-81657-15	
MonoGoggle XTR goggles with detachable face shield	Blue	Clear, antifog	GH-81657-18	

Uvex® by Honeywell Stealth® Safety Goggles**Get superior optics and peripheral vision**

- Indirect ventilation and low profile design for impact and chemical splash protection
- UVExtreme® coating for fog, scratch, and static resistance



Approval: CE En 166

Compliance: ANSI Z87.1-2010, CSA Z94.3

Lens	Catalog number	Price per pair	
		1 pr	10 pr
Clear	GH-86326-00		

Uvex® by Honeywell Strategy™ Goggles**Minimize fogging with Uvextra™ AF lens coating**

Lightweight, TPE body provides exceptional comfort and a snug fit for maximum protection. Available in direct vent or indirect vent styles—both styles fit over most prescription eyewear. Model 86326-20 has an elasticized fabric headband. Model 86326-22 has a neoprene headband for chemical applications.



Compliance: ANSI Z87+ (High impact), CSA Z94.3

Description	Lens	Catalog number	Price per pair	
			1 pr	10 pr
Direct vent goggle	Clear, antifog	GH-86326-20		
Indirect vent goggle		GH-86326-22		

Sellstrom® DP4 Face Shield
Won't limit movement

Faceshield curves naturally to fit facial contours—ensuring reliable protection from splash, particles, and flying debris. Headgear includes ratchet suspension to adjust size and tighten at the turn of a knob.

Soft, padded browguard rests comfortably on face. Rugged, polycarbonate shield is impact- and splash-resistant. Item comes fully assembled with headgear and shield included. Replacement shields are sold separately.



Compliance: ANSI Z87.1+ (High impact), CSA Z94.3

Color	Material	Catalog number	Price per each	
			1 ea	10 ea
Head gear with face shield				
Clear	Polycarbonate	GH-86478-00		
Replacement face shield				
Clear	Polycarbonate	GH-86478-10		