

Guardian Equipment Faucet-Mount Personal Eyewash

Be within reach of an eyewash at all times

- Easily convert a standard faucet into an eyewash station
- Flow controlled by water pressure
- Choose adjustable outlets or gooseneck mount which directs the spray across the eyes

Compliance: ANSI Z358.1-2009 as personal eyewash only.

Goosenecks let you easily adjust eyewash angle.



06767-42

06767-44

Description	Catalog number	Price
Faucet-mount eyewash	GH-06767-42	
Faucet-mount eyewash; with gooseneck mounted outlets	GH-06767-44	

Bradley® On-Site Portable Gravity-Fed Eyewash

Position where you need it—no plumbing needed

- Flushes completely—use just seven gallons of solution for full 15 minute flush
- Know when to refill—transparent polycarbonate tank for easy viewing
- Easy to use—inverted tank is activated when arm is pulled

What's included: transparent tank, yellow polypropylene pedestal, and stainless steel wall bracket with universal identification sign.

Compliance: ANSI Z358.1-2009

Unit with waste cart 86001-08



Description	Dimensions (H x W x D)	Catalog number	Price
On-site eyewash	22" x 24 ³ / ₈ " x 19" (55.9 x 61.9 x 48.3 cm)	GH-86001-00	

Accessories

[GH-86001-08](#) Optional waste cart, 22¹/₂"W x 33"H x 29³/₄"D (56 x 84 x 76 cm)

Honeywell® 100% Sterile Primary Eyewash Station with Alarm

Minimize further injury with sterile delivery system

- Alert others of injury with auto-activation of alarm when unit is activated
- Alerts when mandatory 15-minute flush is complete
- Position and move as needed

Sterile saline cartridges have a 24-month shelf life (from date of manufacture), minimizing replacement time and expense (cartridges sold separately). Cartridge expiration date can easily be seen through side view window. Integrated waste reservoir prevents spills and eases disposal of spent solution.

What's included: emergency eyewash station sign and mounting bracket.

Compliance: ANSI Z358.1-2009



Description	Dimensions (H x W x D)	Cat. no.	Price
100% Sterile eyewash station	34 ³ / ₄ " x 15 ¹ / ₂ " x 17 ¹ / ₂ " (88.3 x 39.4 x 44.5 cm)	GH-06796-01	

[GH-06796-05](#) Eyewash refill cartridge

Guardian Equipment Combination Showers

Safely flush body and eyes separately or simultaneously

- No need to use hands with foot operated models
- Units feature 10"-dia (25 cm) shower head and 12"-dia (31 cm) eyewash basin

Approval: UL, CSA

Compliance: ANSI Z358.1-2009

Specifications

Flow rate Shower:
30 GPM at 30 psi
Eye/facewash:
3.6 GPM at 30 psi
Inlet: 1¹/₄" NPT(F)
Outlet: 1¹/₄" NPT(F)

Valves Shower:
1" NPT(F) brass/
chrome plated, stay open
Eye/facewash: 1/2" NPT(F)
brass/chrome plated,
stay open
Supply pipe: 1¹/₄" NPT(F)
galvanized steel



Safety station 06767-41 features both hand and foot activation

Description	Material	Catalog number	Price
Hand operated	ABS plastic	GH-06767-40	
Hand/foot operated	ABS plastic	GH-06767-41	
Hand operated	Stainless steel	GH-06767-43	
Hand operated w/bowl cover	Stainless steel	GH-06767-45	

