



## Eagle Flammable Storage Cabinets

### Accommodate your needs—adjustable steel shelves hold up to 350 lbs

Flammable cabinets are constructed of epoxy-powder coated, double-walled, 18-gauge steel with 1½" (3.8 cm) insulating air barrier—ideal for safely storing flammable liquid containers up to 5 gallons in size. Cabinets feature dual vents, grounding attachments, and key lock. Available with either manual-latching or self-closing (fusible link actuated at 160°F/71°C) doors. Include adjustable HDPE shelf trays for excellent spill containment. Hazard label: FLAMMABLE—KEEP FIRE AWAY.

**Approval:** FM (self-closing models only)

**Compliance:** OSHA/NFPA Code 30 specifications, UFC 79 (self-closing models only)



Capacity gal. (L)	No. of shelves	Dimensions (W x H x D)		Shpg wt		Manual-latching door		Self-closing door	
		in.	cm	lb	kg	Cat. no.	Price	Cat. no.	Price
4 (15)	1	17½ x 22½ x 18	44.5 x 57 x 45.7	70	31.8	<a href="#">GH-09418-21</a>		<a href="#">GH-09418-20</a>	
12 (45.4)	1	23 x 35 x 18	58.4 x 89 x 45.7	108	49.0	<a href="#">GH-09418-23</a>		<a href="#">GH-09418-22</a>	
16 (60.5)	1	23 x 44 x 18	58.4 x 111.8 x 45.7	150	68.1	<a href="#">GH-09418-25</a>		<a href="#">GH-09418-24</a>	
30 (113.5)	1	43 x 44 x 18	109 x 111.8 x 45.7	320	145	<a href="#">GH-09418-65</a>		<a href="#">GH-09418-26</a>	
30 (113.5)	1					—		<a href="#">GH-09418-30†</a>	
45 (170.3)	2	43 x 65 x 18	109 x 165 x 45.7	435	197	<a href="#">GH-09418-70</a>		<a href="#">GH-09418-27</a>	
45 (170.3)	2					—		<a href="#">GH-09418-40†</a>	
60 (227)	2					31¼ x 65 x 31¼	79.4 x 165 x 79.4	374	170

†Has one shelf-closing sliding door.

#### Accessories

[GH-09418-60](#) Extra shelf for 30- and 45-gal. flammable storage cabinets

[GH-09418-61](#) Extra shelf for 60-gal. flammable storage cabinets



U-loc™ padlockable handle

## Justright® Flammable Storage Cabinets

### Never leave the door open again

Cabinets feature 18-gauge steel, all-welded, double-wall, insulating air barrier construction for protection and durability. The reinforced SpillSlope™ shelves are adjustable in 2¼" (5.7 cm) increments and feature built-in troughs and leakproof wells to contain spills. Self-closing models feature self-latching doors with U-loc™ padlockable handle and 3-point locking system to ensure complete closure.

Models with self-closing doors feature Haz-Alert reflective labeling and a fusible link that melts at 165°F (73.8°C); automatically closing cabinet doors to prevent exposure to fire. Adjustable leveling feet help to maintain proper alignment on uneven surfaces.

**Approval:** FM

**Compliance:** OSHA, NFPA, UFC 79 (self-closing models only)



Capacity	No. of shelves	Dimensions (W x H x D)		Shpg wt		Manual-latching door		Self-closing door	
		in.	cm	lb	kg	Cat. no.	Price	Cat. no.	Price
30 gal. (113.5 L)	1	43 x 44 x 18	109 x 112 x 46	213	97	<a href="#">GH-81790-44</a>		<a href="#">GH-81790-45</a>	
45 gal. (170.3 L)	1	43 x 65 x 18	109 x 165 x 46	313	141	<a href="#">GH-81790-41</a>		<a href="#">GH-81790-36</a>	
60 gal. (227 L)	2	34 x 65 x 34	86 x 165 x 86	392	176	<a href="#">GH-81790-42</a>		<a href="#">GH-81790-37</a>	
90 gal.† (341 L)	2	43 x 65 x 34	109 x 165 x 86	480	218	<a href="#">GH-81790-43</a>		<a href="#">GH-81790-38</a>	

†Codes state that not more than 60 gallons may be Class I and Class II liquids.

## SciMatCo® Flammable Storage Cabinets

### Won't let out spills

Use this lockable, wooden cabinet to conveniently store flammable liquids. Constructed of 1" (2.5 cm)-thick high-density plywood; finished with yellow epoxy paint inside and out. Specially designed floor serves as a liquid-tight trough to retain spills. Locking door features continuous piano-type hinges and a 10" x 10" (25.4 x 25.4 cm) "Flammable" hazard label. Contain one variable position shelf. Meet all applicable OSHA and NFPA standards for flammable safety cabinets. Models 81780-25 and -27 are supplied with self-closing doors that meet the Uniform Fire Code (UFC).

**Compliance:** OSHA, NFPA, UFC (self-closing models only)

Capacity (qty x gal.)	No. of shelves	Dimensions (W x H x D)		Shpg wt		Manual-latching door		Self-closing door	
		in.	cm	lb	kg	Cat. no.	Price	Cat. no.	Price
4 x 1	1	16¾ x 21¼ x 15¾	42.5 x 54 x 40	50	22.7	<a href="#">GH-81781-10</a>		<a href="#">GH-81780-25</a>	
22 x 1		30 x 32 x 18½	76.2 x 81.3 x 47	113	51.8	<a href="#">GH-81781-30</a>		<a href="#">GH-81780-27</a>	

