

Justright® “Compac” Cabinets

Keep chemicals close at hand— ideal for benchtop use

Use these 18-gauge steel cabinets to safely store flammable or combustible liquids. Cabinets come equipped with either a manual or self-closing door (fusible link melts at 165°F/73.9°C) for added safety and one adjustable shelf for convenience. Doors have a three point fail-safe locking mechanism and feature a “Flammable” hazard label. Place cabinets under an existing countertop or use as stand alone units.

Approval: FM (models 81790-22 and -23 only)

Compliance: OSHA/NFPA, UFC 79 (self-closing models only)



Capacity	No. of shelves	Dimensions (W x H x D)		Shpg wt		Catalog number	Price
		in.	cm	lb	kg		
Cabinets with manual doors							
4 gal. (15.1 L)	1	17 x 22 x 17	43.2 x 55.9 x 43.2	62	28.2	GH-81790-21	
12 (45.4 L)	1	24¼ x 35 x 18	61.6 x 89 x 45.7	129	58.6	GH-81790-23	
Cabinets with self-closing doors							
4 gal. (15.1 L)	1	17 x 22 x 17	43.2 x 55.9 x 43.2	62	28.2	GH-81790-20	
12 (45.4 L)	1	24¼ x 35 x 18	61.6 x 89 x 45.7	131	59.5	GH-81790-22	



Eagle PE Acid and Corrosive Cabinets

Maintain safe storage of aggressive chemicals

Adjustable shelves contain small spills and remove for easy cleaning. Doors feature integral handles with key lock holes (lock not included) and recessed areas for additional storage of smaller bottles. Cabinets have a one-gallon top and internal sump capacity, two 2" (5.1 cm) vents with cap, leveling feet, and “Caution Corrosives” label.

Description	Capacity	No. of shelves	Dimensions (W x H x D)	Shpg wt		Blue		White	
				lb	kg	Cat. no.	Price	Cat. no.	Price
Benchtop	4 gal. (15 L)	2	18" x 22" x 18" (45.7 x 55.9 x 45.7 cm)	35	16	GH-81773-00		GH-81773-06	
Under-counter	22 gal. (83 L)	2	35" x 36" x 22" (88.9 x 91.4 x 55.9 cm)	95	43	GH-81773-02		GH-81773-08	
Full-size	44 gal. (166 L)	4	35" x 65" x 22" (88.9 x 165.1 x 55.9 cm)	130	59	GH-81773-04		GH-81773-10	



Justright® HDPE Acid Storage Cabinets

Don't sacrifice workspace—recessed top for additional work surface

These HDPE acid storage cabinets won't corrode or rust when exposed to acids. One-piece, molded body construction prevents leaks. Includes removable bottom tray funnel and sump. Recessed area in door stores small containers.

Style	Capacity	No. of shelves	Dimensions (W x H x D)	Shpg wt lb (kg)	Catalog number	Price
Benchtop	2 gal. (8 L)	—	14¼" x 19½" x 16½" (36.2 x 49.5 x 41.9 cm)	30 (13.7)	GH-81790-00	
Full-size	8 gal. (30 L)	1	36" x 35" x 22" (91.4 x 88.9 x 56 cm)	120 (54.4)	GH-81790-10	



SciMatCo® Polypropylene Acid Storage Cabinets

No more leaks

These polypropylene acid storage cabinets contain no metal parts—they won't corrode or rust. Constructed of ¾" (0.96 cm)-thick white polypropylene, cabinets feature plastic hinges and welded interior seams to prevent leakage. Choose from benchtop or full-size models. All cabinets are lockable and include hazard warning label, padlock, and two keys.

Compliance: OSHA

Style	Capacity (qty x volume)	No. of shelves	Dimensions (W x H x D)		Shpg wt		Catalog number	Price
			in.	cm	lb	kg		
Benchtop	6 x 2.5 L (15 L total)	—	16 x 16 x 16	41 x 41 x 41	25	11.3	GH-81780-15	
Full-size	50 x 2.5 L (125 L total)	1	48 x 40 x 18	122 x 102 x 46	126	57.2	GH-81780-40	
Full-size	100 x 2.5 L (250 L total)	3	48 x 60 x 18	122 x 152 x 46	210	95.3	GH-81780-42	

