

SciMatCo® Acid Storage Cabinets

Won't corrode—metal-free design

Wood Cabinets are made of 1" (2.5 cm)-thick plywood, wood hinges, and feature a liquid-tight floor trough and chemical-resistant epoxy paint. Models 81780-02 and -04 include a liquid-tight top dispensing area. **HDPE Cabinets** are made of ¾" (1.9 cm)-thick high-density polyethylene, plastic hinges, and feature liquid-tight welded interior seams. Model 81780-20 includes a liquid-tight top dispensing area. **Compliance:** OSHA

Material of construction	PP coated lining	Capacity (qty x volume)	No. of shelves	Overall dimensions (W x H x D)	Shpg wt lb (kg)	Catalog number	Price
Wood	None	5 x 2.5 L	None	16¾" x 21¼" x 15¾"	45 (20)	GH-81780-05	
HDPE		6 x 2.5 L			50 (23)	GH-81780-10	
Wood	Partial	24 x 2.5 L	One fixed position	30" x 32" x 18½"	108 (49)	GH-81780-00	
	Partial				142 (64)	GH-81780-02	
	Full	30 x 2.5 L			154 (70)	GH-81780-04	
HDPE	None	36 x 2.5 L		31" x 36" x 20"	165 (75)	GH-81780-20	
					29" x 34½" x 22"	161 (73)	GH-81780-30

Accessories

GH-81780-05 Nitric acid compartment fits on top or bottom shelf of full-size acid storage cabinets. Holds five 2.5-L containers. Constructed of ⅛"-thick polypropylene



Eagle Acid Cabinets

Stands up to chemicals—epoxy-coated steel for protection

Acid cabinets are constructed of epoxy-powder coated, double-walled, 18-gauge steel with 1½" (3.8 cm) insulating air barrier—ideal for both flammable and nonflammable acids and corrosive liquids. Cabinets feature dual vents, grounding attachments, and key lock. Available with either manual-latching or self-closing (fusible link actuated at 160°F/71°C) doors. Includes adjustable HDPE shelf trays for excellent spill containment. Cabinets are blue with hazard label: CAUTION-CORROSIVES. **Approval:** FM (self-closing models only).

Compliance: OSHA/NFPA Code 30 specifications



Capacity (gal.)	No. of shelves	Dimensions (W x H x D)	Shpg wt lb (kg)	Manual-latching door		Self-closing door	
				Cat. no.	Price	Cat. no.	Price
4	1	17½" x 22½" x 18"	80 (36)	GH-09419-03		GH-09419-02	
12	1	23" x 35" x 18"	135 (61)	GH-09419-05		GH-09419-04	
24	3	23" x 35" x 18"	270 (122)	GH-09419-07		GH-09419-06	
30	1	43" x 44" x 18"	265 (120)	GH-09418-80		GH-09418-99	
45	2	43" x 65" x 18"	365 (167)	GH-09418-90		GH-09419-00	
60	2	31¼" x 65" x 31¼"	374 (170)	GH-09418-94		GH-09419-01	



Cabinet 09418-90 features adjustable shelves to accommodate 5-gallon containers.

NEW

Captair® Vented Chemical Storage Cabinets

Don't get overcome by vapors

Vented, ductless cabinets are equipped with a silent turbine fan that draws chemical vapors from bottles into a molecular filter with high absorption capacity—maintaining the purity and quality of the air outside. Polyester-coated steel cabinets include glass doors for immediate view of stored chemicals. Internal adjustable shelves feature magnetic signs for separating and labeling the chemical types stored. Single and double models feature a spill tray at the base and a door lock with keys. Models with a sensor monitor filter performance and use visual and audible alarms to alert you of needed filter maintenance or fan failure. Get better protection by stacking multiple filter cartridges. **Compliance:** AFNOR NF X 15-211, Class II



Description	Capacity (qty x volume)	No. of shelves	Filter type	Dimensions (W x H x D)	Shpg wt lb (kg)	115 VAC, 60 Hz		230 VAC, 60 Hz		Replacement filters	
						Cat. no.	Price	Cat. no.	Price	Cat. no.	Price
Shelf	10 x 1 L	0	Organics	32¼" x 28¼"	100	45	GH-86446-06		GH-86446-07		GH-86446-50
			Organics/acids	x 11¼"			GH-86446-08		GH-86446-09		GH-86446-51
Compact	48 x 1 L	1	Organics	32¼" x 28½"	122	55	GH-86446-00		GH-86446-04		GH-86446-50
			Organics/acids	x 14"			GH-86446-02		GH-86446-05		GH-86446-51
Single	120 x 1 L	4	Organics	31½" x 80¾"	325	147	GH-86446-14		GH-86446-15		GH-86446-53
			Organics/acids	x 20"			GH-86446-16		GH-86446-17		GH-86446-54
Single with sensor	120 x 1 L	4	Organics	31½" x 85½"	325	147	GH-86446-18		GH-86446-19		GH-86446-52
			Organics/acids	x 23¾"			GH-86446-24		GH-86446-25		GH-33520-90
Double with sensor	240 x 1 L	8	Organics	63" x 87"	660	299	GH-86446-26		GH-86446-27		GH-86446-52
			Organics/acids	x 23¾"			GH-86446-28		GH-86446-29		GH-33520-90