

Thermo Scientific™ Tube Revolver

Be more flexible with interchangeable paddles

- Small footprint
- Paddles are adjustable from 0 to 90° to optimize the mixing angle
- Set in “oscillating” mode to achieve more effective mixing, oscillation occurs every 40 degrees in the rotation cycle
- Variable speed with easy-to-use intuitive controls
- Maintenance-free motor provides quiet operation

What's included: two 7 x 10/15-mL paddles, two 7 x 5/7-mL paddles, two 15 x 1.5/2-mL paddles, one 6 x 50-mL paddle, and power cord with plug (model 04725-16 has plug for US; model 04725-17 has plugs for China, Europe, and UK).

NEW



Paddle Attachments

Paddle capacity	Cat. no.	Qty/pk	Price/pk
7 x 10/15-mL tubes	GH-04725-71	2	
7 x 5/7-mL tubes	GH-04725-72	2	
15 x 1.5/2-mL tubes	GH-04725-73	2	
21 x 0.5/0.8-mL tubes	GH-04725-74	2	
6 x 50-mL tubes	GH-04725-75	1	

Speed range	Power		Plug type	Catalog number	Price
	VAC	Hz			
10 to 40 rpm	100 to 240	50/60	US Assorted†	GH-04725-16 GH-04725-17	

†Model 04725-17 includes cord set with plugs for China, Europe, and UK.

Thermo Scientific™ Cimatec™ Magnetic Microplate Shakers

Easily shake 96- or 384-well microplates

- Durable aluminum nickel-coated housing is IP32 rated

Space-saving compact design is ideal for any crowded benchtop!



Zero position, self-centering shakers have adjustable speed control. Automatic start-up enables slow start to prevent spilling of samples. Remote control units have an RS-232 interface—control up to 14 units with control unit or software (both included).

Orbit size	Speed range	Power		Catalog number	Price
		VAC	Hz		
Direct control model (orbital motion only)					
5/64" (2 mm) dia	100 to 2000 rpm	115	50/60	GH-51511-00	
Remote control model (orbital/reciprocating motion)					
5/64" (2 mm) dia	100 to 2000 rpm	115 230	50/60	GH-51511-10 GH-51511-15	

Burrell Wrist-Action® Shakers

Get wrist-action mixing without holding samples

- Adjustment arm lets you choose the shaking amplitude



Two “flask-holding” configurations are available: models with side arm capacity only or models with side arm and top platform capacity. Shaking amplitude is controlled with the adjustment arm. Overload protection turns shaker off in event of a malfunction.

What's included: side arm clamps and a 7-ft (2.1-m) cord with US standard plug; models with a top platform also include a set of 10 platform clamps.

Specifications

Speed: 385 oscillations/min (±10%)
Shaking angle: 0 to 15°
Timer range: 0 to 60 min or continuous
Platform dimensions (W x D): 17" x 7¾" (43.1 x 19.7 cm)
Max load: 10 lbs.

Flask Capacity		115V/60 Hz		220V/50 Hz	
Vessel Capacity	Platform Capacity	Catalog number	Price	Catalog number	Price
4	None	GH-51100-01		GH-51100-02	
8	None	GH-51100-20		GH-51100-25	
12	None	GH-51100-30		GH-51100-35	
4	8†	GH-51100-80		GH-51100-85	
8	8†	GH-51100-90		GH-51100-95	
12	8†	GH-51100-96		GH-51100-97	

†250-mL flasks

Wait!

There's More at
[ColeParmer.com](#)

Find all the
product specs
you need!