

ThermoSafe Lab Mailers

Deliver specimens safely

- Fitted halves cushion contents for superior protection
- Lightweight mailers meet postal regulations for nonhazardous materials

Tube Mailer accepts tubes with rubber stopper or screw cap closures—including Corvac® and Vacutainer® tubes.

Slide Mailer five evenly-spaced slots to protect 1" x 3" (2.5 x 7.6 cm) slides from scratches and cross-contamination. Holds up to ten microscope slides.

Mini Mailer accommodates tubes, ampoules, vials, small bottles, and tissue flasks with space for refrigerants.

Multipurpose Mailer holds cans, screw-cap vials, tubes, swabs, and air filter cartridges.

Aluminum Shipping Can accommodates most commonly used tubes, vials, and bottles. Provides additional security during handling and shipping. Screw-cap and seamless construction prevents leakage.



Mailer type	Mailer capacity	Cavity dimensions (L x W x H)		Catalog number	Qty/cs	Price/cs	Shipping cartons		
		in.	cm				Catalog number	Qty/cs	Price/cs
Tube	One 16 x 103 mm tube	1½ x 1 x ¼	3.8 x 2.5 x 0.6	GH-03727-02	300		GH-03727-21	300	
	Five 13 x 103 mm tubes	1½ x 1 x ¼	3.8 x 2.5 x 0.6	GH-03727-01	150		GH-03727-22	300	
	Eight 16 x 103 mm tubes	1½ x 1 x ¼	3.8 x 2.5 x 0.6	GH-03727-03	50		GH-03727-23	200	
Slide	Ten 1" x 3" slides	4 x 2½ x 2	10.2 x 6.4 x 5.1	GH-03750-10	300		GH-03750-30	300	
Mini	—	5¾ x 4¾ x 3	14.9 x 11.1 x 7.6	GH-03741-20	24		GH-03741-23	24	
Multipurpose	—	8 x 2¼ x 1½	20.3 x 5.7 x 3.8	GH-03741-30	50		GH-03727-25	100	
Aluminum can	—	1¾ dia x 4¾ H	4.4 dia x 12.1 H	GH-03727-04	48		GH-03731-32	100	

ThermoSafe Insulated Shippers

Ship nonhazardous materials without worry

- Add as many ice packs as you need

Purchase the size you need for efficient use of space and refrigerant. Compact shippers have a cylindrical interior to hold bottles, tubes, vials, and other small items. Medium- and large-capacity models have a rectangular interior and include cartons. Mailer 03726-53 has thick walls—save money on refrigerant.

Wall thickness	Inside dimensions (L x W x H)		Outside dimensions (L x W x H)		Catalog number	Qty/cs*	Price/ea
	in.	cm	in.	cm			
Compact insulated shippers							
1½" (3.8 cm)	3¼ H x 3 dia	8.3 H x 7.6 dia	6 x 6 x 6	15.2 x 15.2 x 15.2	GH-03730-20	12	
1½" (3.8 cm)	8 H x 4¾ dia	20.3 H x 12.4 dia	8 x 8 x 11	20.3 x 20.3 x 27.9	GH-03730-30	6	
Medium-capacity shippers							
1½" (3.8 cm)	8 x 6 x 4¼	20.3 x 15.2 x 10.8	11 x 9 x 7¼	27.9 x 22.9 x 18.4	GH-03726-11 †	12	
1½" (3.8 cm)	8 x 5½ x 8½	20.3 x 14.9 x 22.5	11 x 9 x 11½	27.9 x 22.9 x 30.2	GH-03726-21 †	12	
1½" (3.8 cm)	8 x 5½ x 11½	20.3 x 14.9 x 29.2	11 x 9 x 14¼	27.9 x 22.9 x 36.8	GH-03726-31 †	10	
2¼" (5.7 cm)	6¼ x 5¾ x 7¾	15.9 x 14.6 x 19.7	11¼ x 10½ x 12½	28.8 x 26.7 x 32.1	GH-03726-53 †	8	
Large-capacity shippers							
1" (2.5 cm)	11¾ x 8¾ x 11	28.9 x 21.3 x 27.9	13¾ x 10½ x 13	34.9 x 26.7 x 33	GH-03732-00 †	8	
1½" (3.8 cm)	10½ x 7¼ x 10	26.7 x 18.4 x 25.4	13¾ x 10½ x 13½	34.9 x 26.7 x 34.3	GH-03740-00 ‡	8	
1½" (3.8 cm)	11¾ x 9¾ x 7	29.5 x 25.1 x 17.8	14¾ x 13¼ x 10½	37.8 x 33.7 x 25.7	GH-03736-01 †	8	
1½" (3.8 cm)	11¾ x 9¾ x 9	29.5 x 25.1 x 22.9	15 x 13¼ x 12	38.1 x 33.1 x 30.5	GH-03738-01 †	6	
1½" (3.8 cm)	19¾ x 12¾ x 12¼	49.2 x 31.4 x 31.1	22¾ x 15¾ x 15¾	56.8 x 39.1 x 39.1	GH-03739-00 †	2	



Note: For shipping nonhazardous materials only.

***Discount:** Save 10% when ordering one case worth of shippers.

†Supplied with a 200-lb test corrugated carton.

‡Supplied with a 275-lb test fiberboard outer case.

ThermoSafe Insulated PUR Shippers

Get extensive protection for long-range trips

Rigid, reusable, one-piece, three-layer laminate construction provides excellent temperature protection, exceptional strength, and durability. Durable closed-cell polyurethane foam insulated shippers ensure frozen or refrigerated products from moderate and extreme ambient temperature exposure. Flexible polyurethane foam plug seals the top, cushions and insulates contents, and vents dry ice. Shippers withstand crush compression in excess of 5000 lbs. CFC and HCFC free; comply with international clean air regulations.

Wall thickness	Inside dimensions (L x W x H)		Outside dimensions (L x W x H)		Catalog number	Qty/cs	Price/cs
	in.	cm	in.	cm			
2" (5.1 cm)	11 x 8 x 7	29.7 x 20.3 x 17.8	15¾ x 12¾ x 14¼	40 x 32.4 x 36.2	GH-99530-80	3	
	16¼ x 9¼ x 10¼	41.3 x 23.5 x 26	21 x 14 x 17½	53.3 x 35.6 x 44.5	GH-99530-82	2	
	18½ x 14½ x 12	47 x 36.8 x 30.5	23¼ x 19¼ x 19¼	59.1 x 48.9 x 48.9	GH-99530-84	1	
	18½ x 18½ x 16¾	47 x 47 x 42.5	24¼ x 23 x 24	61.6 x 58.4 x 61	GH-99530-86	1	
3" (7.6 cm)	8 x 6 x 8	20.3 x 15.2 x 20.3	14¾ x 12¾ x 16¼	37.5 x 32.4 x 41.3	GH-99530-88	4	
	12 x 10 x 13	30.5 x 25.4 x 33	8¾ x 16¼ x 21¼	22.2 x 42.5 x 21.2	GH-99530-90	2	

