

Cole-Parmer® Solid Laboratory Stoppers, Rubber or Neoprene

No guessing sizes—stopper has size raised on top

Black Rubber Stoppers stay pliable over a long period and withstand laboratory conditions without hardening. Stoppers retain resiliency even after repeated autoclaving. Contain some sulfur. **Autoclavable.**

Green Neoprene Stoppers withstand petroleum products, fats, oils, and organic chemicals. Stoppers exhibit good resiliency and shelf-life. Contain no sulfur. **Autoclavable.**

“Exactly as promised.”



Buy More...Save More!

20% off on 120+
15% off on 30 to 119
10% off on 6 to 29 packs or cases

Standard size no.	Top dia (mm)	Bottom dia (mm)	Height (mm)	Black rubber stoppers			Green neoprene stoppers		
				Catalog number	Qty/ pk†	Price/ pk	Catalog number	Qty/ pk†	Price/ pk
000	12.7	8.2	21	GH-62990-00	181		GH-62991-00	160	
00	15	10	25	GH-62990-02	105		GH-62991-02	95	
0	17	13	25	GH-62990-04	77		GH-62991-04	68	
1	19	14	25	GH-62990-06	57		GH-62991-06	48	
2	20	16	25	GH-62990-08	52		GH-62991-08	44	
3	24	18	25	GH-62990-10	39		GH-62991-10	32	
4	26	20	25	GH-62990-12	33		GH-62991-12	27	
5	27	23	25	GH-62990-14	28		GH-62991-14	23	
5½	28	24	25	GH-62990-16	26		GH-62991-16	23	
6	32	26	25	GH-62990-18	20		GH-62991-18	17	
6½	34	27	25	GH-62990-20	18		GH-62991-20	15	
7	37	30	25	GH-62990-22	15		GH-62991-22	12	
7½	39	31	25	GH-62990-24	14		GH-62991-24	13	
8	41	33	25	GH-62990-26	12		GH-62991-26	10	
8½	43	36	25	GH-62990-28	12		GH-62991-28	11	
9	45	37	25	GH-62990-30	10		GH-62991-30	8	
9½	46	38	25	GH-62990-32	9		GH-62991-32	9	
10	50	42	25	GH-62990-34	8		GH-62991-34	8	
10½	53	45	25	GH-62990-36	7		GH-62991-36	7	
11	56	48	25	GH-62990-38	6		GH-62991-38	6	
11½	63	50	25	GH-62990-40	5		GH-62991-40	4	
12	64	54	25	GH-62990-42	5		GH-62991-42	5	
13	68	58	25	GH-62990-44	4		GH-62991-44	4	
13½	75	62	35	GH-62990-46	3		GH-62991-46	3	
14	90	75	39	GH-62990-48	1		GH-62991-48	1	
15	103	83	39	GH-62990-50	1		GH-62991-50	1	
16	127	90	50	GH-62990-52	1		GH-62991-52	1	
Assortment pack, sizes 00 to 8				GH-62990-90	5 lb		GH-62991-90	5 lb	

†The quantity per pack given is an approximate number based on the average number of stoppers in one pound.

Solid Color-Coded Stoppers, Silicone

Fit a wide range of holes—flexible construction for easy fit

- Lightweight stoppers float if dropped in water
- Handle temperatures from –76 to 392°F (–60 to 200°C)
- Easily adapt to your needs—bore holes for thermometer or tubing addition
- Autoclavable

Buy More...Save More!

20% off on 120+
15% off on 30 to 119
10% off on 6 to 29 packs or cases



Standard size no.	Japanese size no.	Top dia (mm)	Bottom dia (mm)	Height (mm)	Color	Catalog number	Qty/ pk	Price/ pk
000	03	12	8	20	White	GH-06298-00	50	
00	01-02	15	11	22	Yellow	GH-06298-02	50	
0	1-2	17.5	13	25	Green	GH-06298-04	50	
2	3-4	20	15.5	27	Pink	GH-06298-06	20	
4	5-7	25	19	30	Blue	GH-06298-08	20	
5	8-9	30	23	33	White	GH-06298-10	10	
6½	10-11	35	28	35	Yellow	GH-06298-12	10	
8	12-14	40	33	40	Green	GH-06298-14	10	
9½	15-16	46	38	42	Pink	GH-06298-16	5	
10½	17-18	52	44	48	Blue	GH-06298-18	5	
11	19-20	58	49	52	White	GH-06298-20	5	
12	21-23	67	56	52	Yellow	GH-06298-22	1	
13½	24-26	77	65	52	Green	GH-06298-24	1	
14	27-29	87	75	52	Pink	GH-06298-26	1	