

## Cole-Parmer® Write-On Colored Tape and Dispenser

Easily identify samples by color-coding

- Withstands water, oil, and acid
- Easy-write surface accommodates pencil, pen, or permanent marker
- Use in temperatures from -10 to 250°F (-23 to 121°C)
- Optional dispenser for easier tearing



Array of colors and sizes fit conveniently in optional dispenser 06530-11

Buy More...Save More!

- 20% off on 120+
- 15% off on 30 to 119
- 10% off on 6 to 29 packs or cases

| Color          | 1/2" (1.3 cm) W x 14 yd (13 m) L |       |       | 3/4" (1.9 cm) W x 14 yd (13 m) L |       |       | 1" (2.5 cm) W x 14 yd (13 m) L |       |       |
|----------------|----------------------------------|-------|-------|----------------------------------|-------|-------|--------------------------------|-------|-------|
|                | Cat. no.                         | RI/pk | Price | Cat. no.                         | RI/pk | Price | Cat. no.                       | RI/pk | Price |
| White          | <a href="#">GH-06530-21</a>      | 6     |       | <a href="#">GH-06530-31</a>      | 4     |       | <a href="#">GH-06530-41</a>    | 3     |       |
| Yellow         | <a href="#">GH-06530-22</a>      | 6     |       | <a href="#">GH-06530-32</a>      | 4     |       | <a href="#">GH-06530-42</a>    | 3     |       |
| Green          | <a href="#">GH-06530-23</a>      | 6     |       | <a href="#">GH-06530-33</a>      | 4     |       | <a href="#">GH-06530-43</a>    | 3     |       |
| Pink           | <a href="#">GH-06530-24</a>      | 6     |       | <a href="#">GH-06530-34</a>      | 4     |       | <a href="#">GH-06530-44</a>    | 3     |       |
| Red            | <a href="#">GH-06530-25</a>      | 6     |       | <a href="#">GH-06530-35</a>      | 4     |       | <a href="#">GH-06530-45</a>    | 3     |       |
| Orange         | <a href="#">GH-06530-26</a>      | 6     |       | <a href="#">GH-06530-36</a>      | 4     |       | <a href="#">GH-06530-46</a>    | 3     |       |
| Blue           | <a href="#">GH-06530-27</a>      | 6     |       | <a href="#">GH-06530-37</a>      | 4     |       | <a href="#">GH-06530-47</a>    | 3     |       |
| Assorted pack† | <a href="#">GH-06530-28</a>      | 24    |       | <a href="#">GH-06530-38</a>      | 16    |       | <a href="#">GH-06530-48</a>    | 12    |       |

†Assorted pack contains each color above.

[GH-06530-11](#) Tape dispenser

## Hi-Lo Temperature Fiberglass Tape

Don't worry about temperature

- Ideal for extreme temperature use—withstands temperatures from -385 to 550°F (-232 to 288°C)
- Easily write on textured surface



| Width         | Length/roll   | Catalog number              | Price |
|---------------|---------------|-----------------------------|-------|
| 1/2" (1.3 cm) | 25 ft (7.6 m) | <a href="#">GH-08277-50</a> |       |
| 1" (2.5 cm)   |               | <a href="#">GH-08277-55</a> |       |

**Wait!**

There's More at [ColeParmer.com](http://ColeParmer.com)

Find all the product specs you need!

## Autoclave Tape

Know your labware is autoclaved

- Dark-colored diagonal mark revealed after autoclaving at 250°F (121°C) for 15 minutes
- Sticks to glass, cloth, or metal
- Leaves no residue



| Width       | Length/roll  | Catalog number              | Price |
|-------------|--------------|-----------------------------|-------|
| 1" (2.5 cm) | 41 ft (12 m) | <a href="#">GH-08277-62</a> |       |

## Cole-Parmer® Color-Coded Adhesive Tape and Dispenser

No scuffing—adheres to most surfaces

- Easily identify labware, pipes, or wiring
- Optional dispenser provides easy tearing of tape



| Color  | 3/4" (1.9 cm) W x 36 yd (33 m) L |       | 1" (2.5 cm) W x 36 yd (33 m) L |       |
|--------|----------------------------------|-------|--------------------------------|-------|
|        | Catalog number                   | Price | Catalog number                 | Price |
| White  | <a href="#">GH-86209-30</a>      |       | <a href="#">GH-86209-40</a>    |       |
| Yellow | <a href="#">GH-86209-31</a>      |       | <a href="#">GH-86209-41</a>    |       |
| Orange | <a href="#">GH-86209-32</a>      |       | <a href="#">GH-86209-42</a>    |       |
| Red    | <a href="#">GH-86209-33</a>      |       | <a href="#">GH-86209-43</a>    |       |
| Green  | <a href="#">GH-86209-34</a>      |       | <a href="#">GH-86209-44</a>    |       |
| Blue   | <a href="#">GH-86209-35</a>      |       | <a href="#">GH-86209-45</a>    |       |
| Black  | <a href="#">GH-86209-37</a>      |       | <a href="#">GH-86209-47</a>    |       |

[GH-08278-26](#) Multiple roll dispenser, acrylic. For tapes on a 3" (7.6 cm) dia core

## Kapton® Polyimide Tape

Stands up to heat and chemicals

- Silicone adhesive withstands temperatures from -100 to 500°F (-73 to 260°C)
- High tensile strength, good solvent resistance, and excellent dielectric strength for more flexibility
- Meets UL-510 for flame retardant specifications



| Width           | Thickness (mil) | Length/roll    | Catalog number              | Price |
|-----------------|-----------------|----------------|-----------------------------|-------|
| 1/8" (0.3 cm)   | 2.5             | 36 ft (10.9 m) | <a href="#">GH-08277-78</a> |       |
| 1/4" (0.6 cm)   |                 |                | <a href="#">GH-08277-79</a> |       |
| 1/2" (1.3 cm)   |                 |                | <a href="#">GH-08277-80</a> |       |
| 3/4" (1.9 cm)   | 2.5             | 36 ft (10.9 m) | <a href="#">GH-08277-81</a> |       |
| 1" (2.5 cm)     |                 |                | <a href="#">GH-08277-82</a> |       |
| 1 1/2" (3.8 cm) |                 |                | <a href="#">GH-08277-83</a> |       |