

## Masterflex® C-Flex® Pump Tubing

### Minimize gas permeability



**Applications:** General-purpose lab uses requiring high performance and long life.

**Characteristics:** Exceptional tensile and tear strength; good biocompatibility; low gas permeability; and a smooth surface. Opaque white.

**Certifications:** USP Class VI, European Pharmacopoeia (EP 3.2.9), REACH (non-DEHP) Compliant, RoHS Compliant, ADCF Compliant.

**Temperature range:** -100 to 275°F (-73 to 135°C)

**Sterilize:** Autoclave, ethylene oxide, or gamma irradiation.

Buy More...Save More!

20% off on 20+  
15% off on 10 to 19  
10% off on 4 to 9 packs



ANIMAL DERIVED  
INGREDIENT FREE

Tubing size	Hose barb in. (mm)	25 ft/pack		Spool		
		Catalog number	Price/pk	Catalog number	Ft/spool	Price/spool
<b>L/S® Precision pump tubing</b>						
L/S 13	1/16 (1.6)	<a href="#">GH-06424-13</a>		<a href="#">GH-06427-13</a>	400	
L/S 14	1/16 (1.6)	<a href="#">GH-06424-14</a>		<a href="#">GH-06427-14</a>	400	
L/S 16	1/8 (3.2)	<a href="#">GH-06424-16</a>		<a href="#">GH-06427-16</a>	400	
L/S 25	3/16 (4.8)	<a href="#">GH-06424-25</a>		<a href="#">GH-06427-25</a>	400	
L/S 17	1/4 (6.4)	<a href="#">GH-06424-17</a>		<a href="#">GH-06427-17</a>	400	
L/S 18	3/8 (9.5)	<a href="#">GH-06424-18</a>		<a href="#">GH-06427-18</a>	400	
<b>L/S® High-Performance Precision pump tubing</b>						
L/S 15	3/16 (4.8)	<a href="#">GH-06424-15</a>		<a href="#">GH-06427-15</a>	400	
L/S 24	1/4 (6.4)	<a href="#">GH-06424-24</a>		<a href="#">GH-06427-24</a>	400	
L/S 35	3/8 (9.5)	<a href="#">GH-06424-35</a>		<a href="#">GH-06427-35</a>	400	
L/S 36	3/8 (9.5)	<a href="#">GH-06424-36</a>		<a href="#">GH-06427-36</a>	400	
<b>I/P® Precision pump tubing</b>						
I/P 26	1/4 (6.4)	<a href="#">GH-06424-26</a>		<a href="#">GH-06427-26</a>	400	
I/P 73	3/8 (9.5)	<a href="#">GH-06424-73</a>		<a href="#">GH-06427-73</a>	100	
I/P 82	1/2 (12.8)	<a href="#">GH-06424-82</a>		<a href="#">GH-06427-82</a>	100	
<b>I/P® High-Performance Precision pump tubing</b>						
I/P 70	3/8 (9.5)	<a href="#">GH-06424-70</a>		—	—	
I/P 88	1/2 (12.8)	<a href="#">GH-06424-88</a>		—	—	
I/P 89	3/8 (15.9)	<a href="#">GH-06424-89</a>		—	—	
<b>B/T® PerfectPosition™ pump tubing (10-ft/pack)</b>						
B/T 87	3/8 (9.5)	<a href="#">GH-06424-87</a>		—	—	
B/T 91	3/4 (19.1)	<a href="#">GH-06424-91</a>		—	—	

## Masterflex® Tygon® E-LFL Pump Tubing

### Won't age or oxidize



**Applications:** General laboratory use; provides longer life with peristaltic tubing pumps.

**Characteristics:** Long life, fits tightly to glass and metal, bends to small radius curves, nontoxic, and transparent.

**Certifications:** USP Class VI, European Pharmacopoeia (EP 3.2.9), FDA 21 CFR 175.300, EU Food, REACH (non-DEHP) Compliant, RoHS Compliant, ADCF Compliant.

**Temperature range:** -51 to 165°F (-46 to 74°C)

**Sterilize:** Ethylene oxide or autoclave for 30 min at 250°F (121°C), 15 psi (1 bar). After autoclaving, dry at no more than 150°F (66°C) for 2 to 2 1/2 hours.



ANIMAL DERIVED  
INGREDIENT FREE

## Masterflex® PharMed® BPT Tubing

### Forms to your needs



**Applications:** Cell and tissue culture work and pharmaceutical uses. Also good for light-sensitive samples.

**Characteristics:** Nontoxic; nonhemolytic; extremely low permeability; resists acids, alkalies, oxidizing agents, and animal and vegetable oils; heat-sealable, bondable, and formable. Opaque beige.

**Certifications:** USP Class VI, European Pharmacopoeia, (EP 3.2.9), FDA 21 CFR 177.2600, NSF-51, REACH (non-DEHP) Compliant, RoHS Compliant.

**Temperature range:** -60 to 270°F (-51 to 132°C)

**Sterilize:** Autoclave, ethylene oxide, or gamma radiation.

Buy More...Save More!

20% off on 20+  
15% off on 10 to 19  
10% off on 4 to 9 packs



Tubing size	Hose barb in. (mm)	25-ft/pack		Spool		
		Catalog number	Price/pk	Catalog number	Ft/spool	Price/spool
<b>L/S® Precision pump tubing</b>						
L/S 13	1/16 (1.6)	<a href="#">GH-06508-13</a>		<a href="#">GH-95687-13</a>	500	
L/S 14	1/16 (1.6)	<a href="#">GH-06508-14</a>		<a href="#">GH-95687-14</a>	500	
L/S 16	1/8 (3.2)	<a href="#">GH-06508-16</a>		<a href="#">GH-95687-16</a>	500	
L/S 25	3/16 (4.8)	<a href="#">GH-06508-25</a>		<a href="#">GH-95687-25</a>	500	
L/S 17	1/4 (6.4)	<a href="#">GH-06508-17</a>		<a href="#">GH-95687-17</a>	500	
L/S 18	3/8 (9.5)	<a href="#">GH-06508-18</a>		<a href="#">GH-95687-18</a>	500	
<b>L/S® High-Performance Precision pump tubing</b>						
L/S 15	3/16 (4.8)	<a href="#">GH-06508-15</a>		<a href="#">GH-95687-15</a>	400	
L/S 24	1/4 (6.4)	<a href="#">GH-06508-24</a>		<a href="#">GH-95687-24</a>	300	
L/S 35	3/8 (9.5)	<a href="#">GH-06508-35</a>		<a href="#">GH-95687-35</a>	300	
L/S 36	3/8 (9.5)	<a href="#">GH-06508-36</a>		<a href="#">GH-95687-36</a>	100	
<b>I/P® Precision pump tubing</b>						
I/P 26	1/4 (6.4)	<a href="#">GH-06508-26</a>		<a href="#">GH-95687-26</a>	200	
I/P 73	3/8 (9.5)	<a href="#">GH-06508-73</a>		<a href="#">GH-95687-73</a>	150	
I/P 82	1/2 (12.8)	<a href="#">GH-06508-82</a>		<a href="#">GH-95687-82</a>	100	
<b>I/P® High-Performance Precision pump tubing</b>						
I/P 70	3/8 (9.5)	<a href="#">GH-06508-70</a>		<a href="#">GH-95687-70</a>	100	
I/P 88	1/2 (12.8)	<a href="#">GH-06508-88</a>		<a href="#">GH-95687-88</a>	100	
I/P 89	3/8 (15.9)	<a href="#">GH-06508-89</a>		<a href="#">GH-95687-89</a>	100	
<b>B/T® Precision pump tubing</b>						
B/T 88	1/2 (12.8)	—	—	<a href="#">GH-95687-88</a>	100	
B/T 92	1 (25.4)	—	—	<a href="#">GH-95687-92</a>	100	
<b>B/T® High-Performance Precision pump tubing</b>						
B/T 86	3/8 (9.5)	—	—	—	—	
B/T 90	3/4 (19.0)	—	—	<a href="#">GH-95687-90</a>	100	
<b>B/T® PerfectPosition™ pump tubing (10 ft/pack)</b>						
B/T 87	3/8 (9.5)	<a href="#">GH-06507-87</a>		—	—	
B/T 91	3/4 (19.1)	<a href="#">GH-06507-91</a>		—	—	

Tubing size	Hose barb in. (mm)	Catalog number	Ft/pk	Price/pk
<b>L/S® Precision pump tubing</b>				
L/S 13	1/16 (1.6)	<a href="#">GH-06440-13</a>	25	
L/S 14	1/16 (1.6)	<a href="#">GH-06440-14</a>	25	
L/S 16	1/8 (3.2)	<a href="#">GH-06440-16</a>	25	
L/S 25	3/16 (4.8)	<a href="#">GH-06440-25</a>	25	
L/S 17	1/4 (6.4)	<a href="#">GH-06440-17</a>	25	
L/S 18	3/8 (9.5)	<a href="#">GH-06440-18</a>	25	
<b>L/S® High-Performance Precision pump tubing</b>				
L/S 15	3/16 (4.8)	<a href="#">GH-06440-15</a>	25	
L/S 24	1/4 (6.4)	<a href="#">GH-06440-24</a>	25	
L/S 35	3/8 (9.5)	<a href="#">GH-06440-35</a>	25	
L/S 36	3/8 (9.5)	<a href="#">GH-06440-36</a>	25	
<b>I/P® Precision pump tubing</b>				
I/P 26	1/4 (6.4)	<a href="#">GH-06440-26</a>	25	
I/P 73	3/8 (9.5)	<a href="#">GH-06440-73</a>	25	
I/P 82	1/2 (12.8)	<a href="#">GH-06440-82</a>	25	
<b>I/P® High-Performance Precision pump tubing</b>				
I/P 70	3/8 (9.5)	<a href="#">GH-06440-70</a>	25	
I/P 88	1/2 (12.8)	<a href="#">GH-06440-88</a>	25	
I/P 89	3/8 (15.9)	<a href="#">GH-06440-89</a>	25	
<b>B/T® PerfectPosition™ pump tubing</b>				
B/T 87	3/8 (9.5)	<a href="#">GH-06440-87</a>	10	
B/T 91	3/4 (19.0)	<a href="#">GH-06440-91</a>	10	