

### Tubing Accessories

#### Handheld Tubing Cutter

Steel blade coated with PTFE resin produces clean, straight cuts through tubing up to 1 1/4" OD (cuts polyethylene tubing up to 1 1/2" OD). Order carrying pouch and replacement blade separately below.



- [GH-06438-90](#) Handheld tubing cutter
- [GH-06438-81](#) Tubing cutter pouch
- [GH-06438-92](#) Replacement blade for handheld tubing cutter 06438-90

#### Benchtop Tubing Cutter

Steel blade makes right-angle cuts in plastic tubing 1/16" to 5/8" OD.



- [GH-06438-10](#) Benchtop cutter
- [GH-06438-11](#) Replacement blade

#### Plastic Clamp Ties



Perfect for flexible fuel line, water line, and vacuum line applications. Special curved clamp tie head ensures a tight seal. Ties measure 8"L x 0.18"W; maximum diameter of 1 3/4". Black resin resists UV degradation.

- [GH-95615-00](#) Clamp ties, white. 100/pk
- [GH-95615-10](#) Clamp ties, black. 100/pk

#### Stainless Steel Hose Clamps

SS strap and screw housing with a steel screw. Band-type worm drive.



Clamp diameter		Catalog number	Price/pk of 10*
Min	Max		
7/32"	5/8"	<a href="#">GH-06403-11</a>	
1/16"	1 1/4"	<a href="#">GH-06403-12</a>	
13/16"	1 3/4"	<a href="#">GH-06403-13</a>	
1 1/16"	2"	<a href="#">GH-06403-14</a>	
1 5/16"	2 1/4"	<a href="#">GH-06403-15</a>	
2"	2 3/4"	<a href="#">GH-06403-16</a>	
2 3/4"	3 1/2"	<a href="#">GH-06403-21</a>	
3 1/2"	4 3/8"	<a href="#">GH-06403-22</a>	
4 3/8"	5 1/8"	<a href="#">GH-06403-23</a>	
5 1/8"	5 7/8"	<a href="#">GH-06403-24</a>	
5 1/2"	6 1/4"	<a href="#">GH-06403-25</a>	

\*Discounts: Save 10% on 5-24 pks, 15% on 25-99 pks, and 20% on 100+ pks.

#### Cole-Parmer® Plastic Hose Clamps and Kits

Reusable white acetal copolymer or white or black nylon clamps will not rust or corrode. Recommended for continuous use from ambient temperature for the acetal copolymer to 200°F (93°C); ambient temperature for nylon clamps is 180°F (82°C). Clamps are nonconducting and stable in a wide variety of chemicals; black clamps resist UV degradation.

Once set, clamps stay put. To use, just position clamp on hose or tubing bundle and press the jaws together with a pair of pliers. Order clamps individually or in kits. Kits include 170 assorted clamps from 0.228" to 1.405" ID.

- [GH-06832-99](#) White acetal copolymer hose-clamp kit
- [GH-06420-99](#) White nylon hose-clamp kit
- [GH-06430-49](#) Black nylon hose-clamp kit



#### White Acetal Hose Clamps



Inside diameter				Catalog number	Qty/pk	Price/pk**
Decimal inches		Millimeters				
Min	Max	Min	Max			
0.228	0.256	5.8	6.5	<a href="#">GH-06832-01</a>	100	
0.269	0.291	6.8	7.4	<a href="#">GH-95614-00</a>	100	
0.307	0.342	7.8	8.7	<a href="#">GH-06832-03</a>	100	
0.351	0.394	8.9	10.0	<a href="#">GH-06832-02</a>	100	
0.387	0.440	9.8	11.2	<a href="#">GH-95614-01</a>	100	
0.404	0.452	10.3	11.5	<a href="#">GH-06832-04</a>	100	
0.449	0.511	11.4	13.0	<a href="#">GH-06832-06</a>	100	
0.513	0.586	13.0	14.9	<a href="#">GH-06832-08</a>	100	
0.569	0.650	14.5	16.5	<a href="#">GH-06832-10</a>	100	
0.616	0.707	15.7	18.0	<a href="#">GH-06832-12</a>	100	
0.702	0.801	17.8	20.4	<a href="#">GH-06832-14</a>	100	
0.759	0.848	19.3	21.5	<a href="#">GH-06832-16</a>	100	
0.779	0.899	19.8	22.8	<a href="#">GH-06832-18</a>	100	
0.859	0.989	21.8	25.1	<a href="#">GH-06832-20</a>	100	
0.928	1.072	23.6	27.2	<a href="#">GH-06832-22</a>	100	
0.985	1.135	25.0	28.8	<a href="#">GH-06832-24</a>	100	
1.123	1.296	28.5	32.9	<a href="#">GH-06832-28</a>	50	
1.218	1.405	30.9	35.7	<a href="#">GH-06832-32</a>	50	
1.338	1.566	34.0	39.8	<a href="#">GH-06832-34</a>	50	
1.472	1.724	37.4	43.8	<a href="#">GH-06832-36</a>	50	

\*\*Discounts: Save 10% on 4-19 pks, 15% on 20-79 pks, and 20% on 80+ pks.

#### Nylon Hose Clamps

Inside diameter				Qty/pk	White		Black	
Decimal inches		Millimeters			Catalog number	Price/pk**	Catalog number	Price/pk**
Min	Max	Min	Max					
0.246	0.290	5.95	7.5	100	<a href="#">GH-06420-50</a>		<a href="#">GH-06430-07</a>	
0.283	0.312	7.1	7.9	100	<a href="#">GH-06420-52</a>		<a href="#">GH-06430-02</a>	
0.350	0.395	9.1	9.9	100	<a href="#">GH-06420-56</a>		<a href="#">GH-06430-06</a>	
0.360	0.410	9.3	10.5	100	<a href="#">GH-06420-58</a>		<a href="#">GH-06430-08</a>	
0.430	0.480	11.11	12.3	100	<a href="#">GH-06420-60</a>		<a href="#">GH-06430-10</a>	
0.500	0.545	12.7	13.8	100	<a href="#">GH-06420-62</a>		<a href="#">GH-06430-12</a>	
0.525	0.605	13.3	15.4	100	<a href="#">GH-06420-64</a>		<a href="#">GH-06430-14</a>	
0.580	0.660	15.0	16.9	100	<a href="#">GH-06420-66</a>		<a href="#">GH-06430-16</a>	
0.650	0.750	16.6	19.0	100	<a href="#">GH-06420-68</a>		<a href="#">GH-06430-18</a>	
0.750	0.875	19.05	22.2	100	<a href="#">GH-06420-70</a>		<a href="#">GH-06430-20</a>	
0.779	0.899	19.7	22.6	100	<a href="#">GH-06420-72</a>		<a href="#">GH-06430-22</a>	
0.859	0.989	21.8	25.0	100	<a href="#">GH-06420-74</a>		<a href="#">GH-06430-44</a>	
0.900	0.989	23.0	25.0	100	<a href="#">GH-06420-76</a>		<a href="#">GH-06430-26</a>	
0.990	1.135	25.0	28.5	100	<a href="#">GH-06420-78</a>		<a href="#">GH-06430-28</a>	
1.123	1.296	28.5	32.9	50	<a href="#">GH-06420-80</a>		<a href="#">GH-06430-30</a>	
1.250	1.425	31.7	35.9	50	<a href="#">GH-06420-82</a>		<a href="#">GH-06430-32</a>	
1.406	1.610	35.7	40.8	50	<a href="#">GH-06420-84</a>		<a href="#">GH-06430-34</a>	
1.593	1.812	40.4	46.0	50	<a href="#">GH-06420-86</a>		<a href="#">GH-06430-36</a>	
1.790	2.110	45.6	53.5	50	<a href="#">GH-06420-88</a>		<a href="#">GH-06430-38</a>	
1.870	2.125	47.0	52.0	50	<a href="#">GH-06420-90</a>		<a href="#">GH-06430-40</a>	
2.119	2.390	53.5	60.7	25	<a href="#">GH-06420-92</a>		<a href="#">GH-06430-42</a>	

\*\*Discounts: Save 10% on 4-19 pks, 15% on 20-79 pks, and 20% on 80+ pks.