

Cole-Parmer® Disposable Polyethylene, PVC, and FEP Bailers

Easy tie-off, greater water flow, and improved sink rate

- Individually weighted and sealed bailers are cleaned and rinsed with deionized water before packaging

These disposable bailers feature tapered ends and low-snap cord cleat to reduce hang-ups and snags. The angled nozzle ensures positive check-valve control. Choose from virgin polyethylene construction for strength and durability, virgin PVC for strength and economy of polyethylene with transparent features of FEP, or virgin FEP construction for high-purity applications. Double check-valve bailers allow you to sample from specific depth (point-source sampling).



Polyethylene bailers are opaque; PVC and FEP bailers are clear.



QuickFilter® Groundwater Filter

Disposable 0.45-µm filter cartridge with polyethersulfone membrane. Filter has

bailer interface tube for direct connection to bottom of bailer. Gravity forces water through the filter into your sample container.

[GH-99157-50](#) QuickFilter groundwater filter



All bailers have metal inserts for faster sink rate



Length in. (cm)	Outside diameter in. (cm)	Number of check valves	Qty/cs	Catalog number	Price/cs*
Polyethylene bailers					
12 (30.5)	1.6 (4.06)	One	24	GH-99157-00	
		Two		GH-99157-01	
36 (91.4)	0.5 (1.27)	One	24	GH-99157-20	
		Two		GH-99157-21	
36 (91.4)	0.75 (1.91)	One	24	GH-99157-30	
		Two		GH-99157-32	
36 (91.4)	1.6 (4.06)	One	24	GH-99157-02	
		Two		GH-99157-03	
48 (121.9)	1.6 (4.06)	One	24	GH-99157-04	
		Two		GH-99157-05	
PVC bailers					
12 (30.5)	1.6 (4.06)	One	24	GH-99157-40	
36 (91.4)				GH-99157-42	
48 (121.9)				GH-99157-44	
FEP bailers					
36 (91.4)	0.5 (1.27)	One	12	GH-99157-23	
		Two		GH-99157-24	
36 (91.4)	1.6 (4.06)	One	12	GH-99157-12	
		Two		GH-99157-13	

*Discounts: Save 10% on 5-9 cases and 15% on 10+ cases, in any assortment.

Slow Emptying Devices

Reduces flow from bailer, minimizing agitation for VOC analysis.

Use for bailers	Catalog number	Price**
99157-00, -01, -02, -03, -04, -05, -40, -42, -44	GH-99157-06	
99157-12, -13	GH-99157-16	
99157-20, -21	GH-99157-22	
99157-23, -24	GH-99157-25	

**Discounts: Save 10% on 5-9 emptying devices and 15% on 10+ emptying devices.

Reusable Bailers

Sink fast for quicker sampling

PVC Bailers consist of a 3-ft (0.9-m) body and a detachable bottom piece with ball valve that lets water in when sampling; seals liquid in when retrieving. Order appropriate emptying devices and optional bailer extensions in table. Polyester suspension cord is available below.

Type	Three-foot bailers				One-foot extensions				Emptying devices	
	OD	Volume	Cat. no.	Price	Volume	Cat. no.	Price	Cat. no.	Price	
Opaque	1.05"	285 mL	GH-05484-10		—	—		GH-05484-70		
	1.66"	840 mL	GH-05484-12		280 mL	GH-05484-42		GH-05484-72		
	2.375"	1935 mL	GH-05484-14		645 mL	GH-05484-44		—		
Transparent	1.05"	285 mL	GH-05484-15		—	—		GH-05484-70		
	1.66"	840 mL	GH-05484-17		—	—		GH-05484-72		
	3.5"	4170 mL	GH-05484-19		—	—		—		


FEP Bailers are available in two styles and lengths. Economy bailers have a 1¼" (4.4 cm) OD and feature a fixed top and bottom ball valve. Standard bailers have a 1⅞" (4.8 cm) OD and feature interchangeable top and bottom cap configurations. Order polyester suspension cord below.

Length	Cap configurations (top/bottom)	OD	Volume	Catalog number	Price
Economy bailers					
1 ft (0.3 m)	Fixed/ball	1¼" (4.4 cm)	350 mL	GH-05497-60	
3 ft (0.9 m)			1050 mL	GH-05497-65	
Standard bailers					
1 ft (0.3 m)	Standard/standard	1⅞" (4.8 cm)	350 mL	GH-05497-00	
3 ft (0.9 m)			1050 mL	GH-05497-05	
1 ft (0.3 m)	Standard/bottom emptying	1⅞" (4.8 cm)	350 mL	GH-05497-10	
3 ft (0.9 m)			1050 mL	GH-05497-15	
1 ft (0.3 m)	Standard/controlled flow	1⅞" (4.8 cm)	350 mL	GH-05497-20	




Economy FEP bailer 05497-60

Standard FEP bailer 05497-00



Transparent PVC bailer 05484-17



Opaque PVC bailer 05484-14

Polyester Suspension Cord is used to lower and retrieve bailers. Maximum working load is 110 lb (50 kg), 3/16" (0.5 cm) dia. Measures 100 ft (30.5 m) long.

[GH-05499-35](#) Suspension cord