

Cleanroom Swabs

Meet your validation requirements

– Ideal for cleaning small surface areas and for cleaning validation

Sealed swab handles are thermo-formed. Swabs with ESD handles eliminate damage from static electricity and are effective in all humidities.

Fabric Swabs have excellent chemical compatibility. Sealed swabs contain low chloride and other ionic contaminants.

Foam Swabs have sealed handles and are constructed from 100 pores per inch reticulated urethane foam—ideal for solvent dispersion and low-viscosity adhesives. Sealed foam swabs are perfect for removal of solvents and fluxes. Cleanfoam® swabs feature low levels of nonvolatile residue, particle generation, and are constructed of open-cell polyurethane foam for excellent solvent capacity.

Swab tip	Tip description	Handle description	Tip length	Swab length	Compliance	Qty/pk	Catalog number	Price/pk
Fabric swabs								
	Knit polyester	Sealed polypropylene	0.39" (1 cm)	2.75" (7 cm)	—	50	GY-33676-01	
	Knit polyester	Sealed polypropylene	0.66" (1.7 cm)	6.39" (16.2 cm)	—	100	GY-33676-07	
	Knit polyester	Sealed polypropylene	0.16" (0.4 cm)	2.76" (7 cm)	ISO Class 3	500	GY-33677-58	
	Knit polyester	Sealed polypropylene	0.27" (0.7 cm)	6.39" (16.2 cm)	ISO Class 3	100	GY-33677-60	
	Knit polyester	Sealed polypropylene	0.5" (1.3 cm)	5.00" (12.7 cm)	ISO Class 3	100	GY-33677-62	
	Knit polyester	Sealed polypropylene	0.5" (1.3 cm)	5.00" (12.7 cm)	—	100	GY-33677-63	
	Knit polyester	Sealed polypropylene	1.01" (2.6 cm)	5.02" (12.8 cm)	—	20	GY-33677-64	
	Knit polyester	Sealed polypropylene	1.01" (2.6 cm)	5.02" (12.8 cm)	—	20	GY-33677-65	
Foam swabs								
	Foam bud	Hardwood	1.10" (2.8 cm)	6.06" (15.4 cm)	—	500	GY-33676-03	
	Cleanfoam	Polypropylene	0.13" (0.3 cm)	2.75" (7 cm)	ISO Class 5	500	GY-33677-50	
	Flexible cleanfoam	Polypropylene	0.13" (0.3 cm)	2.67" (6.8 cm)	ISO Class 5	500	GY-33677-52	
	Cleanfoam	Polypropylene	0.25" (0.6 cm)	6.37" (16.2 cm)	ISO Class 5	500	GY-33677-55	
	Circular foam	Sealed polypropylene	0.81" (2.1 cm)	5.20" (13.2 cm)	ISO Class 5	100	GY-33677-56	
	Cleanfoam	ESD	0.14" (0.4 cm)	3.50" (8.9 cm)	ISO Class 5	500	GY-33677-72	
	Cleanfoam	ESD	0.15" (0.4 cm)	2.75" (7 cm)	ISO Class 5	500	GY-33677-74	

Critical Task Wipes

Low-lint, absorbent, soft, and nonabrasive

- Won't scratch delicate surfaces
- Single- and two-ply delicate task wipes are made of a finely textured tissue
- Solvent-resistant KimTech CL4 wipes are made of a single-ply, nonwoven fabric specially bonded to eliminate surface fibers and trap particles

Description	Compliance	Wipe size	Qty/bx	Box/cs	Cat. no.	Price/cs
Delicate task wipes						
Kimwipes® EX-L, 1 ply	—	4 1/2" x 8 1/2"	280	60	GY-33670-04	
		15" x 16 3/4"	140	15	GY-33670-06	
Kaydry® EX-L, 2 ply	—	15" x 16 3/4"	90	15	GY-33670-10	
Cleanroom wipes						
Kimtech CL4 Cleanroom	ISO Class 4	12" x 12"	100	5	GY-33670-20	

