

Vacuum Desiccator, PC

Won't shatter

- Easily view samples through transparent material
- No need to grease silicone O-ring
- Holds maximum vacuum of 28" Hg for 24 hours
- Order desiccator plate separately



Plate dia (mm)	Total height (mm)	Clearance above plate (mm)	Qty/pk	Catalog number	Price/pk
230	330	195	1	GY-06520-05	

[GY-06521-00](#) Desiccator plate; ceramic metal, 230 mm dia
[GY-06520-06](#) Replacement stopcock

Vacuum Desiccators, PP/PC

No need for grease

- Maximize interior space with high crowned lid
- Control vacuum draw via stopcock, holds 29" Hg for 24 hours
- Includes perforated plate
- Room temperature use only—do not autoclave



Plate dia (mm)	Total height (mm)	Clearance above plate (mm)	Qty/pk	Catalog number	Price/pk
140	206	122	1	GY-06514-10	
190	260	157		GY-06514-20	
230	311	198		GY-06514-30	

Large-Capacity Vacuum Desiccator, PC

Store four times more than other desiccators

- Remains airtight even if not under pressure for extended period
- Holds maximum vacuum of 29" Hg at room temperature for 24 hours
- Maximize storage with two polypropylene sleeves, or remove for awkward items
- Halves nest inside each other for easy storage



Holding capacity	Inside dia	Total height	Catalog number	Price
65 L (4000 cu. in.)	20" (50.8 cm)	18" (45.7 cm)	GY-06514-50	

[GY-06514-51](#) Vacuum pressure indicator. Plastic bellows type; no tools needed to install
[GY-06514-52](#) Replacement stopcock

Vacuum Desiccators, Glass

Pull more vacuum

- Holds maximum vacuum of 29.9" Hg
- No need for grease to create tight seal
- Order desiccator plate separately

Warning: Do not heat or subject to pressure.



Plate dia (mm)	Bowl capacity	Total height (mm)	Clearance above plate (mm)	Catalog number	Price
140	2400 mL	239	81	GY-34548-27	
190	5800 mL	296	115	GY-34548-28	
230	10,500 mL	344	120	GY-34548-29	

[GY-06518-30](#) Desiccator plate; porcelain, 140 mm dia
[GY-06518-40](#) Desiccator plate; porcelain, 190 mm dia
[GY-06518-50](#) Desiccator plate; porcelain, 230 mm dia

Wait!

There's More at ColeParmer.com

Find more than **100,000** products to choose from!