


Barbed Fittings (continued)

Barbed fittings are designed for quick and easy assembly without tools. Combine these simple, economical fittings with our flexible tubing for use in your low-pressure applications (generally less than 30 psi). Order tubing on pages 988–1017.

For material descriptions, refer to page 302.

NPT male threaded adapters (continued)



BA PFA




BB Brass




BC 316 SS

UNF male threaded adapters



BD HDPE

BE Nylon



BF PP

BG Clear PP



BH PVDF

UNF male threaded adapter elbows



BI 316 SS

Tubing ID	Material	Key	Catalog number	Qty/pk	Price/pk
NPT male threaded adapters, NPT(M) x tubing ID—cont.					
3/8" x 3/8"	HDPE	AU	GY-30621-62	10	
3/8" x 3/8"	Nylon	AV	GY-30621-63	10	
3/8" x 3/8"	PP	AX	GY-40610-42	10	
3/8" x 3/8"	PVDF	AZ	GY-30704-15	10	
3/8" x 3/8"	PFA	BA	GY-06383-94	1	
3/8" x 3/8"	Brass	BB	GY-30904-21	5	
3/8" x 3/8"	316 SS	BC	GY-31208-86	1	
3/8" x 1/2"	HDPE	AU	GY-30621-64	10	
3/8" x 1/2"	Nylon	AV	GY-30621-65	10	
3/8" x 1/2"	PP	AX	GY-40610-43	10	
3/8" x 1/2"	PVDF	AZ	GY-30704-16	10	
3/8" x 1/2"	Brass	BB	GY-30904-22	5	
1/2" x 3/8"	HDPE	AU	GY-31702-18	10	
1/2" x 1/4"	HDPE	AU	GY-30621-73	10	
1/2" x 1/4"	Nylon	AV	GY-30621-74	10	
1/2" x 1/4"	PP	AX	GY-40610-44	10	
1/2" x 1/4"	PVDF	AZ	GY-30704-17	10	
1/2" x 1/4"	316 SS	BC	GY-31210-30	1	
1/2" x 3/8"	HDPE	AU	GY-30621-75	10	
1/2" x 3/8"	Nylon	AV	GY-30621-76	10	
1/2" x 3/8"	PP	AX	GY-40610-45	10	
1/2" x 3/8"	PVDF	AZ	GY-30704-18	10	
1/2" x 3/8"	Brass	BB	GY-30904-31	5	
1/2" x 3/8"	316 SS	BC	GY-31210-31	1	
1/2" x 1/2"	HDPE	AU	GY-30621-77	10	
1/2" x 1/2"	Nylon	AV	GY-30621-78	10	
1/2" x 1/2"	PP	AX	GY-40610-46	10	
1/2" x 1/2"	PVDF	AZ	GY-30704-19	10	
1/2" x 1/2"	Brass	BB	GY-30904-32	5	
1/2" x 1/2"	316 SS	BC	GY-31210-32	1	
1/2" x 5/8"	HDPE	AU	GY-30621-66	10	
1/2" x 5/8"	Nylon	AV	GY-30621-68	10	
1/2" x 5/8"	PP	AX	GY-40621-69	10	
1/2" x 5/8"	PVDF	AZ	GY-30621-67	5	
1/2" x 5/8"	Brass	BB	GY-30904-52	5	
1/2" x 5/8"	316 SS	BC	GY-31210-33	1	
1/2" x 3/4"	HDPE	AU	GY-30621-70	10	
1/2" x 3/4"	Nylon	AV	GY-30621-72	10	
1/2" x 3/4"	PP	AX	GY-40610-47	10	
1/2" x 3/4"	PVDF	AZ	GY-30621-71	5	
1/2" x 3/4"	316 SS	BC	GY-31210-34	1	
3/4" x 3/8"	HDPE	AU	GY-30621-18	10	
3/4" x 3/8"	Nylon	AV	GY-30621-19	10	
3/4" x 3/8"	PP	AX	GY-40610-49	5	
3/4" x 3/8"	PVDF	AZ	GY-30704-22	5	
3/4" x 3/8"	Brass	BB	GY-30904-53	5	
3/4" x 1/4"	HDPE	AU	GY-30621-16	10	
3/4" x 1/4"	Nylon	AV	GY-30621-17	10	
3/4" x 1/4"	PP	AX	GY-40610-48	5	
3/4" x 1/4"	PVDF	AZ	GY-30704-21	5	
3/4" x 1/2"	HDPE	AU	GY-30621-20	10	
3/4" x 1/2"	Nylon	AV	GY-30621-21	10	
3/4" x 1/2"	PP	AX	GY-40610-50	5	
3/4" x 1/2"	PVDF	AZ	GY-30704-23	5	
3/4" x 1/2"	Brass	BB	GY-30904-42	5	
3/4" x 5/8"	HDPE	AU	GY-30621-08	10	
3/4" x 5/8"	Nylon	AV	GY-30621-10	10	
3/4" x 5/8"	PP	AX	GY-40621-11	10	
3/4" x 5/8"	PVDF	AZ	GY-30621-09	5	
3/4" x 5/8"	Brass	BB	GY-30904-54	5	
3/4" x 3/4"	HDPE	AU	GY-30621-12	10	
3/4" x 3/4"	Nylon	AV	GY-30621-13	10	
3/4" x 3/4"	PP	AX	GY-40610-51	5	
3/4" x 3/4"	PVDF	AZ	GY-30704-24	5	

Tubing ID	Material	Key	Catalog number	Qty/pk	Price/pk
NPT male threaded adapters, NPT(M) x tubing ID—cont.					
3/4" x 3/4"	Brass	BB	GY-30904-44	5	
3/4" x 3/4"	316 SS	BC	GY-31210-44	1	
3/4" x 1"	HDPE	AU	GY-30621-14	10	
3/4" x 1"	Nylon	AV	GY-30621-15	10	
3/4" x 1"	PP	AX	GY-40610-52	5	
3/4" x 1"	PVDF	AZ	GY-30704-25	5	
3/4" x 1"	Brass	BB	GY-30904-55	5	
3/4" x 1"	316 SS	BC	GY-31210-45	1	
1" x 3/4"	Nylon	AV	GY-31702-00	10	
1" x 3/4"	316 SS	BC	GY-31210-50	1	
1" x 1"	HDPE	AU	GY-31517-18	10	
1" x 1"	Nylon	AV	GY-30401-34	10	
1" x 1"	PP	AX	GY-40610-53	5	
1" x 1"	PVDF	AZ	GY-30704-26	5	
1" x 1"	316 SS	BC	GY-31210-51	1	
1" x 1 1/4"	Nylon	AV	GY-31408-12	5	
1" x 1 1/4"	Black PP	AW	GY-31407-12	5	
1 1/4" x 1"	Nylon	AV	GY-31408-13	5	
1 1/4" x 1"	Black PP	AW	GY-31407-13	5	
1 1/4" x 1 1/4"	Nylon	AV	GY-31408-14	5	
1 1/4" x 1 1/4"	Black PP	AW	GY-31407-14	5	
1 1/4" x 1 1/4"	316 SS	BC	GY-31210-60	1	
1 1/4" x 1 1/2"	Black PP	AW	GY-31407-15	5	
1 1/2" x 1 1/4"	Nylon	AV	GY-31408-17	5	
1 1/2" x 1 1/4"	Black PP	AW	GY-31407-17	5	
1 1/2" x 1 1/2"	Nylon	AV	GY-31408-16	5	
1 1/2" x 1 1/2"	Black PP	AW	GY-31407-16	5	
1 1/2" x 1 1/2"	316 SS	BC	GY-31210-61	1	
1 1/2" x 2"	Nylon	AV	GY-31408-18	5	
1 1/2" x 2"	Black PP	AW	GY-31407-18	5	
2" x 1 1/2"	Nylon	AV	GY-31408-19	5	
2" x 1 1/2"	Black PP	AW	GY-31407-19	5	
2" x 2"	Nylon	AV	GY-31408-20	5	
2" x 2"	Black PP	AW	GY-31407-20	5	
2" x 2"	316 SS	BC	GY-31210-70	1	
UNF male threaded adapters, UNF(M) x tubing ID					
10-32 x 1/16"	HDPE	BD	GY-30621-02	10	
10-32 x 1/16"	Nylon	BE	GY-30621-03	25	
10-32 x 1/16"	PP	BF	GY-40621-04	25	
10-32 x 1/16"	PVDF	BD	GY-30704-80	10	
10-32 x 3/32"	HDPE	BB	GY-30629-00	10	
10-32 x 3/32"	Nylon	BE	GY-30621-00	25	
10-32 x 3/32"	PP	BF	GY-40621-01	25	
10-32 x 3/32"	PVDF	BH	GY-30704-81	10	
10-32 x 1/8"	HDPE	BD	GY-30621-05	10	
10-32 x 1/8"	Nylon	BE	GY-30621-06	10	
10-32 x 1/8"	PP	BF	GY-40621-07	25	
10-32 x 1/8"	PVDF	BD	GY-30704-82	10	
10-32 x 5/32"	Nylon	BE	GY-31500-53	25	
10-32 x 5/32"	Clear PP	BG	GY-31501-53	25	
10-32 x 5/32"	PVDF	BH	GY-30704-83	10	
1/4-28 x 1/16"	PVDF	BH	GY-30704-84	10	
1/4-28 x 3/32"	PVDF	BH	GY-30704-85	10	
1/4-28 x 1/8"	Nylon	BE	GY-31500-54	25	
1/4-28 x 1/8"	Clear PP	BG	GY-31501-54	25	
1/4-28 x 1/8"	PVDF	BH	GY-30704-86	10	
1/4-28 x 5/32"	PVDF	BH	GY-30704-87	10	
1/4-28 x 3/16"	PVDF	BH	GY-30704-88	10	
1/4-28 x 1/4"	Nylon	BE	GY-31500-55	25	
1/4-28 x 1/4"	Clear PP	BG	GY-31501-55	25	
UNF male threaded adapter elbows, UNF(M) x tubing ID					
10-32 x 1/16"	316 SS	BI	GY-31209-45	1	
10-32 x 1/8"	316 SS	BI	GY-31209-46	1	