

## General Protocol Incubators

### No more difficult setting of parameters

- Corrosion-resistant stainless steel interior
- Internal glass door allows sample viewing without disturbing temperature

These gravity convection incubators provide top-quality temperature uniformity, ranging from 5°C above ambient to 75°C. A unique airflow design, advanced microprocessor control, and automatic overtemperature alarm ensure that an optimal environment is maintained.

**What's included:** two adjustable stainless steel shelves and power cord.

**ISO9001:2008**  
CERTIFIED SUPPLIER



Capacity cu ft (L)	Temperature range	Accuracy at 37°C	Temperature uniformity at 37°C	Dimensions (W x H x D)		Shelf positions	Shelves included	VAC, Hz	Shpg wt lb (kg)	Catalog number	Price
				Chamber	Overall						
2.6 (75)	+5°C to 75°C	±0.2°C	±0.6°C	14" x 20" x 16¼" (35.4 x 50.8 x 41.4 cm)	20⅞" x 28⅜" x 22⅝" (53 x 72 x 56.5 cm)	13	2	120,60	88 (40.0)	<a href="#">GY-38800-02</a>	
4.0 (117)	+5°C to 75°C	±0.2°C	±0.6°C	18¼" x 24" x 16¼" (46.4 x 60.8 x 41.4 cm)	25¼" x 32¼" x 22⅝" (64 x 82 x 56.5 cm)	16	2	120,60	112 (50.9)	<a href="#">GY-38800-04</a>	
6.85 (194)	+5°C to 75°C	±0.2°C	±0.6°C	18¼" x 27⅞" x 23⅞" (46.4 x 70.8 x 58.9 cm)	25¼" x 36¼" x 29" (64 x 92 x 73.8 cm)	19	2	120,60	143 (64.9)	<a href="#">GY-38800-06</a>	
14.3 (405)	+5°C to 75°C	±0.4°C	±0.4°C	21⅞" x 51½" x 22⅞" (54.4 x 130.7 x 56.9 cm)	30⅞" x 60⅞" x 30⅞" (77.8 x 154.5 x 77 cm)	39	2	120,60	320 (145)	<a href="#">GY-38800-03</a>	
26.4 (747)	+5°C to 75°C	±0.4°C	±1.3°C	39½" x 51½" x 22⅞" (100.4 x 130.7 x 56.9 cm)	49¾" x 60⅞" x 30⅞" (126.1 x 154.5 x 77 cm)	39	2	120,60	443 (201)	<a href="#">GY-38800-05</a>	

## Digital Mechanical Convection Incubators

### Monitor and control remotely

- RS-232 communication interface and software for remote PC control
- CLS (customer logical safe)—control system thermal safety features
- Fine tune the PID temperature control with auto-tuning feature
- Electronic programmable timer for setting start and stop automatically

**What's included:** RS-232 cable and software, two wired shelves, and 6-ft (1.8-m) power cord.



#### Specifications

Temperature range: 5° above ambient to 75°C      Accuracy at 40°C: ±0.1°C      Uniformity at 40°C: ±0.4°C

Capacity cu ft (L)	Dimensions (W x H x D)		Shelf positions	Shelves included	VAC, Hz	Shpg wt lb (kg)	Catalog number	Price	Wire shelves		Perforated shelves	
	Chamber	Overall							Cat. no.	Price	Cat. no.	Price
2.1 (59.5)	15¾" x 16½" x 14¼" (40 x 41.9 x 36.2 cm)	23½" x 29¼" x 21¾" (59.7 x 74.3 x 55.2 cm)	8	2	120,60 240,50/60	99 (45)	<a href="#">GY-79510-02</a>		<a href="#">GY-79510-04</a>		<a href="#">GY-79510-06</a>	
							<a href="#">GY-79510-00</a>					
3.7 (104.8)	19" x 20½" x 16" (48.3 x 52.1 x 40.6 cm)	26½" x 33½" x 23¾" (67.3 x 85.1 x 60.3 cm)	12	2	120,60 240,50/60	121 (55)	<a href="#">GY-79510-10</a>		<a href="#">GY-79510-12</a>		<a href="#">GY-79510-14</a>	
							<a href="#">GY-79510-08</a>					
5.4 (152.9)	24" x 21¼" x 18" (61 x 54 x 45.7 cm)	31½" x 34¾" x 25¾" (80 x 88.3 x 65.4 cm)	12	2	120,60 240,50/60	137 (62)	<a href="#">GY-79510-18</a>		<a href="#">GY-79510-20</a>		<a href="#">GY-79510-22</a>	
							<a href="#">GY-79510-16</a>					

## Advanced Protocol Incubators

### Put equipment right inside

- Internal socket allows the use of other lab equipment inside the unit
- Microprocessor control with vacuum fluorescent display

Dual convection allows for different applications; fan speed is adjustable from 0 to 100%. Corrosion-resistant stainless steel interior is easy to clean and internal glass door allows sample viewing without impacting temperature. Digital timer can be set for daily or weekly on/off cycles. Small footprint saves space in your lab.

**What's included:** two adjustable stainless steel shelves and power cord.

**ISO9001:2008**  
CERTIFIED SUPPLIER



Capacity cu ft (L)	Accuracy at 37°C	Temperature range	Temperature uniformity at 37°C	Dimensions (W x H x D)		Shelf positions	Shelves included	VAC, Hz	Shpg wt lb (kg)	Catalog number	Price
				Chamber	Overall						
2.3 (66)	±0.1°C	5°C above ambient to 105°C	±0.6°C	13⅞" x 20" x 14½" (35.4 x 50.8 x 36.8 cm)	20⅞" x 28⅞" x 22¼" (53 x 72 x 56.5 cm)	13	2	120,60	99 (45)	<a href="#">GY-38800-08</a>	
3.67 (104)	±0.1°C		±0.6°C	18⅞" x 23⅞" x 14½" (46.4 x 60.8 x 36.8 cm)	25¼" x 32⅞" x 22¼" (64 x 82 x 56.5 cm)	16	2	120,60	123 (56)	<a href="#">GY-38800-10</a>	
6.3 (178)	±0.1°C		±0.6°C	18⅞" x 27⅞" x 21⅞" (46.4 x 70.8 x 54.3 cm)	25¼" x 36¼" x 29" (64 x 92 x 73.8 cm)	19	2	120,60	154 (70)	<a href="#">GY-38800-12</a>	