

Faucet-Mount Eyewash

Ensure safety and keep a working faucet



- Single actuator pin activates eyewash
- Steady water flow to sprayheads even under varying water supply conditions
- Chrome-plated brass pipe and fittings

Compliance: ANSI Z358.1-2004, SEI certified

Description	Catalog number	Price
Faucet-mount eyewash	GY-86000-22	

Wait! There's More...

Eye protection products, see pages 820-821.



Eyewash Bowls

Never lose dust covers again!

- Flag handle activation of a stay-open valve
- 11½"-dia (29 cm) bowl acts like a sink to drain water away
- Available in wall-mount or pedestal models

What's included: ANSI-compliant identification sign.

Compliance: ANSI Z358.1-2004



06767-15



06767-17

Description	Material	Catalog number	Price
Wall mount	ABS plastic	GY-06767-15	
Wall mount	Stainless steel	GY-06767-16	
Wall mount with cover	Stainless steel	GY-06767-17	

[GY-06767-19](#) Pedestal with foot pedal

Portable Pressurized Eyewash with Drench Hose

On-site emergency relief where you need it

- Includes 8-ft (2.4-m) yellow, reinforced thermoplastic drench hose
- Stainless steel tank features tire filler valve with 0 to 160 psi air gauge
- Pressure relief valve prevents over-pressurization

Flow rates: eyewash exceeds minimum 0.4 GPM at 30 psi; drench hose exceeds minimum 3 GPM at 30 psi.

Compliance: ANSI Z358.1-2004



Capacity	Dimensions (H x dia)	Weight empty/full	Catalog number	Price
5 gal. (19 L)	27½" x 8½" (70 x 21.6 cm)	14 lb/43 lb (6.4 kg/19.5 kg)	GY-86000-08	
10 gal. (38 L)	25¼" x 12¼" (64 x 31 cm)	23 lb/86 lb (10.4 kg/39 kg)	GY-86000-10	
15 gal. (57 L)	35⅜" x 12¼" (90.5 x 31 cm)	28 lb/103 lb (12.7 kg/46.7 kg)	GY-86000-12	

[GY-86000-19](#) Optional four wheel cart

Eyewash Solutions

Improve performance and protect users

- One bottle of either solution sufficient for 14-16 gallons (53-60 L)
- Eyesaline® pH balanced to relieve eyes and reduce likelihood of additional eye injury
- De-fend® inhibits bacterial growth
- 2-year shelf life, lot and date controlled



Description	Volume	Catalog number	Price
pH balanced, bacteria-inhibiting saline solution	180 oz	GY-06796-64	
Bacteria-inhibiting eyewash preservative	8 oz	GY-06796-66	