

Earplugs

Protect your hearing

Photo	ANSI approval/compliance	Plug features	NRR	Size	Cord options	Pairs/bx	Catalog number	Price per box
 <p>TaperFit® 2</p>	S3.19-1974	Tapered shape for easy removal. Made of soft polyurethane. Individually wrapped by pairs in poly bags.	32 dB	Regular	Uncorded	200	GY-48491-10	
 <p>Yellow Neon</p>	S3.19-1974	Made of soft foam to provide the highest NRR available. Bright yellow neon color makes monitoring use easy.	33 dB	Regular	Uncorded	200	GY-48491-60	
 <p>Push-Ins™</p>	S3.19-1974, CSA A(L)	Unique stem design allows you to simply push plug in and go. Small diameter and soft outer skin enhance wearer comfort. Individually wrapped by pairs in poly bags.	28 dB	One size fits all	Uncorded	200	GY-48491-80	
 <p>Foam</p>	S3.19-1974, CSA A(L)	Soft foam, tapered earplugs conform to the unique shape of each ear for excellent hearing protection and comfort, and are hypo-allergenic. The soft smooth foam seals the ear comfortably while resisting dirt for hygiene.	29 dB	One size fits all	Uncorded	200	GY-83111-00	
 <p>Max®</p>	S3.19-1974, CSA A(L)	Smooth, pre-shaped polyurethane foam with soil resistant skin. High attenuation for maximum protection. Individually wrapped by pairs in poly bags.	33 dB	One size fits all	Uncorded	200	GY-86310-00	
					Corded	100	GY-86310-01	
 <p>Laser Lite®</p>	S3.19-1974, CSA A(L)	Low-pressure polyurethane foam expands gently inside the ear canal for comfortable long-term wear. Contoured T-shape delivers easy handling. High-visibility magenta and yellow colors make compliance checks quick and easy.	32 dB	One size fits all	Uncorded	200	GY-86310-39	
 <p>Max-Lite®</p>	S3.19-1974, CSA A(L)	Low pressure for long-term comfort. Self-adjusting to fit any ear. Non-irritating and non-allergenic. Individually wrapped by pairs in poly bags.	30 dB	One size fits all	Uncorded	200	GY-86310-70	
					Corded	100	GY-86310-71	
 <p>AirSoft® 2</p>	S3.19-1974, CSA A(L)	A soft shell of attenuating material surrounds a cushion of air for superior comfort. Packaged in convenient flip-top box.	27 dB	One size fits all	Corded	100	GY-86310-31	