

## Cole-Parmer® Rocking Platform Shakers

### Shake at the speed and angle you need

- Designed to function in temperature controlled environments from 4 to 65°C and 85% humidity
- Platform rocks from 4 to 160 tilts per minute
- Degree of tilt is adjustable  $\pm 20^\circ$
- Solid-state speed control ensures speed remains constant

**What's included:** UL-listed power supply. The 115 VAC models have a 4-ft (1.2-m) power cord with US standard plug; 230 VAC models have a 5-ft (1.5-m) cord with European plug.

#### Specifications

**Speed range:** 4 to 160 oscillations per minute **Maximum load:** 15 lb (6.8 kg)

Type	Shaking angle	Platform dimensions (W x H x D)	Power			Catalog number	Price
			VAC	Hz	Amps		
Single platform	Adjustable through 20° from horizontal	14" x 7" x 13" (35.6 x 17.8 x 33 cm)	115	60	0.5	<a href="#">GY-51401-01</a>	
			230	50	0.3	<a href="#">GY-51401-06</a>	
Double platform		14" x 11½" x 13" (35.6 x 29.2 x 33 cm)	115	60	0.5	<a href="#">GY-51401-11</a>	
			230	50	0.3	<a href="#">GY-51401-16</a>	



 Cole-Parmer®

## Dry Powder Rocking Shaker

### Protect against chemical deterioration

- Adjustable silicone-lined rack
- Unique mixing motion tosses powder from end-to-end while also rotating it
- Adjustable tilt capability and variable-speed control

**What's included:** 6-ft (1.8-m) three-wire cord with plug (US standard plug on 120 VAC models; three-wire plug on 240 VAC models).

Speed range	Maximum load	Bottle size	Shaking angle	Power			Catalog number	Price
				VAC	Hz	Amps		
2 to 60 rpm	15 lb	7" to 10" H; up to 7" dia	0 to 20°	120	50/60	1.50	<a href="#">GY-51605-00</a>	
				240		0.75	<a href="#">GY-51605-15</a>	

51605-00  
Shown with bottle  
(not included)

CE



## Compact Digital Rocking Shaker

### Place in incubators (non CO<sub>2</sub>), chambers, and refrigerators

- PID control for a consistent, smooth rocking motion
- Digital speed control easily adjusts from 5 to 100 rpm
- Adjustable tilt angle from 7 to 13° ensures gentle sample agitation
- Use in timer mode up to 99 hrs 59 minutes or continuous rocking

**What's included:** dimpled silicone mat, tray, two securing bands, and power cord (model 04725-06 has plug for US; model 04725-07 has plugs for China, Europe, and UK).

Shaking range	Power		Plug type	Catalog number	Price
	VAC	Hz			
7 to 13°	100 to 240	50/60	US	<a href="#">GY-04725-06</a>	
			Assorted†	<a href="#">GY-04725-07</a>	

†Model 04725-07 includes cord set with plugs for China, Europe, and UK.

[GY-04725-88](#) Rubber sticky mat and tray

[GY-04725-89](#) Dimpled silicone mat and tray

[GY-04725-90](#) Universal harness. Includes tray, sticky pad, and rubber bands

[GY-04725-91](#) Rubber bands for universal harness

**NEW**



CE

#### Specifications

**Speed range:** 5 to 100 rpm

**Maximum load:** 11 lb (5 kg)

**Timer:** 1 min to 99 hours, 59 min

**Platform dimensions:** 10⅞" x 10⅞"  
(27.6 x 27.6 cm)