

## Tube Revolver

### Be more flexible with interchangeable paddles

- Small footprint
- Paddles are adjustable from 0 to 90° to optimize the mixing angle
- Set in "oscillating" mode to achieve more effective mixing, oscillation occurs every 40 degrees in the rotation cycle
- Variable speed with easy-to-use intuitive controls
- Maintenance-free motor provides quiet operation

**What's included:** two 7 x 10/15-mL paddles, two 7 x 5/7-mL paddles, two 15 x 1.5/2-mL paddles, one 6 x 50-mL paddle, and power cord with plug (model 04725-16 has plug for US; model 04725-17 has plugs for China, Europe, and UK).

**NEW**



Speed range	Power		Plug type	Catalog number	Price
	VAC	Hz			
10 to 40 rpm	100 to 240	50/60	US	<a href="#">GY-04725-16</a>	
			Assorted†	<a href="#">GY-04725-17</a>	

†Model 04725-17 includes cord set with plugs for China, Europe, and UK.

#### Paddle Attachments

Paddle capacity	Cat. no.	Qty/pk	Price/pk
7 x 10/15-mL tubes	<a href="#">GY-04725-71</a>	2	
7 x 5/7-mL tubes	<a href="#">GY-04725-72</a>	2	
15 x 1.5/2-mL tubes	<a href="#">GY-04725-73</a>	2	
21 x 0.5/0.8-mL tubes	<a href="#">GY-04725-74</a>	2	
6 x 50-mL tubes	<a href="#">GY-04725-75</a>	1	

## Stovall Belly Dancer™ Shaker

### Ensure thorough mixing

- Unique, undulating motion with suction feet
- Constructed with chemically resistant materials
- Lightweight and extremely quiet

Trouble-free construction contains no belts or pulleys. High-quality shunt wound DC motor and control. Variable-speed control, from 0 to 125 rpm.



Collar adjustment varies platform angle from flat to 12° pitch. Orbital throw is 1" (2.5-cm). The open-sided platform accommodates oversize containers.

**What's included:** a platform, removable nonskid mat, 6-ft (1.8-m) 110/115 VAC power cord (no cord included for 220/240 VAC model).

#### Specifications

**Speed range:** 0 to 125 rpm  
**Maximum load:** 20 lb (9.1 kg)

**Platform dimensions (W x D):**  
12" x 12" (30.5 x 30.5 cm)

VAC	Power		Catalog number	Price
	Hz	Amps		
110/115 220/240	50/60	1.5	<a href="#">GY-51650-00</a> <a href="#">GY-51650-05</a>	

## Wrist-Action® Shakers

### Get wrist-action mixing without holding samples

- Adjustment arm lets you choose the shaking amplitude



Two "flask-holding" configurations are available: models with side arm capacity only or models with side arm and top platform capacity. Shaking amplitude is controlled with the adjustment arm. Overload protection turns shaker off in event of a malfunction.

**What's included:** side arm clamps and a 7-ft (2.1-m) cord with US standard plug; models with a top platform also include a set of 10 platform clamps.

#### Specifications

**Speed:** 385 oscillations/min (±10%)

**Timer range:** 0 to 60 min or continuous

**Max load:** 10 lbs.

**Shaking angle:** 0 to 15°

**Platform dimensions (W x D):**  
17" x 7¾" (43.1 x 19.7 cm)

Flask capacity		115 VAC, 60 Hz		220 VAC, 50 Hz	
Vessel capacity side arms	Platform capacity	Catalog number	Price	Catalog number	Price
4	None	<a href="#">GY-51100-01</a>		<a href="#">GY-51100-02</a>	
8	None	<a href="#">GY-51100-20</a>		<a href="#">GY-51100-25</a>	
12	None	<a href="#">GY-51100-30</a>		<a href="#">GY-51100-35</a>	
4	8†	<a href="#">GY-51100-80</a>		<a href="#">GY-51100-85</a>	
8	8†	<a href="#">GY-51100-90</a>		<a href="#">GY-51100-95</a>	
12	8†	<a href="#">GY-51100-96</a>		<a href="#">GY-51100-97</a>	

†250-mL flasks

**Wait!**

**There's More at**  
[ColeParmer.com](http://ColeParmer.com)

Find all the  
**product specs**  
you need!