

Cole-Parmer® Solid Laboratory Stoppers, Rubber or Neoprene

No guessing sizes—stopper has size raised on top

Black Rubber Stoppers stay pliable over a long period and withstand laboratory conditions without hardening. Stoppers retain resiliency even after repeated autoclaving. Contain some sulfur. **Autoclavable.**

Green Neoprene Stoppers withstand petroleum products, fats, oils, and organic chemicals. Stoppers exhibit good resiliency and shelf-life. Contain no sulfur. **Autoclavable.**

“Exactly as promised.”



Standard size no.	Top dia (mm)	Bottom dia (mm)	Height (mm)	Black rubber stoppers			Green neoprene stoppers		
				Catalog number	Qty/pk†	Price/pk	Catalog number	Qty/pk†	Price/pk
000	12.7	8.2	21	GY-62990-00	181		GY-62991-00	160	
00	15	10	25	GY-62990-02	105		GY-62991-02	95	
0	17	13	25	GY-62990-04	77		GY-62991-04	68	
1	19	14	25	GY-62990-06	57		GY-62991-06	48	
2	20	16	25	GY-62990-08	52		GY-62991-08	44	
3	24	18	25	GY-62990-10	39		GY-62991-10	32	
4	26	20	25	GY-62990-12	33		GY-62991-12	27	
5	27	23	25	GY-62990-14	28		GY-62991-14	23	
5½	28	24	25	GY-62990-16	26		GY-62991-16	23	
6	32	26	25	GY-62990-18	20		GY-62991-18	17	
6½	34	27	25	GY-62990-20	18		GY-62991-20	15	
7	37	30	25	GY-62990-22	15		GY-62991-22	12	
7½	39	31	25	GY-62990-24	14		GY-62991-24	13	
8	41	33	25	GY-62990-26	12		GY-62991-26	10	
8½	43	36	25	GY-62990-28	12		GY-62991-28	11	
9	45	37	25	GY-62990-30	10		GY-62991-30	8	
9½	46	38	25	GY-62990-32	9		GY-62991-32	9	
10	50	42	25	GY-62990-34	8		GY-62991-34	8	
10½	53	45	25	GY-62990-36	7		GY-62991-36	7	
11	56	48	25	GY-62990-38	6		GY-62991-38	6	
11½	63	50	25	GY-62990-40	5		GY-62991-40	4	
12	64	54	25	GY-62990-42	5		GY-62991-42	5	
13	68	58	25	GY-62990-44	4		GY-62991-44	4	
13½	75	62	35	GY-62990-46	3		GY-62991-46	3	
14	90	75	39	GY-62990-48	1		GY-62991-48	1	
15	103	83	39	GY-62990-50	1		GY-62991-50	1	
16	127	90	50	GY-62990-52	1		GY-62991-52	1	
Assortment pack, sizes 00 to 8				GY-62990-90	5 lb		GY-62991-90	5 lb	

†The quantity per pack given is an approximate number based on the average number of stoppers in one pound.

Solid Color-Coded Stoppers, Silicone

Fit a wide range of holes—flexible construction for easy fit

- Lightweight stoppers float if dropped in water
- Handle temperatures from –76 to 392°F (–60 to 200°C)
- Easily adapt to your needs—bore holes for thermometer or tubing addition
- Autoclavable



Standard size no.	Japanese size no.	Top dia (mm)	Bottom dia (mm)	Height (mm)	Color	Catalog number	Qty/pk	Price/pk
000	03	12	8	20	White	GY-06298-00	50	
00	01–02	15	11	22	Yellow	GY-06298-02	50	
0	1–2	17.5	13	25	Green	GY-06298-04	50	
2	3–4	20	15.5	27	Pink	GY-06298-06	20	
4	5–7	25	19	30	Blue	GY-06298-08	20	
5	8–9	30	23	33	White	GY-06298-10	10	
6½	10–11	35	28	35	Yellow	GY-06298-12	10	
8	12–14	40	33	40	Green	GY-06298-14	10	
9½	15–16	46	38	42	Pink	GY-06298-16	5	
10½	17–18	52	44	48	Blue	GY-06298-18	5	
11	19–20	58	49	52	White	GY-06298-20	5	
12	21–23	67	56	52	Yellow	GY-06298-22	1	
13½	24–26	77	65	52	Green	GY-06298-24	1	
14	27–29	87	75	52	Pink	GY-06298-26	1	