

Cole-Parmer® Versi-Vials

Don't sacrifice performance for price

- Eliminate costly needle damage with limited-volume inserts featuring bottom springs
- Get easier volume identification with graduated marking spots



Snap Vials

- Ideal for autosamplers
- Get a tight seal with enhanced neck, which minimizes breakage



98720-10



98720-18



98720-14

Description	Catalog number	Qty/pk	Price/pk
Snap vials, 2 mL, 12 mm x 32 mm			
Clear	GY-98720-00	100	
Clear, graduated white marking spot	GY-98720-01	100	
Amber, graduated white marking spot	GY-98720-02	100	
Limited-volume insert, 250 µL			
Bottom-spring insert, glass	GY-98730-00	100	
Closures, 11 mm			
Polycrimp seals, clear PTFE/red rubber	GY-98720-10	100	
Snap caps, clear 10 mil PTFE	GY-98720-14	100	
Snap caps, clear PTFE/red rubber	GY-98720-16	100	
Aluminum seals, blue	GY-98720-18	100	



98722-01



Wide-Neck Vials

- Ideal for robotic-arm autosample
- Wide-neck vials are designed to precisely center a limited-volume insert in the vial neck

Bottom-spring insert 98730-00 shown inside vial 98722-01



98722-11

Description	Catalog number	Qty/pk	Price/pk
Wide-neck vials; 2 mL, 12 mm x 32 mm			
Clear, graduated white marking spot	GY-98722-01	100	
Amber, graduated white marking spot	GY-98722-02	100	
Limited-volume inserts, 250 µL			
Bottom-spring insert, glass	GY-98730-00	100	
Preassembled closure and septa, 9 mm, screw-thread			
Blue cap, PTFE/silicone	GY-98722-12	100	



98721-01



Screw-Thread Vials

- Standard-opening vials are designed to work in autosamplers
- Screw-thread necks accept 8-425 mm closures and septa

Flat-bottom insert 98730-04 shown inside vial 98721-01



98721-12



98721-10

Description	Catalog number	Qty/pk	Price/pk
Screw-thread vials, 2 mL			
Clear	GY-98721-00	100	
Clear, graduated white marking spot	GY-98721-01	100	
Amber, graduated white marking spot	GY-98721-02	100	
Limited-volume insert, 250 µL			
Flat-bottom insert, glass	GY-98730-04	100	
Closures, 8-425 mm			
Top seal, clear molded 10 mil PP	GY-98721-10	100	
Open-top caps for Shimadzu, black PP (require separate seals, below)	GY-98721-12	100	
Seals for 98721-12 caps (above)			
PTFE/red rubber, 0.040"	GY-98721-21	100	
Red PTFE/silicone, slit, 0.035"	GY-98721-22	100	

Shell Vials with Plugs

- Ensure safe handling with thick-walled shell
- Get a tight seal with polyethylene (PE) plugs

Convenience packs include a clear covered tray containing 100 (12 x 32 mm) shell vials and 100 plugs that are packed separately so they remain particle-free.

Choose either clear Type I borosilicate glass vials in three sizes or limited-volume 700 µL polypropylene (PP) vials.



98723-02
Shell vials with plugs

Description	Catalog number	Qty/pk	Price/pk
Shell vial convenience packs, with plugs			
Limited-volume PP vials; 8 mm plug	GY-98723-00	100	
Clear glass vials; 8 mm plug	GY-98723-02	100	
Clear glass vials; 12 mm plug	GY-98723-04	100	
Clear glass vials; 15 mm plug	GY-98723-06	100	
Limited-volume inserts, 250 µL			
Bottom-spring insert, glass	GY-98730-00	100	
Bottom-spring insert, PP	GY-98730-02	100	