

032-15-GL FLOWMETER CALIBRATION DATA 032/221

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		0202-0e-09

Max. Flow	Min. Flow	Units	Metering Fluid	Date
48.7	3.66	std. ml/min	air	30-Nov-1999

Model Number	03216-04	Metering Temperature	70.0 °F
Tube Number	032-15-GL	Metering Pressure	14.70 psia
Serial Number		Metering density	0.001200 g/ml
Float Material	glass	Metering Viscosity	0.01812 cp
Float Density	2.53 g/ml	Density at STD.Cond	0.001200 g/ml
STD. Conditions	STP: 1 atm @ 70 °	Accuracy	Standard
Room Temperature	70.0 °F	Barometric Pressure	14.70 psia

SCALE READINGS AT CENTER OF FLOAT	
Scale Reading (mm)	Flow
65	48.7
60	43.8
55	38.1
50	32.7
45	27.9
40	22.9
35	19.0
30	15.5
25	12.6
20	9.94
15	7.27
10	5.41
5	3.66