Cole-Parmer®
Delivering Solutions You Trust

Telephone: 847.549.7600
800.323.4340
Fax: 847.247.2929
E-mail: techinfo@coleparmer.com
Web: www.coleparmer.com

092-04-GL FLOWMETER CALIBRATION DATA 092/36

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		1085-A1-AM-03D

Max. Flow	Min. Flow	Units	Metering Fluid	Date
2169	242	std. ml/min	oxygen	30-Nov-1999

Model Number	03227-20	**Metering Temperature**	70.0 °F
Tube Number	092-04-GL	**Metering Pressure**	14.70 psia
Serial Number		**Metering density**	0.001326 g/ml
Float Material	glass	**Metering Viscosity**	0.02030 cp
Float Density	2.53 g/ml	**Density at STD.Cond**	0.001326 g/ml
STD. Conditions	STP: 1 atm @ 70 °	**Accuracy**	std.
Room Temperature	70.0 °F	**Barometric Pressure**	14.70 psia

SCALE READINGS AT CENTER OF FLOAT

Scale Reading (mm)	Flow
150	2169
140	2039
130	1908
120	1791
110	1663
100	1548
90	1427
80	1293
70	1155
60	1005
50	850
40	691
30	532
20	370
10	242