

Orbital Shaking from 20-100RPM with Temperature Control

Interchangeable Platforms

 <p>Gentle Orbital Mixing</p>	 <p>Unique Temperature Flow</p>	 <p>Durable No-walk Housing</p>	 <p>28° to 75° C</p>
--	--	--	---



Standard

Non-slip tray contains spills
Fast temperature ramp up
Clear dome for 360° view
Minimal temperature fluctuation with open door



Increased Capacity

Stacking tray accessory can be stacked with no tools required



Unique Access

Access samples 3 ways -
Door
Kickstand (back, left or right)
Removable Cover

Specifications

Speed (RPM)	20-100 RPM
Orbit	19mm
Temperature	28° to 75° C
Weight	9 Kg (20 lbs.)
Dimensions	450 x 480mm (17.6 x 19in)
Platform	305 x 305 mm (12 x 12in)
Platform Weight Capacity	3 Kg (6.6 lbs)
Chamber Height	305mm (12in)
Chamber Volume	40 L (2400 cubic inches)

Ordering Information

Voltage & Plug configuration	GTS 100
120V - U.S Standard	SI-G100
230V - No Plug	SI-G101
230V - European Plug	SI-G102
230V - British Plug	SI-G103
230V - Swiss Plug	SI-G104
240V - Aust. Plug	SI-G106
100V	SI-G105

Accessory Ordering Information

Catalog No.	Description	Platform Capacity *
SI-1610	100 mL Flask Clamp	16
SI-1611	125/150 mL Flask Clamp	16
SI-1612	250 mL Flask Clamp	16
SI-1613	500 mL Flask Clamp	9
SI-1614	1 L Flask Clamp	5
SI-1615	2 L Flask Clamp	3

* See platform weight capacity

Catalog No.	Description
SI-M150	Stacking Tray
SI-1616	Double Sided Adhesive Tape, 60inx 1in (1.5m x 25.5mm)
SI-M1617	Adhering Mat, Blue, 300mm x 300mm (11.8in x 11.8in)
SI-G150	GTS Non-Slip Platform
SI-G1550	GTS Ratcheting Clamp Platform
SI-G1650	GTS Flask Clamp Platform
SI-G1750	GTS Adhering Mat Platform

