# Cole-Parmer®

Cole-Parmer® Gravity and Mechanical

**Convection Drying Ovens** 

- Low energy consumption provides operating cost savings
- PID controller gives you accurate and reliable temperature control
- Requires minimal heating time
- Easy-to-view LCD shows time, current and set temperatures, running status, and fan status
- Stainless steel inner chamber and powder-coated steel plate exterior resist corrosion for longer lifetime
- Rounded inner chamber corners offer easy cleaning
- Long-lasting silicone rubber gasket offers a tight seal, ensuring good heat retention and low energy consumption



Mechanical convection oven



# **Cole-Parmer®**

# Cole-Parmer® Gravity and Mechanical **Convection Drying Ovens**

Our gravity and mechanical convection drying ovens offer multiple safety features such as temperature deviation alarm, overtemperature set point alarm, overcurrent protection, and auto-start after power loss/return.

Gravity convection ensures gentle, natural, air circulation within the chamber suitable for sterilization, powder drying, high-temperature storage, and other applications requiring subtle airflow. Able to heat samples up to 200°C (392°F).

**Mechanical convection** offers fast heat-up and uniform temperature throughout the chamber for greater drying efficiency. The mechanical oven has an air vent on the back that can be adjusted by the knob located in front of the oven to control inner air and vapor circulation—ideal for your drying and sterilization needs. Able to heat samples up to 250°C (482°F).

Each oven includes stainless steel shelves with mounting brackets. Additional shelves can be ordered separately (see table).



Mechanical convection oven

### coleparmer.com

USA: +1.800.323.4340 +1.847.549.7600

Canada: +1.800.363.5900 China: +86.21.5109.9909 France: +33 (0) 1486 37800

Germany: +49 (0) 9377 92030

India: +1.800.266.1244 Italy: +39 (0) 1313 89513 UK: +44 (0) 1480.272279

All other countries: +1.847.549.7600



# Cole-Parmer® Gravity and Mechanical Convection Drying Ovens

#### **Specifications**

#### Temperature range:

Gravity: 10°C above ambient to 200°C (50 to 392°F)

Mechanical: 10°C above ambient to 250°C (50 to 482°F)

Display resolution: 0.1°C
Temperature control accuracy: ±0.5°C
Timer range: 0 to 99 hrs, 59 min

#### Rise time:

Gravity: 15 to 30 min to 100°C Mechanical: 20 to 50 min to 100°C



Capacity cu ft (L)	Temperature uniformity	No. of shelves included	No. of shelf positions	Dimensions (W x H x D)		Power			Oven	Additional shelf
				Chamber	Overall	VAC	Hz	Watts	Item number	Item number
Gravity convection ovens										
0.95 (27)	±3% at 100°C	2	6	12.6" x 14" x 11.8" (32 x 35.5 x 30 cm)	18" x 26" x 20.5" (46 x 66 x 52 cm)	120 220	60 50/60	- 850	ML-52411-00 ML-52411-01	ML-52411-36
1.97 (56)	±3% at 100°C	2	8	15.75" x 16.3" x 13" (40 x 41.5 x 33 cm)	21.2" x 28.3" x 21.6" (54 x 72 x 55 cm)	120 220	60 50/60	- 1000	ML-52411-02 ML-52411-03	ML-52411-37
3.4 (96)	±3.5% at 100°C	2	10	17.7" x 20" x 17" (45 x 50.5 x 43 cm)	23.2" x 32" x 25.5" (59 x 81 x 65 cm)	120 220	60 50/60	- 1400	ML-52411-04 ML-52411-05	ML-52411-38
5 (140)	±3.5% at 100°C	2	11	20.5" x 22.6" x 19.7" (52 x 57.5 x 50 cm)	26" x 34.6" x 28.3" (66 x 88 x 72 cm)	120 220	60 50/60	- 2000	ML-52411-06 ML-52411-07	ML-52411-39
7 (200)	±4% at 100°C	2	13	22.4" x 25" x 22" (57 x 64 x 56 cm)	28" x 37.2" x 30.7" (71 x 94.5 x 78 cm)	220	50/60	2200	ML-52411-08	ML-52411-40
Mechanica	I convection ovens									
0.56 (16)	±1.5% at 100°C	2	4	9.8" x 9.8" x 10" (25 x 25 x 26 cm)	20.8" x 16.3" x 14.8" (53 x 41.5 x 37.6 cm)	120 220	60 50/60	- 600	ML-52411-09 ML-52411-10	ML-52411-41
1 (30)	±2% at 100°C	2	5	13" x 12.5" x 12.5" (34 x 32 x 32 cm)	24.5" x 20" x 17.75" (62.2 x 50.5 x 45.1 cm)	120 220	60 50/60	- 850	ML-52411-11 ML-52411-12	ML-52411-42
1.7 (50)	±2.5% at 100°C	2	6	16.5" x 13.8" x 15.5" (42 x 35 x 39.5 cm)	27.5" x 21" x 20.8" (70 x 53.5 x 53 cm)	120 220	60 50/60	- 1100	ML-52411-13 ML-52411-14	ML-52411-43
2.8 (80)	±3% at 100°C	2	7	17.7" x 17.7" x 15.75" (45 x 45 x 40 cm)	29" x 24.2" x 20.5" (73.6 x 61.5 x 52.2 cm)	120 220	60 50/60	- 1550	ML-52411-15 ML-52411-16	ML-52411-44
4.8 (136)	±3% at 100°C	2	10	21.6" x 21.6" x 17.7" (55 x 55 x 45 cm)	32.75" x 28" x 22.8" (83.2 x 71.5 x 58.1 cm)	120 220	60 50/60	- 2050	ML-52411-17 ML-52411-18	ML-52411-45
7.8 (220)	±3% at 100°C	2	14	23.6" x 29.5" x 19.6" (60 x 75 x 50 cm)	34.6" x 36" x 24.8" (88 x 91.5 x 63 cm)	220	50/60	2450	ML-52411-19	ML-52411-46
14 (400)	±3.5% at 100°C	3	12	39.4" x 31.5" x 20" (100 x 80 x 51 cm)	50.5" x 41.7" x 29.5" (128.5 x 106 x 75 cm)	220	50/60	3100	ML-52411-20	ML-52411-47
22 (620)	±4% at 100°C	4	12	33" x 53.3" x 23.6" (84 x 135.5 x 60 cm)	38.5" x 74" x 31.5" (98 x 188 x 80 cm)	220	50/60	4000	ML-52411-21	ML-52411-48

### coleparmer.com

USA: +1.800.323.4340 +1.847.549.7600 Canada: +1.800.363.5900 China: +86.21.5109.9909 France: +33 (0) 1486 37800 Germany: +49 (0) 9377 92030 India: +1.800.266.1244 Italy: +39 (0) 1313 89513 UK: +44 (0) 1480.272279

All other countries: +1.847.549.7600

