



PH ELECTRODES

## 924 003 Glass Bodied Platinum Redox Electrode

## Description

This electrode is designed for standard ORP measurements of general solutions. It is suitable for general purpose measurements and accurate Q.C. and research work.



## Technical specifications

Parameter	Specification
Туре	Combination
Sealed/refillable	Refillable
Filling solution	4.0M KCI/AgCl (025 196)
End type	Platinum
mV Range	0-1000mV
Temperature range	0-80°C
Reference type	AgCI, liquid filled single junction
Junction type	Annular ceramic
Body material	Glass
Dimensions (length x diameter)	120mm x 12mm
Cable Length	1 metre (nominal)
Termination	BNC

This can be used with the following Jenway pH meters: - 550, 570, 3510, 3520 and 3540. This datasheet is for your guidance only.