

Cole-Parmer®

Cole-Parmer® Aseptic Sampling Assemblies With Nalgene® Media Bottles



These single-use sampling assemblies eliminate setup and after-use cleaning steps required for reusable containers. Aseptic sampling assemblies provide a closed system to reduce contamination and help protect sample integrity.

Each assembly includes a sterilized one-piece molded cap with TPE tubing, pinch clamp (on feed line), dip tube, hydrophobic filter (on vent line), and square polyethylene terephthalate glycol (PETG) media bottle. The cap features two ports with TPE tubing: one for venting and one for transferring.



CERTIFICATION

USP Class VI and RoHS compliant

WARNING: This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

APPLICATIONS

- Bio research, pharmaceutical, and life sciences applications

FEATURES/BENEFITS

- One-piece molded cap design reduces contamination and product loss
- Eliminate cleaning validation time
- Two ports with 1/8" ID x 1/4" OD TPE tubing vent and transfer lines
- Bagged and labeled in an ISO Class 7 cleanroom
- Gamma irradiated to sterility assurance level 10⁻⁶
- Lot traceable
- Autoclavable

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®
coleparmer.com

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

Specification and Ordering Table

Capacity (mL)	Bottle Material	Cap Material	Cap/Stopper Size	Vent Port Tube Length: in. (cm)	Transfer Port Tube Length: in. (cm)	Item Number
60	PETG	Polypropylene	24-415	2" (5)	8" (20)	50142-61
125	PETG	Polypropylene	38-430	4" (10)	18" (45)	50142-62
250	PETG	Polypropylene	38-430	4" (10)	18" (45)	50142-63
500	PETG	Polypropylene	38-430	4" (10)	18" (45)	50142-64
1000	PETG	Polypropylene	38-430	4" (10)	18" (45)	50142-65
2000	Polycarbonate	Polypropylene	38-430	4" (10)	18" (45)	50142-66